

MasterConnect LEDtube EM/Mains T8

MAScon LEDtube IA 1200mm UO 16.5W840 T8

Philips MasterConnect LEDtube EM/Mains T8 means easy upgrade to a connected lighting system. Its 2.4GHz mesh networking technology enables wireless integration with a variety of control devices, such as sensor and switch. The result? Even more energy saving and enhanced flexibility in your space. Through dimming, occupancy sensing and/or daylight harvesting, lamps deliver 50% or more energy saving thanks to MasterConnect technology.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,500 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	151.52 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	16.5 W
Lamp Current (Max)	76 mA
Lamp Current (Min)	69 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	Wireless Dim


MasterConnect LEDtube EM/Mains T8

Photometric data




Spectral Power Distribution Colour - MAScon LEDtube IA 1200mm UO 16.5W840 T8


Lifetime




Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W840 T8



Lumen Maintenance Diagram - MAScon LEDtube IA 1200mm UO 16.5W840 T8




Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W840 T8



Lumen Maintenance Diagram - MAScon LEDtube IA 1200mm UO 16.5W840 T8

MasterConnect LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAScon LEDtube IA 1200mm UO 16.5W840 T8

