

# Classic filament LEDbulbs

## CLA LEDBulb ND 10-100W A67 E27 865 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information		Lamp Current (Nom)	
Cap-Base	E27 [ E27]		86 mA
Nominal Lifetime (Nom)	15000 h	Wattage Equivalent	100 W
Switching Cycle	20000X	Starting Time (Nom)	0.5 s
Technical Type	10-100W	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	865 [ CCT of 6500K]	T-Case Maximum (Nom)	48 °C
Luminous Flux (Nom)	1521 lm		
Luminous Flux (Rated) (Nom)	1521 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	152.10 lm/W	Bulb Finish	Clear
Color Consistency	<6	Approval and Application	
Color Rendering Index (Nom)	80	Energy Efficiency Label (EEL)	A++
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	10 kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		
Power (Nom)	10 W		


# Classic filament LEDbulbs

## Product Data

Full product code	871869676708500
Order product name	CLA LEDBulb ND 10-100W A67 E27 865 CL
EAN/UPC - Product	8718696767085
Order code	929001815402
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001815402
Net Weight (Piece)	0.040 kg


## Dimensional drawing




Bulb A70 230V 11-100W 1521lm 6500K E27ND

Product	D	C
CLA LEDBulb ND 10-100W A67 E27 865 CL	70 mm	128 mm


## Photometric data



CLA LEDbulb 100W E27 865 CL A67



CLA LEDbulb 100W E27 865 CL A67




CLA LEDbulb 60W E27 840 CL A60

# Classic filament LEDbulbs

## Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

