



# LED Highbay

## 125HB/LED/750/ND NB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

### Product data

| General Information                   |                                 |
|---------------------------------------|---------------------------------|
| Cap-Base                              | EX39 [Exclusionary Mogul Screw] |
| Nominal lifetime                      | 50,000 hour(s)                  |
| Switching Cycle                       | 50,000                          |
| Lighting Technology                   | LED                             |
| EU RoHS compliant                     | Yes                             |
| Light Technical                       |                                 |
| Color Code                            | 750 [CCT of 5000K]              |
| Beam Angle (Nom)                      | 70 degree(s)                    |
| Luminous Flux                         | 16,000 lm                       |
| Color Designation                     | Daylight                        |
| Correlated Color Temperature (Nom)    | 5000 K                          |
| Luminous Efficacy (rated) (Nom)       | 128.00 lm/W                     |
| Color Consistency                     | <6                              |
| Color rendering index (CRI)           | 70                              |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %                            |
| Operating and Electrical              |                                 |
| Line Frequency                        | 50 to 60 Hz                     |
| Input Frequency                       | 50 to 60 Hz                     |
| Power Consumption                     | 125 W                           |
| Lamp Current (Nom)                    | 1,100 mA                        |
| Wattage Equivalent                    | 320 W                           |


| Starting Time (Nom)           | 0.5 s                         |
|-------------------------------|-------------------------------|
| Warm-up time to 60% light     | 0.5 s                         |
| Power Factor (Fraction)       | 0.9                           |
| Voltage (Nom)                 | 120-277 V                     |
| UL Type                       | Type B - bypass the ballast   |
| Temperature                   |                               |
| T-Case Maximum (Nom)          | 75 °C                         |
| Controls and Dimming          |                               |
| Dimmable                      | No                            |
| Mechanical and Housing        |                               |
| Bulb Shape                    | Others                        |
| Approval and Application      |                               |
| Energy Consumption kWh/1000 h | - kWh                         |
| Energy Certifications         | DLC Standard                  |
| Product Data                  |                               |
| Order product name            | 125HB/LED/750/ND NB DL BB 2/1 |
| Full product name             | 125HB/LED/750/ND NB DL BB 2/1 |
| Order code                    | 929001852504                  |
| Material Nr. (12NC)           | 929001852504                  |

LED Highbay

|                                 |              |
|---------------------------------|--------------|
| Numerator - Quantity Per Pack   | 1            |
| EAN/UPC - Product/Case          | 046677478117 |
| Numerator - Packs per outer box | 2            |



|                |                |
|----------------|----------------|
| EAN/UPC - Case | 50046677478112 |
|----------------|----------------|

Dimensional drawing




| Product                       | D      | C      |
|-------------------------------|--------|--------|
| 125HB/LED/750/ND NB DL BB 2/1 | 211 mm | 252 mm |

Photometric data



Spectral Power Distribution Colour - 125HB/LED/750/ND NB DL BB 2/1

Light Distribution Diagram - 125HB/LED/750/ND NB DL BB 2/1




General uniform lighting 125HB/LED/750/ND NB DL BB 2/1


General uniform lighting - 125HB/LED/750/ND NB DL BB 2/1

LED Highbay

Lifetime



Life Expectancy Diagram - 125HB/LED/750/ND NB DL BB 2/1



Lumen Maintenance Diagram - 125HB/LED/750/ND NB DL BB 2/1

