



# MASTER Plastic LEDbulbs

## MASTER LED BULB DT 12-75WE27 927-922 A67 FR

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information		Light Technical	
Cap-Base	E27 [E27]	Color Code	922-927 [CCT of 2200K-2700K]
Nominal lifetime	25,000 hour(s)	Beam Angle (Nom)	200 degree(s)
Switching Cycle	100,000	Luminous Flux	1,055 lm
Lighting Technology	LED	Color Designation	Warm White (WW)
EU RoHS compliant	Yes	Luminous Efficacy (rated) (Nom)	87.00 lm/W
		Color Consistency	<6
		Color rendering index (CRI)	90

MASTER Plastic LEDbulbs

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	12 W
Lamp Current (Nom)	68 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.1 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	176 °F
----------------------	--------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Bulb Shape	A67 [A 67mm]
------------	--------------


Approval and Application

Energy Consumption kWh/1000 h	12 kWh
-------------------------------	--------

Product Data


Order product name	MAS LED bulb DT 12-75WE27 927-922 A67 FR
Full product name	MASTER LED BULB DT 12-75WE27 927-922 A67 FR
Full product code	871869682618800
Order code	362723
Material Nr. (12NC)	929001868602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696826188
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696826195

Dimensional drawing




Product	D	C
MAS LED bulb DT 12-75WE27 927-922 A67 FR	3-1/16 inch	5-5/8 inch

Photometric data




General uniform lighting - MAS LED bulb DT 12-75WE27 927-922 A67 FR



Spectral Power Distribution Colour - MAS LED bulb DT 12-75WE27 927-922 A67 FR


MASTER Plastic LEDbulbs

Photometric data




Light Distribution Diagram - MAS LED bulb DT 12-75WE27 927-922 A67 FR

Lifetime



Lumen Maintenance Diagram - MAS LED bulb DT 12-75WE27 927-922 A67 FR



Life Expectancy Diagram - MAS LED bulb DT 12-75WE27 927-922 A67 FR

