



MASTER Plastic LEDbulbs

MASLEDbulb DT 15-100WE27 927-922 A67FR

The MASTER LEDbulb range delivers a dimmable glow effect for a welcoming, warm atmosphere, making it ideal for general lighting applications in the hospitality industry. Its unique design radiates warm light in all directions, making it a true alternative to the incandescent lamp. They are particularly suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of incandescent bulbs, MASTER LEDbulb delivers huge energy savings and minimizes maintenance cost without any compromise on light quality. They can be used together with most leading-edge dimmers, enabling further efficiencies while helping to create the desired atmosphere.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights


Product data

General Information			
Cap-Base	E27 [E27]	Beam Angle (Nom)	200 degree(s)
Nominal lifetime	25,000 hour(s)	Luminous Flux	1,521 lm
Switching Cycle	100,000	Color Designation	Warm White (WW)
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	101.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical			
Color Code	922-927 [CCT of 2200K-2700K]		


MASTER Plastic LEDbulbs

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	15 W
Lamp Current (Nom)	85 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.1 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted

Dimensional drawing




Photometric data



General uniform lighting - MASLEDbulb DT 15-100WE27 927-922 A67FR

Bulb Shape	A67 [A 67mm]
Approval and Application	
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	MASLEDbulb DT 15-100WE27 927-922 A67FR
Full product name	MASLEDbulb DT 15-100WE27 927-922 A67FR
Full product code	871869682620100
Order code	929001868702
Material Nr. (12NC)	929001868702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696826201
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696826218


Product	D	C
MASLEDbulb DT 15-100WE27 927-922 A67FR	77 mm	142 mm



Spectral Power Distribution Colour - MASLEDbulb DT 15-100WE27 927-922 A67FR


MASTER Plastic LEDbulbs

Photometric data




Light Distribution Diagram - MASLEDBulb DT 15-100WE27 927-922 A67FR

Lifetime



Lumen Maintenance Diagram - MASLEDBulb DT 15-100WE27 927-922 A67FR



Life Expectancy Diagram - MASLEDBulb DT 15-100WE27 927-922 A67FR

