



T8

12T8/MAS/48-840/MF18/G 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h
Light Technical	
Color Code	841 [CCT of 4100K (841)]
Beam Angle (Nom)	240 °
Initial lumen (Nom)	1800 lm
Luminous Flux (Rated) (Nom)	1800 lm
Rated Beam Angle	240 °
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	12 W

Lamp Current (Max)	120 mA
Lamp Current (Min)	40 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	1200 mm

T8

Approval and Application


Energy Saving Product	Yes
Approbation Marks	RoHS compliance UL certificate DLC compliance

Product Data

Order product name	12T8/MAS/48-840/MF18/G 10/1
EAN/UPC - Product	046677532697

Order code	532697
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001877034
Net Weight (Piece)	0.215 kg
Model Number	9290018770A



Dimensional drawing



Performance TypeB 1800lm 12W


Product	D1	D2	A1	A2	A3
12T8/MAS/48-840/MF18/G 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

Photometric data




LEDtube PRO 12W G13 840 24D ND

LEDtube PRO 12W G13 830 24D ND




LEDtube PRO 12W G13 840 24D ND


Lifetime




LEDtube PRO 12W G13 830 24D ND




LEDtube PRO 12W G13 830 24D ND



LEDtube PRO 12W G13 830 24D ND



LEDtube PRO 12W G13 830 24D ND



LEDtube PRO 12W G13 830 24D ND

