

T8

12T8/PER/48-850/BB18/G 10/1 FB


Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	12 W
Nominal lifetime	50,000 hour(s)	Lamp Current (Max)	120 mA
Switching Cycle	50,000	Lamp Current (Min)	40 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.9
Color Code	850 [CCT of 5000K]	Voltage (Nom)	120-277 V
Beam Angle (Nom)	240 degree(s)	Temperature	
Luminous Flux	1,800 lm	Ambient temperature range	-4 °F to 113 °F
Color Designation	Daylight	T-Case Maximum (Nom)	158 °F
Correlated Color Temperature (Nom)	5000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	150.00 lm/W	Dimmable	No
Color Consistency	<5	Mechanical and Housing	
Color rendering index (CRI)	80	Product Length	47-1/4 inch
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	T8
Operating and Electrical			
Line Frequency	50 to 60 Hz		


Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard
Product Data	
Order product name	12T8/PER/48-850/BB18/G 10/1 FB

Dimensional drawing




Product	D1	D2	A1	A2	A3
12T8/PER/48-850/ BB18/G 10/1 FB	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch


Photometric data





Light Distribution Diagram - 12T8/PER/48-850/BB18/G 10/1 FB




Spectral Power Distribution Colour - 12T8/PER/48-850/BB18/G 10/1 FB




Lifetime



Life Expectancy Diagram - 12T8/PER/48-850/BB18/G 10/1 FB




Life Expectancy Diagram - 12T8/PER/48-850/BB18/G 10/1 FB



Life Expectancy Diagram - 12T8/PER/48-850/BB18/G 10/1 FB

Lumen Maintenance Diagram - 12T8/PER/48-850/BB18/G 10/1 FB



Lumen Maintenance Diagram - 12T8/PER/48-850/BB18/G 10/1 FB

