



MASTER LEDspot LV

MASTER LED 7-50W 940 MR16 36D Dim

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	GU5.3 [GU5.3]	4000 K	
Nominal lifetime	40,000 hour(s)	Luminous Efficacy (rated) (Nom)	
Switching Cycle	50,000	75.00 lm/W	
Lighting Technology	LED	Color Consistency	
EU RoHS compliant	Yes	<4	
Light Technical		Color rendering index (CRI)	
Color Code	940 [CCT of 4000K]	90	
Beam Angle (Nom)	36 degree(s)	LLMF At End Of Nominal Lifetime (Nom)	
Luminous Flux	530 lm	70 %	
Luminous Intensity (Nom)	1,500 cd	Operating and Electrical	
Color Designation	Cool White (CW)	Line Frequency	
		- Hz	
		Input Frequency	
		- Hz	
		Power Consumption	
		7 W	
		Lamp Current (Nom)	
		830 mA	
		Wattage Equivalent	
		50 W	
		Starting Time (Nom)	
		0.5 s	

MASTER LEDspot LV

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes


Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	MASTER LED 7-50W 940 MR16 36D Dim
Full product name	MASTER LED 7-50W 940 MR16 36D Dim
Full product code	871869681243300
Order code	929001880308
Material Nr. (12NC)	929001880308
Local order code	LED940MR1636DD
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696812433
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696812440

Dimensional drawing




Product	D	C
MASTER LED 7-50W 940 MR16 36D Dim	50.5 mm	46.5 mm

Photometric data




Spectral Power Distribution Colour - MASTER LED 7-50W 940 MR16 36D Dim



Light Distribution Diagram - MASTER LED 7-50W 940 MR16 36D Dim


Photometric data




Calculation Photometrics 4.5 Philips Lighting B.V. Page 1/1

Accent Lighting Spots - MASTER LED 7-50W 940 MR16 36D Dim

Lifetime



Lumen Maintenance Diagram - MASTER LED 7-50W 940 MR16 36D Dim



Life Expectancy Diagram - MASTER LED 7-50W 940 MR16 36D Dim

