



MASTER LEDspot LV

MASTER LED 7-50W 940 MR16 36D Dim

MASTER LEDspot LV 可提供耀眼的重要照明光束，是最適合聚光照明的改裝解決方案。MASTER LEDspot LV 設計來做為鹵素燈或白熾燈的改裝替代方案。其可實現最真實的色彩，創造適合住宅、旅館的溫馨舒適氛圍，還能在零售應用中強調商品之美。新型外殼尺寸更小，適合市場上採用 MR16 GU 5.3 固定座的多數燈具。本產品採用飛利浦專利解決方案，廣泛與標準 12V 鹵素電子變壓器相容，也提供相當於 MR16 鹵素聚光燈的高光束強度。調光功能可營造出希望的氛圍，還能搭配各種調光器使用。其高 SDCM 可確保色彩一致性，在整個使用壽命期間長保不變。MASTER LEDspot LV 節能效果極高，可將維護成本降至最低，而不會對光線品質和使用壽命造成任何影響，還能讓住宅所有人和企業主在短時間內回收投資。

产品数据


一般資訊		LLMF 標稱壽命結束 (規範)	
燈座基底	GU5.3 [GU5.3]	70 %	
標稱使用壽命	40,000 h	運轉與電力	
切換週期	50,000	線路頻率	- Hz
照明技術	LED	輸入頻率	- Hz
符合歐盟 RoHS 標準	是	耗電量	7 W
照明技術		燈具電流 (標稱)	830 mA
色碼	940 [CCT of 4000K]	相等瓦數	50 W
光束角 (Nom)	36 °	起始時間 (標稱)	0.5 s
光通量	530 lm	達到 60% 光色的熱機時間	0.5 s
光強 (標稱)	1,500 cd	功率因數 (比值)	0.7
色彩名稱	冷白光 (CW)	電壓 (標稱)	12 V
相關色彩溫度 (規範)	4000 K	溫度	
光效 (額定) (標準)	75.00 lm/W	T 盒上限 (正常情況)	90 °C
色彩一致性	<4		
演色性指數 (CRI)	90		

MASTER LEDspot LV

控制與調光	
可調光	是
機械與外罩	
燈泡形狀	MR16 [2 吋/50mm]
認證與應用	
適合補強燈	是
能源消耗 kWh/1000 h	8 kWh
產品資料	
下訂產品名稱	MASTER LED 7-50W 940 MR16 36D Dim


完整產品名稱	MASTER LED 7-50W 940 MR16 36D Dim
完整產品代碼	871869681243300
訂單代碼	929001880308
材質 Nr. (12NC)	929001880308
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718696812433
分子 - 每一外盒包裝	10
EAN/UPC - 箱	8718696812440

二维绘图




Product	D	C
MASTER LED 7-50W 940 MR16 36D Dim	50.5 mm	46.5 mm

光度数据




Spectral Power Distribution Colour - MASTER LED 7-50W 940 MR16 36D Dim



Light Distribution Diagram - MASTER LED 7-50W 940 MR16 36D Dim


光度数据




Technical Information 1.1 Philips Lighting B.V. Page 10

Accent Lighting Spots - MASTER LED 7-50W 940 MR16 36D Dim

壽命



Lumen Maintenance Diagram - MASTER LED 7-50W 940 MR16 36D Dim



Life Expectancy Diagram - MASTER LED 7-50W 940 MR16 36D Dim

