

# Corepro InstantFit (UL Type-A) T8

## 30T8/COR/96-835/IF39/G/FA8 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

#### **Product data**

General Information				
Ceneral information				
Cap-Base	FA8 [FA8]			
Nominal lifetime	50,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	835 [CCT of 3500K]			
Beam Angle (Nom)	240 degree(s)			
Luminous Flux	3,950 lm			
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3500 K			
Luminous Efficacy (rated) (Nom)	131.00 lm/W			

Color Consistency	ANSI		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	35000-150000 Hz		
Input Frequency	35000-150000 Hz		
Power Consumption	30 W		
Lamp Current (Max)	350 mA		
Lamp Current (Min)	100 mA		
Wattage Equivalent	60 W		
Starting Time (Nom)	0.5 s		
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.9		


Datasheet, 2023, November 3 data subject to change

## Corepro InstantFit (UL Type-A) T8

Voltage (Nom)	200-500 V
UL Type	UL Type A
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	113 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	94-1/2 inch
Bulb Shape	Т8
Approval and Application	
Energy Saving Product	Yes


Approval Marks	UL certificate RoHS compliance		
Energy Consumption kWh/1000 h	- kWh		
Energy Certifications	DLC Standard		
<b>Application Conditions</b>			
can it be used in closed luminaires	Yes		
Product Data			
Order product name	30T8/COR/96-835/IF39/G/FA8 10/1		
Full product name	30T8/COR/96-835/IF39/G/FA8 10/1		
Order code	533018		
Material Nr. (12NC)	929001897204		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	046677533014		
Numerator - Packs per outer box	10		
EAN/UPC - Case	50046677533019		

## Dimensional drawing




Product	D1	D2	A1	A2	А3
30T8/COR/96-835/	1-1/16 inch	1-1/8 inch	93-3/16 inch	93-9/16 inch	93-15/16 inch
IF39/G/FA8 10/1					

#### Photometric data




Light Distribution Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1



Spectral Power Distribution Colour - 30T8/COR/96-835/IF39/G/FA8 10/1

## Corepro InstantFit (UL Type-A) T8


#### Photometric data




Calculus Photogramories 4.5 Philips Lighting G.V. Page: 171


General uniform lighting - 30T8/COR/96-835/IF39/G/FA8 10/1

#### Lifetime






Lumen Maintenance Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1



Lumen Maintenance Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1




Life Expectancy Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1

Life Expectancy Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1

## Corepro InstantFit (UL Type-A) T8

## Lifetime



Life Expectancy Diagram - 30T8/COR/96-835/IF39/G/FA8 10/1

