PHILIPS

Lighting



MASTER LEDtube Mains T5



MASTER LEDtube 1200mm HO 26W 865 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! . Perfectly safe, reliable & easy to install Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximize value over lifetime with high energy saving and lower maintenance costs.

Product data

General Information	
Cap-Base	G5
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	3,900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	150 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	26 W
Lamp Current (Nom)	125 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	54 W
Inrush current at mains	20
Max. lamp no. on MCB B type 10A - Mains	31

MASTER LEDtube Mains T5

Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	-
Max. lamp no. on MCB B type 16A - Mains	50
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	-
Ballast Compatibility	Mains

Temperature

Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	65 °C

Controls and Dimming

Dimmable	No

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T5


Approval and Application

Energy Efficiency Class	D
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	26 kWh
EPREL Registration Number	1476414

Product Data

Order product name	MAS LEDtube 1200mm HO 26W 865 T5
Full product name	MASTER LEDtube 1200mm HO 26W 865 T5
Full product code	871869681925800
Order code	81925800
Material Nr. (12NC)	929001908702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696819258
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696819265


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm HO 26W 865 T5	15.5 mm	17.1 mm	1,149 mm	1,156 mm	1,163 mm

MASTER LEDtube Mains T5


Photometric data



Spectral Power Distribution Colour - MAS LEDtube 1200mm HO 26W 865 T5




General uniform lighting - MAS LEDtube 1200mm HO 26W 865 T5




Light Distribution Diagram - MAS LEDtube 1200mm HO 26W 865 T5

Lifetime




Life Expectancy Diagram - MAS LEDtube 1200mm HO 26W 865 T5




Life Expectancy Diagram - MAS LEDtube 1200mm HO 26W 865 T5

MASTER LEDtube Mains T5


Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 26W 865 T5



Lumen Maintenance Diagram - MAS LEDtube 1200mm HO 26W 865 T5



Life Expectancy Diagram - MAS LEDtube 1200mm HO 26W 865 T5

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.