



TrueForce High Lumen PAR

23PAR30s/PER/930/S15/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.


Product data

General Information		Power (Rated) (Nom)	
Base	E26 [Single Contact Medium Screw]		23 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	206 mA
Switching Cycle	50000X	Wattage Equivalent	75 W
Technical Type	23-75W	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.9
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	930 [CCT of 3000K]	T-Case Maximum (Nom)	94 °C
Beam Angle (Nom)	15 °		
Initial lumen (Nom)	1900 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	1900 lm	Dimmable	No
Luminous Intensity (Nom)	12000 cd		
Color Designation	White (WH)	Approval and Application	
Rated Beam Angle	15 °	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	82.00 lm/W	Product Data	
Color Consistency	<4	Order product name	23PAR30s/PER/930/S15/ND/120V 6/1FB
Color Rendering Index (Nom)	90	EAN/UPC - Product	046677534684
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order code	534685
		Numerator - Quantity Per Pack	1
Operating and Electrical			
Input Frequency	50 to 60 Hz		

TrueForce High Lumen PAR

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917404
Net Weight (Piece)	0.220 kg



Dimensional drawing



PAR30s 24.5-W 2000lm 15D 3000K E26 ND

Product	D	C
23PAR30s/PER/930/S15/ND/120V 6/1FB	96 mm	94 mm


Photometric data



LEDspot PAR30 1FB

LEDspot PAR30 1FB



LEDspot 23 PAR30L 930 S15



LEDspot 23 PAR30L 930 S15

TrueForce High Lumen PAR

Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

