

CorePro MainsFit (UL Type-B) T8

8.5T8/COR/24-850/MF11/G 10/1

The CorePro MainsFit (UL Type B) lamps are designed to be the perfect retrofit solution to move from traditional fluorescent lamps to energy saving LEDs. This ballast bypass lamp has everything needed built into the lamp with proven energy savings, long life (up to 50k hours), surge suppression and industry leading safety features. All lamps in the CorePro MainsFit family are double-ended to help simplify the installation. In addition, all lamps meet the Philips standards for light quality so that end users will be in a comfortable environment regardless of the CorePro MainsFit lamp type.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	1,150 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	135.00 lm/W
Color Consistency	<5
Color rendering index (CRI)	82

LLMF At End Of Nominal Lifetime (Nom) 70 %		
Operating and Electrical		
Line Frequency	50 to 60 Hz	
Input Frequency	50 to 60 Hz	
Power Consumption	8.5 W	
Lamp Current (Max)	75 mA	
Lamp Current (Min)	36 mA	
Wattage Equivalent	17 W	
Starting Time (Nom)	0.9 s	
Warm-up time to 60% light	0.9 s	
Power Factor (Fraction)	0.9	
Voltage (Nom)	120-277 V	
UL Type	UL Type B	
Temperature		
Ambient temperature range	-4 °F to 113 °F	


Datasheet, 2023, August 16 data subject to change

CorePro MainsFit (UL Type-B) T8

T-Case Maximum (Nom)	122 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	23-5/8 inch
Bulb Shape	Т8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC
	compliance
Energy Consumption kWh/1000 h	- kWh

Energy Certifications	DLC Standard
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	8.5T8/COR/24-850/MF11/G 10/1
Full product name	8.5T8/COR/24-850/MF11/G 10/1
Order code	535484
Material Nr. (12NC)	929001934104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677535483
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677535488


Dimensional drawing




 Product
 D
 A1
 A2
 A3

 8.5T8/COR/24-850/MF1I/G10/1
 1-1/16 inch
 23-1/4 inch
 23-1/2 inch
 23-13/16 inch

Photometric data






180°

Spectral Power Distribution Colour - 8.5T8/COR/24-850/MF11/G 10/1

Light Distribution Diagram - 8.5T8/COR/24-850/MF11/G 10/1

CorePro MainsFit (UL Type-B) T8


Photometric data




Calculus Photometrics 4.5 Philips Lighting Scv. Fago: 171


General uniform lighting - 8.5T8/COR/24-850/MF11/G 10/1

Lifetime






Life Expectancy Diagram - 8.5T8/COR/24-850/MF11/G 10/1



Lumen Maintenance Diagram - 8.5T8/COR/24-850/MF11/G 10/1




Lumen Maintenance Diagram - 8.5T8/COR/24-850/MF11/G 10/1

Life Expectancy Diagram - 8.5T8/COR/24-850/MF11/G 10/1

CorePro MainsFit (UL Type-B) T8

Lifetime



Life Expectancy Diagram - 8.5T8/COR/24-850/MF11/G 10/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.