



LED Designer Deco

7.5A50/VIN/820/CL/G/D+CORD VIN


Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

General Information		Warm-up time to 60% light		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	Power Factor (Fraction)		0.7
Nominal lifetime	15,000 hour(s)	Voltage (Nom)		120 V
Switching Cycle	20,000			
Rated Lifetime (Hours)	15,000 hour(s)	Temperature		
Lighting Technology	LED	T-Case Maximum (Nom)		113 °F
EU RoHS compliant	Yes			
Light Technical		Controls and Dimming		
Color Code	820 [CCT of 2000K]	Dimmable		Yes
Luminous Flux	400 lm			
Color Designation	Flame	Mechanical and Housing		
Correlated Color Temperature (Nom)	2000 K	Bulb Shape		A50 [A 50 inch]
Luminous Efficacy (rated) (Nom)	53.00 lm/W			
Color Consistency	<6	Approval and Application		
Color rendering index (CRI)	80	Energy Consumption kWh/1000 h		- kWh
LLMF At End Of Nominal Lifetime (Nom)	70 %	EyeComfort		Yes
Operating and Electrical		Product Data		
Line Frequency	50 to 60 Hz	Order product name		7.5A50/VIN/820/CL/G/D+CORD VIN
Input Frequency	50 to 60 Hz	Full product name		7.5A50/VIN/820/CL/G/D+CORD VIN
Power Consumption	7.5 W	Order code		539676
Lamp Current (Nom)	70 mA	Material Nr. (12NC)		929001936495
Wattage Equivalent	40 W	Numerator - Quantity Per Pack		1
Starting Time (Nom)	0.5 s	EAN/UPC - Product/Case		046677539672
		Numerator - Packs per outer box		2



EAN/UPC - Case	50046677539677
----------------	----------------

Dimensional drawing




Product	D	C
7.5A50/VIN/820/CL/G/D+CORD VIN	6-5/16 inch	11-1/2 inch

Photometric data



Spectral Power Distribution Colour - 7.5A50/VIN/820/CL/G/D+CORD VIN

Light Distribution Diagram - 7.5A50/VIN/820/CL/G/D+CORD VIN



General uniform lighting - 7.5A50/VIN/820/CL/G/D+CORD VIN

Lifetime



Life Expectancy Diagram - 7.5A50/VIN/820/CL/G/D+CORD VIN



Lumen Maintenance Diagram - 7.5A50/VIN/820/CL/G/D+CORD VIN

