

Premium LED bulbs

Vintage Filament

LEDClassic 35W A60 E27 825 100-240V NDBR

Featuring a classic heritage design, the new Philips Vintage LED lamp family is reminiscent of familiar incandescent bulbs. Available in an array of giant shapes, candles and other familiar form factors, they provide a seamless fit across your space. When used as a statement piece, they add a sense of nostalgia and create a highly desirable atmosphere for socialization and relaxing.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	825 [CCT of 2500K]
Luminous Flux	400 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	4 W
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V
Temperature	
T-Case Maximum (Nom)	52 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Transparent amber
Bulb Shape	A60
Approval and Application	
Energy Consumption kWh/1000 h	- kWh

Premium LED bulbs Vintage Filament

Product Data	
Order product name	LEDClassic 35W A60 E27 825 100-240V NDBR
Full product name	LEDClassic 35W A60 E27 825 100-240V NDBR
Full product code	871869959566100
Order code	929001941546
Material Nr. (12NC)	929001941546



Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699595661
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699595678

Dimensional drawing




Product	D	C
LEDClassic 35W A60 E27 825 100-240V NDBR	60 mm	106 mm

Photometric data



General uniform lighting - LEDClassic 35W A60 E27 825 100-240V NDBR


Spectral Power Distribution Colour - LEDClassic 35W A60 E27 825 100-240V NDBR




Light Distribution Diagram - LEDClassic 35W A60 E27 825 100-240V NDBR

Premium LED bulbs Vintage Filament

Lifetime



Life Expectancy Diagram - LEDClassic 35W A60 E27 825 100-240V NDBR



Lumen Maintenance Diagram - LEDClassic 35W A60 E27 825 100-240V NDBR

