

LED G25

3.8G25/PER/927-922/CL/G/E26/WGX1FB T20

Philips G25 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	3.8-40W

Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	300 °
Initial lumen (Nom)	350 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700-2200 K
Luminous Efficacy (rated) (Nom)	92.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	3.8 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.75
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	50 °C


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Order product name	3.8G25/PER/927-922/CL/G/E26/WGX1FB T20
EAN/UPC - Product	046677549503
Order code	549501
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001969704
Net Weight (Piece)	0.040 kg

LED G25



Dimensional drawing



Bulb G25 120V 4.5-40W 350lm 2200-2700K

Product	D	C
3.8G25/PER/927-922/CL/G/E26/WGX1FB T20	80 mm	121 mm


Photometric data



© 2019 Philips Lighting B.V. Page 1/1

LEDbulb CL,FR 927


LEDbulb 40W E26 G25 927 CL



LEDbulb 927 CL

LED G25

Lifetime



15K LED

15K LMP

