



TrueForce LED Public (Urban/Road – HPL/SON)

TrueForce LED HPL ND 30-21W E27 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) lamps. These lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, with a low initial investment delivering instant savings. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing system, thereby enhancing the light quality without having to change the fixtures or sacrifice the light effect.

Product data

General Information		Colour Rendering Index horiz (Nom)	
Cap-Base	E27 [E27]		80
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Nominal Lifetime (Nom)	50000 h	Operating and Electrical	
Switching Cycle	50000X	Input Frequency	50 to 60 Hz
Technical Type	21-80W	Power (Rated) (Nom)	21 W
		Lamp Current (Nom)	95 mA
		Wattage Equivalent	80 W
		Starting Time (Nom)	0.45 s
		Warm Up Time to 60% Light (Nom)	0.45 s
		Power Factor (Nom)	0.95
		Voltage (Nom)	220-240 V
Light Technical			
Colour Code	840 [CCT of 4000K]		
Beam Angle (Nom)	360 °		
Luminous Flux (Nom)	3000 lm		
Colour Designation	Cool White (CW)		
Colour Temperature, horizontal (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	142.00 lm/W		
Color Consistency	<6		

TrueForce LED Public (Urban/Road – HPL/SON)

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------


Approval and Application

Energy Efficiency Label	A++
Energy Consumption kWh/1000 h	21 kWh

Product Data

Full product code	871869963816000
Order product name	TrueForce LED HPL ND 30-21W E27 840
EAN/UPC - Product	8718699638160
Order code	63816000
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002006202
Net Weight (Piece)	0.370 kg


Dimensional drawing




Tforce LED HPL ND 3klm E27 840 CL IP65

Product	D	C
TrueForce LED HPL ND 30-21W E27 840	75 mm	178 mm

Photometric data




LEDTrueForce E27 360



LEDTrueForce E27 21W 4000K


TrueForce LED Public (Urban/Road – HPL/SON)

Photometric data




LEDTrueForce E27 21W 4000K

Lifetime



LEDTrueForce Others 360



LEDTrueForce Others 360

