



# TrueForce LED Public (Urban/Road – HPL/SON)

## TrueForce LED HPL ND 38-28W E27 830

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) lamps. These lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, with a low initial investment delivering instant savings. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing system, thereby enhancing the light quality without having to change the fixtures or sacrifice the light effect.

### Product data

General Information		Colour Rendering Index horiz (Nom)	
Cap-Base	E27 [ E27]		80
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Nominal Lifetime (Nom)	50000 h	Operating and Electrical	
Switching Cycle	50000X	Input Frequency	50 to 60 Hz
Technical Type	28-125W	Power (Rated) (Nom)	28 W
		Lamp Current (Nom)	125 mA
		Wattage Equivalent	125 W
		Starting Time (Nom)	0.45 s
		Warm Up Time to 60% Light (Nom)	0.45 s
		Power Factor (Nom)	0.95
		Voltage (Nom)	220-240 V
Light Technical			
Colour Code	830 [ CCT of 3000K]		
Beam Angle (Nom)	360 °		
Luminous Flux (Nom)	3800 lm		
Colour Designation	White (WH)		
Colour Temperature, horizontal (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	135.00 lm/W		
Color Consistency	<6		

# TrueForce LED Public (Urban/Road – HPL/SON)

## Temperature

T-Case Maximum (Nom)	85 °C
----------------------	-------

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Clear
-------------	-------


## Approval and Application

Energy Efficiency Label	A++
Energy Consumption kWh/1000 h	28 kWh

## Product Data

Full product code	871869963818400
Order product name	TrueForce LED HPL ND 38-28W E27 830
EAN/UPC - Product	8718699638184
Order code	63818400
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002006302
Net Weight (Piece)	0.370 kg


## Dimensional drawing




Tforce LED HPL ND 4klm E27 830 CL IP65

Product	D	C
TrueForce LED HPL ND 38-28W E27 830	75 mm	178 mm

## Photometric data




LEDTrueForce E27 28W 3000K



LEDTrueForce E27 360

# TrueForce LED Public (Urban/Road – HPL/SON)


## Photometric data




© 2020 Philips Lighting B.V. Page 1/1

LEDTrueForce E27 28W 3000K

## Lifetime



LEDTrueForce Others 360



LEDTrueForce Others 360

