



TrueForce - LED HID HPL

TForce LED HPL ND 40-28W E27 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED to HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

Warnings and Safety

- Installation should always be performed by a qualified electrician or installer. Use the installation guide for instructions

Product data

General Information			
Cap-Base	E27 [E27]	Luminous Efficacy (rated) (Nom)	142 lm/W
Nominal lifetime	50,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Flickering value (PstLM)	1
CE mark	Yes	Stroboscopic effect value (SVM)	1.6
EU RoHS compliant	Yes	Photobiological safety according to EN 62471	RG1
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	360 degree(s)	Input Frequency	50 to 60 Hz
Luminous Flux	4,000 lm	Power Consumption	28 W
Color Designation	Cool White (CW)	Lamp Current (Nom)	125 mA
Correlated Color Temperature (Nom)	4000 K	Starting Time (Nom)	0.45 s
		Warm-up time to 60% light	0.45 s

TrueForce - LED HID HPL

Power Factor (Fraction)	0.95
Voltage (Nom)	220-240 V
Max. lamp no. on MCB B type 10A - Mains	47
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	47
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	8
Max. lamp no. on MCB B type 16A - Mains	74
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	74
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	14

Temperature

Ambient temperature range	-30 to +45 °C
T-Case Maximum (Nom)	60 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
-------------	-------

Bulb Shape	Others
------------	--------


Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	28 kWh
EPREL Registration Number	403571

Product Data



Order product name	TForce LED HPL ND 40-28W E27 840
Full product name	TForce LED HPL ND 40-28W E27 840
Full product code	871869963820700
Order code	929002006402
Material Nr. (12NC)	929002006402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699638207
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699638214

Dimensional drawing



Product	D	C
TForce LED HPL ND 40-28W E27 840	75 mm	178 mm

Photometric data




General uniform lighting - TForce LED HPL ND 40-28W E27 840

Light Distribution Diagram - TForce LED HPL ND 40-28W E27 840


TrueForce - LED HID HPL

Photometric data




Spectral Power Distribution Colour - TForce LED HPL ND 40-28W E27 840

Lifetime



Life Expectancy Diagram - TForce LED HPL ND 40-28W E27 840



Lumen Maintenance Diagram - TForce LED HPL ND 40-28W E27 840

