

# TrueForce LED Public (Urban/Road – HPL/SON)

## TrueForce LED HPL ND 60-42W E27 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED-to-HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

### Warnings and Safety

- Installation must always be performed by a qualified electrician or installer. Use the installation guide for instructions
- Link to Ballast – igniter compatibility list <https://www.assets.signify.com/is/content/Signify/Assets/philips-lighting/global/HIDLED-EU-compatibility-list-professional.pdf>

### Product data

General Information		Light Technical	
Cap base	E27	Colour Code	840 [CCT of 4000K]
Nominal lifetime	50,000 h	Beam angle (nom.)	360 degree(s)
Switching Cycle	50,000	Luminous Flux	6,000 lm
Lighting Technology	LED	Colour designation	Cool White (CW)
Flux measurement reference	Sphere	Correlated Colour Temperature	4000 K
CE mark	Yes	Luminous efficacy (rated) (nom.)	142 lm/W
EU RoHS compliant	Yes	Colour consistency	<6
		Colour rendering index (CRI)	80
		LLMF at end of nominal lifetime (nom.)	70 %

## TrueForce LED Public (Urban/Road – HPL/SON)

Flickering value (PstLM)	1
Stroboscopic effect	1.6
Photobiological safety according to EN 62471	RG1


### Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	42 W
Lamp current (nom.)	186 mA
Starting time (nom.)	0.45 s
Warm-up time to 60% light	0.45 s
Power Factor (Fraction)	0.95
Voltage (nom.)	220-240 V
Inrush current at mains	6.3
Max. lamp no. on MCB B type 10A — Mains	30
Max. lamp no. on MCB B type 10A — EM ballast without Comp. Cap.	30
Max. lamp no. on MCB B type 10A — EM ballast with Comp. Cap.	7
Max. lamp no. on MCB B type 16A — Mains	48
Max. lamp no. on MCB B type 16A — EM ballast without Comp. Cap.	48
Max. lamp no. on MCB B type 16A — EM ballast with Comp. Cap.	11
Ballast Compatibility	EM/Mains

### Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

### Dimensional drawing



T-Case maximum (nom.)	65 °C
-----------------------	-------

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Lamp Finish	Clear
Bulb shape	Others

### Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	42 kWh
EPREL registration number	403604



### Product Data

Order product name	TForce LED HPL ND 60-42W E27 840
Full product name	TrueForce LED HPL ND 60-42W E27 840
Full EOC	871869963824500
Order code	63824500
Material no. (12 NC)	929002006602
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699638245
Numerator – packs per outer box	6
EAN/UPC – Case	8718699638252

Product	D	C
TForce LED HPL ND 60-42W E27 840	84 mm	178 mm

# TrueForce LED Public (Urban/Road – HPL/SON)

## Photometric data




General uniform lighting - TForce LED HPL ND 60-42W E27 840

Spectral Power Distribution Colour - TForce LED HPL ND 60-42W E27 840




Light Distribution Diagram - TForce LED HPL ND 60-42W E27 840

## Lifetime



Life Expectancy Diagram - TForce LED HPL ND 60-42W E27 840



Lumen Maintenance Diagram - TForce LED HPL ND 60-42W E27 840

## TrueForce LED Public (Urban/Road – HPL/SON)

