



TrueForce LED Public (Urban/Road – HPL/SON)



TrueForce LED HPL ND 60-42W E40 840

Philips TrueForce LED lamps provide an easy LED solution with a fast payback to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. These post-top lamps bring the energy efficiency and long lifetime benefits of LED-to-HID replacement, delivering instant savings for a low initial investment. With the right lamp size and light distribution, customers can easily retrofit TrueForce LED lamps into their existing HPL and SON system, thereby enhancing the light quality with LED HID, without having to change the fixtures or sacrifice the light effect.

Warnings and Safety

- $\cdot \ \text{Installation must always be performed by a qualified electrician or installer}. \ Use the installation guide for instructions$
- Link to Ballast igniter compatibility list https://www.assets.signify.com/is/content/Signify/Assets/philips-lighting/global/HIDLED-EU-compatibility-list-professional.pdf

Product data

General Information		
Cap base	E40	
Nominal lifetime	50,000 h	
Switching Cycle	50,000	
Lighting Technology	LED	
Flux measurement reference	Sphere	
CE mark	Yes	
EU RoHS compliant	Yes	

Light Technical	
Colour Code	840 [CCT of 4000K]
Beam angle (nom.)	360 degree(s)
Luminous Flux	6,000 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	142 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %


Datasheet, 2024, February 16 data subject to change

TrueForce LED Public (Urban/Road - HPL/SON)

Flickering value (PstLM)	1
Stroboscopic effect	1.6
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	42 W
Lamp current (nom.)	186 mA
Starting time (nom.)	0.45 s
Warm-up time to 60% light	0.45 s
Power Factor (Fraction)	0.95
Voltage (nom.)	220-240 V
Inrush current at mains	6.3
Max. lamp no. on MCB B type 10A — Mains	30
Max. lamp no. on MCB B type 10A — EM ballast	30
without Comp. Cap.	
Max. lamp no. on MCB B type 10A $-$ EM ballast	7
with Comp. Cap.	
Max. lamp no. on MCB B type 16A — Mains	48
$\ensuremath{Max}.\ensuremath{lamp}$ no. on MCB B type 16A — EM ballast	48
without Comp. Cap.	
Max. lamp no. on MCB B type 16A — EM ballast	11
with Comp. Cap.	
Ballast Compatibility	EM/Mains
Temperature	
Ambient temperature range	-30 to +45 ℃

T-Case maximum (nom.)	65 ℃
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	Others
Approval and Application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	42 kWh
EPREL registration number	403606
Product Data	
Order product name	TForce LED HPL ND 60-42W E40
	840
Full product name	TrueForce LED HPL ND 60-42W
	E40 840
Full EOC	871869963828300
Order code	63828300
Material no. (12 NC)	929002006802
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699638283
Numerator – packs per outer box	6
EAN/UPC - Case	8718699638290


Dimensional drawing




Product	D	С
TForce LED HPL ND 60-42W E40 840	84 mm	191 mm

TrueForce LED Public (Urban/Road - HPL/SON)


Photometric data






General uniform lighting - TForce LED HPL ND 60-42W E40 840


Spectral Power Distribution Colour - TForce LED HPL ND 60-42W E40 840



Light Distribution Diagram - TForce LED HPL ND 60-42W E40 840

Lifetime





data subject to change

Life Expectancy Diagram - TForce LED HPL ND 60-42W E40 840

Lumen Maintenance Diagram - TForce LED HPL ND 60-42W E40 840

TrueForce LED Public (Urban/Road - HPL/SON)



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.