



T8


44T8HO/COR/96-850/MF54/G/R17d 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data


General Information		Input Frequency	
Cap-Base	R17D [R17d (RDC)]	Power Consumption	44 W
Nominal lifetime	50,000 hour(s)	Lamp Current (Max)	375 mA
Switching Cycle	50,000	Lamp Current (Min)	168 mA
Lighting Technology	LED	Wattage Equivalent	96 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
		Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.9
Color Code	850 [CCT of 5000K]	Voltage (Nom)	120-277 V
Beam Angle (Nom)	240 degree(s)	UL Type	Type B - bypass the ballast
Luminous Flux	5,400 lm	Temperature	
Color Designation	Daylight	Ambient temperature range	-20 °C to 45 °C
Correlated Color Temperature (Nom)	5000 K	T-Case Maximum (Nom)	55 °C
Luminous Efficacy (rated) (Nom)	122.00 lm/W	Controls and Dimming	
Color Consistency	<5	Dimmable	No
Color rendering index (CRI)	82	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Photometric data




Spectral Power Distribution Colour - 44T8HO/COR/96-850/MF54/G/R17d 10/1

Lifetime



Lumen Maintenance Diagram - 44T8HO/COR/96-850/MF54/G/R17d 10/1

Life Expectancy Diagram - 44T8HO/COR/96-850/MF54/G/R17d 10/1




Life Expectancy Diagram - 44T8HO/COR/96-850/MF54/G/R17d 10/1

Life Expectancy Diagram - 44T8HO/COR/96-850/MF54/G/R17d 10/1

T8

Lifetime



Lumen Maintenance Diagram - 44T8HO/COR/96-850/MF54/G/R17d 10/1

