



T8

9.5T8/MAS/48-850/IF16/P/DIM 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data


General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	9.5 W
Nominal lifetime	70,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	120-277, 347 V
Light Technical		UL Type	Type A - works on ballast
Color Code	850 [CCT of 5000K]	Temperature	
Beam Angle (Nom)	180 degree(s)	Ambient temperature range	-20 °C to 55 °C
Luminous Flux	1,600 lm	T-Case Maximum (Nom)	55 °C
Color Designation	Daylight	Controls and Dimming	
Correlated Color Temperature (Nom)	5000 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	168.00 lm/W	Mechanical and Housing	
Color Consistency	<5	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Material	Plastic
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	1,200 mm
Operating and Electrical			
Line Frequency	50 to 60 Hz		

T8

Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	9.5T8/MAS/48-850/IF16/P/DIM 10/1


Full product name	9.5T8/MAS/48-850/IF16/P/DIM 10/1
Order code	474007
Material Nr. (12NC)	929002016104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677474003
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677474008

Dimensional drawing




Product	D1	D2	A1	A2	A3
9.5T8/MAS/48-850/IF16/P/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm

Photometric data




Spectral Power Distribution Colour - 9.5T8/MAS/48-850/IF16/P/DIM 10/1




Light Distribution Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1

Photometric data




General Uniform Lighting - 9.5T8/MAS/48-850/IF16/P/DIM 10/1


Lifetime




Life Expectancy Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1



Life Expectancy Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1



Lumen Maintenance Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1



Life Expectancy Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1

Lifetime



Lumen Maintenance Diagram - 9.5T8/MAS/48-850/IF16/P/DIM 10/1

