



MASTER Value LEDtube T8



MASTER LEDtube VLE 600mm HO 8W 830 T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance – for use in all general lighting, office, industry, retail and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	60,000 h
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Colour Code	830 [CCT of 3000K]
Beam angle (nom.)	190 degree(s)
Luminous Flux	1,000 lm
Colour designation	White (WH)
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	125.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	8 W
Lamp current (max.)	38 mA
Lamp current (min.)	34 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	18 W
Max. lamp no. on MCB B type 10A — Mains	90
Max. lamp no. on MCB B type 10A — EM ballast without Comp. Cap.	180

MASTER Value LEDtube T8

Max. lamp no. on MCB B type 10A — EM ballast with Comp. Cap.	30
Max. lamp no. on MCB B type 16A — Mains	150
Max. lamp no. on MCB B type 16A — EM ballast without Comp. Cap.	290
Max. lamp no. on MCB B type 16A — EM ballast with Comp. Cap.	49

Temperature

Ambient temperature range	-20°C to 45°C
T-Case maximum (nom.)	55 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Product length	600 mm

Approval and Application


Energy Efficiency Class	E
-------------------------	---

Energy-saving product	Yes
Approval marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy consumption kWh/1,000 hours	8 kWh
EPREL registration number	1095862

Product Data



Order product name	MAS LEDtube VLE 600mm HO 8W 830 T8
Full product name	MASTER LEDtube VLE 600mm HO 8W 830 T8
Full EOC	871869964679000
Order code	64679000
Material no. (12 NC)	929002021102
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699646790
Numerator – packs per outer box	10
EAN/UPC - Case	8718699646806

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube VLE 600mm HO 8W 830 T8	25.8 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

Photometric data




General uniform lighting - MAS LEDtube VLE 600mm HO 8W 830 T8

Light Distribution Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8


MASTER Value LEDtube T8

Photometric data




Spectral Power Distribution Colour - MAS LEDtube VLE 600mm HO 8W 830 T8


Lifetime




Lumen Maintenance Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8



Life Expectancy Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8



Life Expectancy Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8



Lumen Maintenance Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8

MASTER Value LEDtube T8

Lifetime



Life Expectancy Diagram - MAS LEDtube VLE 600mm HO 8W 830 T8

