PHILIPS

Lighting



MASTER Value LEDtube T8

MASTER LEDtube VLE 1200mm UO 16W 865 T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance – for use in all general lighting, office, industry, retail, and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	156.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	16 W
Lamp Current (Max)	75 mA
Lamp Current (Min)	68 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C

Controls and Dimming	
Dimmable	No

MASTER Value LEDtube T8


Mechanical and Housing	
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh

Product Data	
Order product name	MAS LEDtube VLE 1200mm UO 16W 865 T8


Full product name	MASTER LEDtube VLE 1200mm UO 16W 865 T8
Full product code	871869964701800
Order code	64701800
Material Nr. (12NC)	929002022202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699647018
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699647025

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube VLE 1200mm UO 16W 865 T8	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




Light Distribution Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8



Spectral Power Distribution Colour - MAS LEDtube VLE 1200mm UO 16W 865 T8


MASTER Value LEDtube T8

Photometric data




General uniform lighting - MAS LEDtube VLE 1200mm UO 16W 865 T8


Lifetime




Lumen Maintenance Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8



Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8




Lumen Maintenance Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8



Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8

MASTER Value LEDtube T8

Lifetime



Life Expectancy Diagram - MAS LEDtube VLE 1200mm UO 16W 865 T8

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.