PHILIPS Lighting

Corepro InstantFit (UL Type-A) T8

10T8/COR/48-830/IF15/G/DIM 10/1

The CorePro InstantFit LED lamps provide hassle-free installation with simple lampfor-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect .Other lamps claim compatibility but only CorePro InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality CorePro InstantFit lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the CorePro InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	70,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	1,500 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	160.00 lm/W


Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	25000-105000 Hz
Input Frequency	25000-105000 Hz
Power Consumption	10 W
Lamp Current (Max)	260 mA
Lamp Current (Min)	100 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9

Corepro InstantFit (UL Type-A) T8

Voltage (Nom)	120-277, 347 V
UL Type	UL Type A
Temperature	
Ambient temperature range	-4 °F to 113 °F
T-Case Maximum (Nom)	122 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	Т8
Approval and Application	
Energy Saving Product	Yes

Approval Marks	RoHS compliance UL certificate DLC
	compliance
Energy Consumption kWh/1000 h	– kWh
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	10T8/COR/48-830/IF15/G/DIM 10/1
Full product name	10T8/COR/48-830/IF15/G/DIM 10/1
Order code	553214
Material Nr. (12NC)	929002252734
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677553210
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677553215

Dimensional drawing




Product D1 D2 A1 A2 A3 10T8/COR/48-830/ 1-1/16 inch 1-1/8 inch 47-3/16 inch 47-1/2 inch 47-3/4 inch IF15/G/DIM 10/1

Photometric data

	1 × TLE	D 10W 3006K 246D 9290032537
		1 x 1930 in.
Frietmanning dagram	Duanity nativation diagram	LGR diagram
200	Top (#8) Televan, UN EX.20	a state
KAX	A CONTRACTOR OF THE	A CONTRACTOR OF CONTRACTOR
1((33))		- AR120
KX 37		
N		
	Distorter ferrer milite	Laminance Table
Street Street	Minima R briefly of artistic desired	<u></u>
Sheek building		
And party of		EFFER
		8188888888
		E CE E E E E E E
	(depend	1244

New Tables 8 V


Accent Lighting Spots - 10T8/COR/48-830/IF15/G/DIM 10/1



Light Distribution Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1


Corepro InstantFit (UL Type-A) T8


Photometric data



Spectral Power Distribution Colour - 10T8/COR/48-830/IF15/G/DIM 10/1

Lifetime





Life Expectancy Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1

Lumen Maintenance Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1

40000

60000

80000

100000

100000

Burning hours

Time (hours)

70

60


50

0

20000

Corepro InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 10T8/COR/48-830/IF15/G/DIM 10/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 20 - data subject to change