



# **T8**

# 10.5T8/MAS/48-850/MF16/P 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

#### **Product data**

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	70,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	850 [CCT of 5000K]			
Beam Angle (Nom)	180 degree(s)			
Luminous Flux	1,650 lm			
Color Designation	Daylight			
Correlated Color Temperature (Nom)	5000 K			
Luminous Efficacy (rated) (Nom)	157.00 lm/W			
Color Consistency	<5			
Color rendering index (CRI)	80			
LLMF At End Of Nominal Lifetime (Nom) 70 %				
Operating and Electrical				
Line Frequency	50 to 60 Hz			


50 to 60 Hz			
10.5 W			
100 mA			
43 mA			
32 W			
0.5 s			
0.7 s			
0.9			
120-277 V			
Type B - bypass the ballast			
-4 °F to 113 °F			
158 °F			
No			
Frosted			

Datasheet, 2023, November 12 data subject to change

Bulb Material	Plastic			
Product Length	47-1/4 inch			
Bulb Shape	Tube, double-ended			
Approval and Application				
Energy Saving Product	Yes			
Approval Marks	RoHS compliance UL certificate DLC			
	compliance			
Energy Consumption kWh/1000 h	- kWh			
Product Data				
Order product name	10 5T8/MAS/48-850/MF16/P 10/1			


Full product name	10.5T8/MAS/48-850/MF16/P 10/1		
Order code	557371		
Material Nr. (12NC)	929002325304		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	046677557379		
Numerator - Packs per outer box	10		
EAN/UPC - Case	50046677557374		

## Dimensional drawing



Product	D1	D2	A1	A2	А3
10.5T8/MAS/48-850/	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch
MF16/P 10/1					

#### Photometric data






Spectral Power Distribution Colour - 10.5T8/MAS/48-850/MF16/P 10/1


General uniform lighting - 10.5T8/MAS/48-850/MF16/P 10/1


#### Photometric data




Light Distribution Diagram - 10.5T8/MAS/48-850/MF16/P 10/1

#### Lifetime






#### Life Expectancy Diagram - 10.5T8/MAS/48-850/MF16/P 10/1



Life Expectancy Diagram - 10.5T8/MAS/48-850/MF16/P 10/1




Lumen Maintenance Diagram - 10.5T8/MAS/48-850/MF16/P 10/1

Life Expectancy Diagram - 10.5T8/MAS/48-850/MF16/P 10/1

3

### Lifetime



Lumen Maintenance Diagram - 10.5T8/MAS/48-850/MF16/P 10/1

