



MASTER LEDtube Mains T5



MASTER LEDtube 1500mm UO 36W 865 T5

The new Philips Master LEDtube Mains T5 brings simplicity to your lighting project. You don't need to pay attention to the driver technology anymore. Thanks to a unique design, Philips MASTER LEDtube Mains T5 installs in luminaires operating on mains power connection. So simple to operate! . Perfectly safe, reliable & easy to install, the Philips MASTER LEDtube Mains T5 is the ideal alternative to standard fluorescent tubes to maximise value over lifetime with high energy savings and lower maintenance costs.

Product data

General Information	
Cap base	G5
Nominal lifetime	50,000 h
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Colour Code	865 [CCT of 6500K]
Beam angle (nom.)	200 degree(s)
Luminous Flux	5,600 lm
Colour designation	Cool Daylight
Correlated Colour Temperature	6500 K
Luminous efficacy (rated) (nom.)	155 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80

LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	36 W
Lamp current (nom.)	160 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V
LED alternative to fluorescent lamp power	80 W
Inrush current at mains	10.1
Max. lamp no. on MCB B type 10A — Mains	21

MASTER LEDtube Mains T5

Max. lamp no. on MCB B type 10A — EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 10A — EM ballast with Comp. Cap.	-
Max. lamp no. on MCB B type 16A — Mains	34
Max. lamp no. on MCB B type 16A — EM ballast without Comp. Cap.	-
Max. lamp no. on MCB B type 16A — EM ballast with Comp. Cap.	-
Ballast Compatibility	Mains

Temperature

Ambient temperature range	-20°C to 45°C
T-Case maximum (nom.)	75 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Product length	1,500 mm
Bulb shape	T5


Approval and Application

Energy Efficiency Class	D
Energy-saving product	Yes
Approval marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy consumption kWh/1,000 hours	36 kWh
EPREL registration number	403648

Product Data

Order product name	MAS LEDtube 1500mm UO 36W 865 T5
Full product name	MASTER LEDtube 1500mm UO 36W 865 T5
Full EOC	871951429054900
Order code	29054900
Material no. (12 NC)	929002475002
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8719514290549
Numerator – packs per outer box	10
EAN/UPC – Case	8719514290556


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm UO 36W 865 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm

MASTER LEDtube Mains T5


Photometric data



General uniform lighting - MAS LEDtube 1500mm UO 36W 865 T5




Spectral Power Distribution Colour - MAS LEDtube 1500mm UO 36W 865 T5




Light Distribution Diagram - MAS LEDtube 1500mm UO 36W 865 T5

Lifetime




Life Expectancy Diagram - MAS LEDtube 1500mm UO 36W 865 T5




Life Expectancy Diagram - MAS LEDtube 1500mm UO 36W 865 T5

MASTER LEDtube Mains T5


Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1500mm UO 36W 865 T5



Lumen Maintenance Diagram - MAS LEDtube 1500mm UO 36W 865 T5



Life Expectancy Diagram - MAS LEDtube 1500mm UO 36W 865 T5

