



Energy Saver GU24

EL/mdTQS 23W GU24


Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Product data

General Information		Lamp Current (Nom)	
Base	GU24 [GU24]		360 mA
Nominal Lifetime (Nom)	10000 h	Warm Up Time to 60% Light (Min)	5 s
Switching Cycle	5000X	Warm Up Time to 60% Light (Max)	40 s
		Power Factor (Nom)	0.55
		Voltage (Nom)	110-127 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Initial lumen (Nom)	1600 lm		
Luminous Flux (Rated) (Nom)	1600 lm	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Max)	2.5 mg
Lumen Maintenance 2000 h (Nom)	85 %	Energy Consumption kWh/1000 h	23 kWh
Lumen Maintenance 5000 h (Nom)	70 %		
Chromaticity Coordinate X (Nom)	459	Product Data	
Chromaticity Coordinate Y (Nom)	412	Order product name	EL/mdTQS 23W GU24
Correlated Color Temperature (Nom)	2700 K	EAN/UPC - Product	046677454210
Luminous Efficacy (rated) (Nom)	67 lm/W	Order code	454215
Color Rendering Index (Nom)	80	Numerator - Quantity Per Pack	1
LLMF At End Of Nominal Lifetime (Nom)	50 %	Numerator - Packs per outer box	6
		Material Nr. (12NC)	929689791501
Operating and Electrical		Net Weight (Piece)	0.086 kg
Input Frequency	50 or 60 Hz		
Power (Rated) (Nom)	23.0 W		

Energy Saver GU24

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQS 23W GU24	61.5 mm	110.0 mm	50.5 mm

TORNADO T2 23W/827 GU24 110-127V 50/60Hz

