# **Downlighting**

# LIGHTOLIER

## Calculite LED 6" gen 3





**C6RDL** Round Downlight

Calculite LED 6" generation 3 provides excellent performance coupled with optimized installation flexibility. Industry leading visual comfort and uniform illumination make it an ideal choice for open office, institution, healthcare, and retail applications.

Buy American Act of 1933 (BAA) Compliant luminaire\*: Complete luminaire = Frame-BAC + Engine-BAC + Trim-BAC

\* BAA compliance requires that BAC option be selected for each of frame, engine, and trim. Frame, engine, and trim will be shipped together as a single product. Accessories (optional) are not currently BAA-compliant.

Frame: Ordered & shipped separately

Project:
Location:
Cat.No:
Туре:
Qty:
Matara

Follow the ordering guidelines below. Each step is a separate order line.

Step 1

	Frame 6R						Example: 6RN	
Step 2	Engine &	Trim: Ordered	d & shipp	ed as a single pro	duct.			
	Engine C6L				-C6R		Example: C6L1593	85MZ10U-C6RDLCCP
Step 3 (optiona	Accessor	ries: Ordered	& shippe	ed separately.				
Frame						Standa	d example: 6RN	BAC example: 6RN-BAC
Series 6R	Installation		Voltag	e/Options				
6R 6" Non-IC Round	N New const	ruction		Universal 120/277/3 Emergency, 6W Sel		Chicago Plenum² Meets the requirer	nents of the Buy Amer	ican Act of 1933 (BAA) <sup>10</sup>
	R Remodeler	•	_	Universal 120/277/3	347V <b>BAC</b> I	Meets the requirer	nents of the Buy Amer	rican Act of 1933 (BAA) <sup>10</sup>
Engine					Standard example: C6L209	930MZ10D20UF	BAC example: Co	6L20930MZ10D20U-BAC
Series C6L	Lumens	CRI/CCT		Beam	Dimming	Options	Voltage	Options
C6L Calculite LED 6"	10 1000 lm 15 1500 lm	927 90CRI/ 930 90CRI/	3000K	N Narrow (40°) M Medium (56°)	<b>Z10</b> 0-10 V 1% <b>Z10-D2O</b> 0-10 V 1% Dim to Off (u)	p to 3500lm)	U 120/277V 3 347V <sup>6</sup> (Z10 only)	F Flex install <sup>7</sup> (no frame required)
gen 3	20 2000lm 25 2500lm 30 3000lm 35 3500lm	935 90CRI/ 940 90CRI/ 950 90CRI/ D2W 90CRI/	4000K 5000K <sup>3</sup>	<b>W</b> Wide (76°)	L01 Lutron PEQO EcoSystem 0.1' L1 Lutron LDE1 EcoSystem (500 RA Integral Interact RF sensor	Im not available)	U 120/277V	R Calculite legacy retrofit - select legacy luminaires <sup>8</sup>
	48 4800 lm* 60 6000 lm*	to 1800 (dim-to-	)K⁴		D DALI 0.1% <sup>6</sup>	None LIN Linear	U 120/277V	BAC Meets the requirements of the Buy American
	* See marked spacings requirements				SOL EldoLED Solo 0-10V 0.1%  DMX Digital Multiplexing  w/RDM 0.1%	None LIN Linear SQR Square	U 120/277V	Act of 1933 (BAA) <sup>10</sup>
	on page 9.				E Forward & Reverse Phase (u	p to 3000lm)	1 120V	1
Trim	•				Stand	dard example: C6	SRDLCCP I BAC e	xample: C6RDLCCP-BAC

See footnotes on page 2.

Series

C6

C6 Calculite

LED 6"

gen 3



CC Comfort clear

CZ Champagne bronze

Comfort clear diffuse

WHAMF White (gloss antimicrobial)

WHAMF White (gloss antimicrobial)





Flange

- White (matte)

- (not applicable)

Polished (matches aperture)

F Flangeless (requires CA6RFT)

F Flangeless (requires CA6RFT)

- White (matches finish)

- White (matches finish)





Options

IEM6 Trim mounted

EM test switch

BAC Meets the requisites of the Buy American

Act of 1933 (BAA)10



CD

Aperture

R Round

R

Style

**DL** Downlight

SL Shower light9

Finish

BK Black (anodized)

CL Specular clear

WH White (matte)

WH White (matte)

# Round Downlight

#### Accessories (Not currently BAA-compliant) learn more below

SWCS Interact Ready System Bridge Accessory (refer to SWCS spec sheet for options and details)

6RNSR 6" round/square non-IC frame for use with Flex (F) light engine (provides mechanical support for rough-in construction only, no junction box)

LCEM6 Field installable Bodine BSL06 emergency battery pack (for Flex (F) light engine only, includes switch mounting plate)

T347-75VA 347:120V step-down transformer for non-IC (N) frame only (see page 3)
7925 Sloped ceiling 6" adapter for 6RN and 6RA frames, specify with flanged

trims only. (refer to SCA spec sheet for slope options)

CA6RFT Mud-in ring for use in 6" round flangeless trim installations

(ordered with a flangeless trim)

CAEM6 Field-installable Bodine BSL6 6W battery pack with self-test/self-diagnostic (for new construction frames, 120-277V - see page 3 for details)

C6RVPWH IP65 Rated vandal proof matte white accessory mounts onto flangeless

trims (C6RDLUF) and new construction frame only **CAEM6TSCP** Emergency test switch mounting plate.

SCP Emergency test switch mounting plate.

Must be ordered with EM6 frame for remote test switch (see page 3)

### **Beam options**

Trim	Nar. engine	Med. engine	Wide engine
Nar. & Med.	20° (0.3 s.c.)	44° (0.7 s.c.)	59° (0.9 s.c.)
Wide	35° (0.6 s.c.)	59° (1.0 s.c.)	69° (1.2 s.c.)

### **Round Downlight**

### Photometric - Downlights with CRI of 90+ & R9 of 50+

Lumen		Flux	Efficacy	Beam				IES	TM-30	D-18	
Package	Beam	(lm)	(lm/W)	Angle	СВСР	CRI	R9	$R_{f}$	$R_g$	R <sub>cs,h1</sub>	UGR
1000 lm	Narrow (N)	989	115	36°	2510	90+	50+	91	100	-5%	0
	Medium (M)	1011	116	57°	1183	90+	50+	91	100	-5%	0
	Wide (W)	942	108	76°	641	90+	50+	91	100	-5%	0
1500 lm	Narrow (N)	1522	119	36°	3863	90+	50+	91	100	-5%	1
	Medium (M)	1530	117	57°	1790	90+	50+	91	100	-5%	1
	Wide (W)	1420	109	76°	965	90+	50+	91	100	-5%	1
2000 lm	Narrow (N)	2075	119	36°	5265	90+	50+	91	100	-5%	2
	Medium (M)	2070	116	57°	2422	90+	50+	91	100	-5%	2
	Wide (W)	1918	107	76°	1304	90+	50+	91	100	-5%	2
2500 lm	Narrow (N)	2511	115	36°	6372	90+	50+	91	100	-5%	3
	Medium (M)	2526	119	57°	2954	90+	50+	91	100	-5%	3
	Wide (W)	2377	112	76°	1616	90+	50+	91	100	-5%	3
3000 lm	Narrow (N)	2927	115	36°	7428	90+	50+	91	100	-5%	4
	Medium (M)	3051	116	57°	3568	90+	50+	91	100	-5%	4
	Wide (W)	2834	107	76°	1926	90+	50+	91	100	-5%	4
3500 lm	Narrow (N)	3333	117	36°	8457	90+	50+	91	100	-5%	4
	Medium (M)	3414	116	57°	3993	90+	50+	91	100	-5%	4
	Wide (W)	3145	107	76°	2138	90+	50+	91	100	-5%	4
4800 lm	Narrow (N)	4491	111	36°	11397	90+	50+	91	100	-5%	5
	Medium (M)	4874	116	57°	5701	90+	50+	91	100	-5%	6
	Wide (W)	4500	107	76°	3059	90+	50+	91	100	-5%	5
6000 lm	Narrow (N)	5529	104	36°	14031	90+	50+	91	100	-5%	6
	Medium (M)	6090	112	57°	7123	90+	50+	91	100	-5%	6
	Wide (W)	5628	103	76°	3825	90+	50+	91	100	-5%	6



# AccuRender Technology (CRI 90+)

The right light brings colors to life. Our new AccuRender technology helps ensure colors are rendered more accurately and consistently, while doing so as efficiently as CRI 80 products.



Standard CRI 80

Good color rendering and high efficacy



Standard CRI 90

Better color rendering and low efficacy



AccuRender

Best color rendering, color preference and high efficacy

### **Enjoy design flexibility**

### Full range of products and options:

- Available soon in across Lightolier portfolio for application flexibility
- Multiple color temperatures (CCTs) and lumen packages offered

### **Promote savings**

## High efficacy, with no penalty:

- Energy efficacy compares well to conventional 80 CRI
- Up to 25% more energy savings vs competitor 90 CRI¹
- · Helps meet Title 24 requirements

### Show your true colors

## High color rendering:

- True to life colors that help energize your environment and render better flesh tones critical for healthcare hospitality and retail applications.
- R<sub>a</sub> up to 94 CRI
   R<sub>f</sub> up to 92 TM-30
   R<sub>g</sub> up to 67 CRI
   R<sub>th1</sub> up to 91 TM-30
   R<sub>g</sub> up to 100 TM-30
   R<sub>g</sub> up to -5% TM-30

### Achieve color balance

## Best in class color consistency:

Promote aesthetic harmony in your space with ≤ 2 SDCM

### Footnotes for page 1

- Emergency (EM6) frame is compatible with reflector mounted test switch when trim is ordered with IEM6 option, DL style trim only (not compatible with 347V configs). For remote mount switch, order standard trim and CAEM6TSCP mounting plate accessory.
- 2. Chicago plenum (LC) frame option not available with BAC nor EM6 options.
- Consult factory for 5000K CCT (50)with narrow (N) beam
- Dim-to-warm (D2W) available only with Z10 dimming up to 2500lm. Narrow (N) and medium (M) beam engines only.
- 5. Linear driver profile (see page 8)
- 6. DALI 4800lm and 6000lm, and all RA options require linear driver configuration (see page 8).
- Flex install option requires light engine & trim only. Up to 3500lm only. Not available with Interact (RA) dimming and IEM6 trim options.

- 8. Retrofits select legacy luminaires (E & Z10 dimming only see pages 2 & 7).
- Non-conductive flush mount lens with pre-installed gasket (matte white non-conductive flange with diffuse lens that is flush with the flange).
- 10. Failure to properly select the "BAC" suffix could result in you receiving product that is not BAA compliant product with no recourse for an RMA or refund. This BAC designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies.

# Round Downlight

### Frame-in-kits

### **New Construction:**

Galvanized stamped steel for dry or plaster ceilings. Preinstalled telescoping mounting bars from 13" to 24". For 4' distances, use 1/2" EMT, 1-1/2" x 1/2" U or C channel.

Max ceiling thickness is 2.75" (70 mm) plenum depth for installation.

#### Patented install Mounting frame:

- Pre-installed mounting bars for fast and toolless installs into T-grid & hat channel ceilings.
- Close-cut aperture design eliminates possibility of gap between ceiling opening and reflector flange.
- Separate wiring compartment for wiring frame to building allows inspection prior to light engine install.
- Simple plug-and-play connection between frame and light engine from below ceiling.

#### Retrofit

 Easily updates legacy Calculite downlights to the latest LED technology. Includes light engine, trim, and driver mounted on cover plate that mounts to junction box of previous Calculite generations. Order with R option code at end of light engine catalog number (see details on page 7).

### Compatibility:

Frames	Engines
With CFL S6132_series	Use Retrofit configuration C6R_ Trim + C6L_ Engine
With INC BS600_series	Use Retrofit configuration C6R_ Trim + C6L_ Engine
With LED C6L_N series C6X6L_N series P6RD_N_ series	Use Retrofit configuration C4R_ Trim + C6L_ Engine C6S_ Trim + C6L_ Engine C6R_ Trim + C6L_ Engine

\* Not available for retrofitting luminaires with integral emergency battery.

## **Emergency**

Bodine BSL6 6W battery pack with self-test/diagnostic functionality. Factory or field mounted to from

- For trim with integral emergency test switch, order trim with IEM6 option (ex: C6RDLCCIEM6).
- For remote ceiling mounted test switch, order standard trim (ex: C6RDLCC). Optional accessory ceiling mounting plate available (CAEM6TSCP) for remote mounted test switch.
- Refer to Calculite-LyteProfile-EasyLyte Emergency Battery Pack specification sheet for more details.

### **Dimming**

All configurations are FCC Class A unless otherwise specified.

- Advance 0-10V 1% (Z10), logarithmic curve is standard. Specify D2O for factory-set dimto-off function, consult factory for linear dimming curve.
- EldoLED SOLODrive (SOL) 0-10v 0.1%
- Lutron PEQ0 (L) Hi-Lume Premier 0.1% EcoSystem
- · Lutron LDE1 (L01) EcoSystem 1%
- Electronic low voltage (E) forward or reverse phase dimming, Remodel and AirSeal IC Shallow are FCC Class B
- DALI (D) DT6 DALI 0.1%
- DMX (DMX) Digital Multiplexing with RDM 0.1%

#### **Dimming Options**

The following are factory-set options for the SOL, D, and DMX driver options (ex. DMXLIN):

- · SOL/D/DMX: Logarithmic (-) standard
- · SOL/D/DMX: Linear (LIN)
- · SOL/DMX: Square (SQR)
- Dim to Warm (D2W): option changes CCT from 3000-1800K gradually as it dims. Use with Z10 dimming only. Fixture-to-fixture consistency of ≤3SDCM at 2700K & 3000K, and ≤5SDCM at 1800K.

### **Optical systems**

### Comfort throughout the space:

True 50° physical cutoff and 45° reflected cutoff.

### Quality of light:

2 SDCM ensures color consistency from fixture to fixture and over the luminaire's long lifetime.

### MesoOptics PET optical diffusion film:

Provides a smooth beam shape and mitigates color over angle with optimized luminaire efficiency. Mitigates LED pixilation.

### **Light Engine**

Quick connect power pack allow for easy installation and replacement from below ceiling with no need for additional wiring. This allows for:

- Frame and ceiling installation to be performed while still finalizing details such as lumen packages, CCT and control type.
- Easy replacement of electronics at end of life with minimal wasted material and labor required.
- · Ease and upgradability of technology.
- 347V light engines are Z10 dimming only and include dedicated 347V driver. For 347V non-Z10 dimming, order T347-75VA field-installed stepdown transformer accessory.

### **Options and Accessories**

Flangeless mud-in ring: Use CA6RFT for use with flangless plaster installations.

**Sloped ceilings:** Compatible with sloped ceiling adapters (see **SCA** spec sheet).

C6RVPWH: includes machined aluminum ring painted white, gasketed for IP65 protection, and impact resistant polycarbonate lens (IK10). Locks in place with discrete setscrew (key included). Available also with antimicrobial fiinsh (C6RVPWHAMF).

CAEM6TSCP: Ceiling cover plate for remote mounted EM6 test switch. 1/2" (25mm) hole, 4 3/8" (109mm) x 2 3/4" (69mm) rectangular. Includes two mounting screws.

Field install EM6 kit with Bodine BSL6 6W battery pack with self-test/self-diagnostic: Includes remote ceiling plate for test switch. To mount test switch to trim for new construction frame, order trim with IEM6 option code (e.g. C6RDLCCIEM6). Refer to Calculite-LyteProfile-EasyLyte Emergency Battery Pack specification sheet for more details.

CAEM6: For use with UniFrame frame in kits.

LCEM6: For use with Flex intall (F) light engines.

**SWCS:** Interact Ready System Bridge Accessory. Requires IRT9015 IR remote and Interact Pro App for commissioning.

**T347-75VA:** Field installable 347:120V 75VA stepdown transformer, attaches to knock out on frame junction box, for use with non-IC (N) frames. Not for use with emergency options.

### Title 24 exceptions

- 1000lm configurations
- Champagne Bronze & Black finishes

### **Labels and Listings**

- cULus listed for wet locations
- RoHS certified
- CEC Title 24 JA8 certified
- CCEA (frames with \*LC suffix)
- IP65 rated with vandal proof accessory
- Red List Declare label certified, ID SIG-0017 (<u>View full Declare label</u>)

### Warranty



5 year limited warranty

Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty on complete luminaire systems.

# Round Downlight

# interact


THUCH GOU				
			Gatev	vay Connected
		Standalone	Option 1	Option 2
Dimming, grouping, and zoning		<b>~</b>	<b>✓</b>	<b>~</b>
Bluetooth and ZigBee enabled		<b>✓</b>	<b>✓</b>	<b>~</b>
Motion sensing and daylight harvesting		<b>✓</b>	<b>✓</b>	<b>~</b>
Integration with 0-10V and phase dimming fixtures		<b>~</b>	<b>✓</b>	<b>~</b>
Code compliance		<b>~</b>	<b>✓</b>	<b>~</b>
Granular dimming and dwell time		<b>✓</b>	<b>✓</b>	<b>~</b>
Correlated color temperature (CCT) tuning by switch	New	<b>✓</b>	<b>✓</b>	<b>~</b>
Support for sensor-based Tunable White luminaires	New	<b>✓</b>	<b>✓</b>	<b>~</b>
Energy reporting and monitoring			<b>✓</b>	<b>~</b>
Scheduling			<b>✓</b>	<b>~</b>
Demand response			<b>✓</b>	<b>~</b>
BMS integration (BACnet)				<b>~</b>
Floor plan visualization				<b>~</b>
IoT sensors for wellness				<b>~</b>
IoT Apps for productivity				<b>~</b>

### Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.

System level	
Total number of gateways	Unlimited
Total number of devices	200 per network
Luminaires with integrated sensors	150
Smart TLEDS	150
· Zones + groups	64
Total number of ZGP devices (sensors and switches)	50
Sensors	30
· Switches	50

Group level	
Recommended number of lights	40 (maximum 150)
Number of ZGP devices	5
Number of scenes	16



dillatin

# Round Downlight

### Wireless controls options

### Interact

- SWZCS is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the standalone mode (similar to SpaceWise) when configured without a gateway or in a cloud connected mode if a compatible gateway is used.
- Interact includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & BlueTooth connectivity.
   The App provides flexibility to choose between a gateway or non gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote on-site to identify and group devices together.

### Compatible with:

- SWS200 & UID8465 wireless scene switch
- Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
- Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
- LCN3110: battery powered IP65 presence sensor, OCC sensor IA CM IP65W
- LCN3120: battery powered IP65 presence & daylight sensor, OCC-DL sensor IA CM IP65 WH
- For more information on Interact visit: interact-lighting.com/interactproscalablesystem

### Radio only sensor (RA or RADIO)

- Integral RA or RADIO only sensor simply enables wireless mesh connectivity to the luminaire without any occupancy or daylight sensing.
- Ideal for applications where sensing functionality is managed by other Interact devices and the luminaire only needs to have wireless connectivity.
- Interact includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & Bluetooth connectivity.
   The App provides flexibility to choose between a gateway or non-gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely, identify and group devices together onsite.
- Compatible with SWS200 and UID8465 wireless scene switch, wireless Occ sensor (OCC SENSOR IA CM IP42 WH 10/1) and wireless Day/Occ sensor (OCC MULTI SENSOR IA CM WH 10/1).
- For more information on Interact visit: interact-lighting.com/interactproscalablesystem

### Sensor bundle (IAOSB or SB)

- A wireless IoT connected lighting solution for large enterprises that span across multiple floors, buildings and require multiple gateways.
- View all your projects under one dashboard and easily compare insights from multiple projects in one view.
- Compatible with SWS200 wireless scene switch, wireless Occ sensor (OCC SENSORIA CM IP42 WH 10/1) and wireless Day/Occ sensor (OCC MULTI SENSOR IA CM WH 10/1) and wireless Occupancy or Daylight & Occupancy sensors available. Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- IAOSB or SB option in addition to occupancy and daylights sensing supports advanced IoT capabilities, such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- Requires compatible Gateway and internet connectivity for commissioning.
- For more information, visit: interact-lighting.com/interactproscalablesystem

### **Emergency Options (ER100)**

- Power Sensing (factory default) –
  Recommended UL924 option requires unswitched
  power sense line, absence of voltage on the
  normal circuit triggers luminaire to 100% output.
- Power Interruption Detection (field option) –
  Detects AC power interruption >30ms triggers
  90 minute emergency mode with luminaire at
  100% output.

## Interact supported sensor option codes across Genlyte product lines

	Evokit	Day-Brite	Ledalite	Lightolier
ZigBee + Bluetooth + Sensing	SWZCS	SWZCS	CS	SBA accessory (external)
ZigBee + Bluetooth	RADIO	RADIO	RA	RA
ZigBee + Bluetooth + Sensing + Environmental data	IAOSB	IAOSB	SB	SB
ZigBee + Highbay + Sensing	-	SWZCSH	-	-

# Round Downlight

### **Polished Reflectors**



Specular clear (CL): Most specular and most efficient finish, delivers maximum photometric performance but can produce a mirror image effect of the interior space.



Comfort clear (CC): Semi-specular finish that softens the light at the source of the reflector and creates a subtle, even luminance from the reflector cone.



Comfort clear diffuse (CD): Slightly diffuse clear finish, that eliminates iridescence and reduces the mirror image effect inherent with specular finishes.



Vandal proof (VP): Provides an elegant solution for vandal resistant needs. One piece machined aluminum ring with impact resistant clear lens. Flangeless (F) flange must be ordered. Provides the luminaire with an IK10 impact and IP65 rating



Champagne bronze (CZ): Semi-specular finish that softens light at the source of the reflector while providing a warmer reflector appearance (slightly warmer).



White (WH): (matte) Brightest illuminated aperture and provides the smoothest transition to most ceilings when off (white is only available with a white flange).



Black (BK): (anodized) Specular finish that provides the lowest aperture brightness possible and significantly reduces source identification in a ceiling.



Shower light (SL): Wet location rated shower light with clear acrylic lens applicable in any installation requiring dead front trims, interior or exterior non-corrosive applications, or where a diffused lens at the ceiling is required (non-conductive).

### **Flanges**




White (-): (matte) Provides the smoothest transition to ceilings when off.



**Polished (P):** (matches aperture) Produces a continuous look throughout the reflector (aperture matching).



Flangeless (F): (flush-mount)Creates a flush, virtually seamless transition from aperture to ceiling.



Mud-in ring (FT): Low profile, machined aluminum mud-in ring provides a raised rib to plaster up to and a 3/16" flange thickness. The ring is attached to the ceiling material as opposed to the frame-in kit to avoid conduction of heat and vibration which can cause yellowing or cracking of the plaster.

non-IC frame.

23/4 in

70 mm

Maximum ceiling thickness

(<del>-</del>)


Ceiling Cutout

ø6¾in 162mm

# Round Downlight

## **New Construction (N) Emergency battery** 12% in 314 mm EM6 option on new construction non-IC frame. 81/2 in 209 mm 10%in 257mm 10%in 264 mm (1) .13%in 346 mm Center point location for integral emergency test switch (IEM6) 6RN-NJB has the **Emergency battery** pack shown with same dimensions (no junction box) EM6 option on new construction


### Chicago Plenum (LC)



## Remodeler (R)

(85 mm)

6%in 161mm





ø6in

ø7%in \_ 184mm


152 mm

# Flangeless mud-in ring (CA6RFT) accessory







### Retrofit (R) with round trim



## Vandal Proof (VP) accessory




# Round Downlight




& 6000lm, & RA light engines.


Sensor shown for RA light engine only.


## Flex Install (F)






### LCEM6 Flex install (F) engine only





connector to j-box knock out

## 6RNSR Flex install non-IC frame



Α	В	C	D	E	F
13 ¼"	9 5/8"	13 %"	1½"	6¾"	5¾"
334mm	244mm	345mm	37mm	162mm	169mm

# Round Downlight

### **Electrical - Narrow**

Light	Input	Input	Input	Drive	Input	LED	THD Factor	Power Factor
engine	Volts	Freq.		Current	Power	Power	@ Max	Load
	120V	50/60Hz	0.072A	0.22A	8.6W	7.0W	<10%	>0.9
1000lm	277V	50/60Hz	0.032A	0.22A	8.8W	7.0W	<20%	>0.9
	347V	50/60Hz	0.029A	0.22A	10.0W	7.0W	<30%	>0.9
	120V	50/60Hz	0.107A	0.33A	12.8W	10.7W	<10%	>0.9
1500lm	277V	50/60Hz	0.046A	0.33A	12.9W	10.7W	<10%	>0.9
	347V	50/60Hz	0.042A	0.33A	14.6W	10.7W	<25%	>0.9
	120V	50/60Hz	0.145A	0.45A	17.4W	14.7W	<10%	>0.9
2000lm	277V	50/60Hz	0.063A	0.45A	17.5W	14.7W	<10%	>0.9
	347V	50/60Hz	0.056A	0.45A	19.4W	14.7W	<20%	>0.9
	120V	50/60Hz	0.178A	0.55A	21.4W	18.2W	<10%	>0.9
2500lm	277V	50/60Hz	0.078A	0.55A	21.5W	18.2W	<10%	>0.9
	347V	50/60Hz	0.065A	0.55A	22.7W	18.2W	<20%	>0.9
	120V	50/60Hz	0.212A	0.65A	25.5W	21.7W	<10%	>0.9
3000lm	277V	50/60Hz	0.091A	0.65A	25.3W	21.7W	<10%	>0.9
	347V	50/60Hz	0.077A	0.65A	26.7W	21.7W	<15%	>0.9
	120V	50/60Hz	0.237A	0.75A	28.4W	24.4W	<10%	>0.9
3500 lm	277V	50/60Hz	0.103A	0.75A	28.4W	24.4W	<10%	>0.9
	347V	50/60Hz	0.084A	0.75A	29.1W	24.4W	<15%	>0.9
	120V	50/60Hz	0.338A	1.05A	40.5W	34.9W	<10%	>0.9
4800lm	277V	50/60Hz	0.145A	1.05A	40.3W	34.9W	<10%	>0.9
	347V	50/60Hz	0.118A	1.05A	41.0W	34.9W	<10%	>0.9
	120V	50/60Hz	0.442A	1.35A	53.0W	45.6W	<10%	>0.9
6000lm	277V	50/60Hz	0.188A	1.35A	52.1W	45.6W	<10%	>0.9
	347V	50/60Hz	0.153A	1.35A	53.0W	45.6W	<10%	>0.9

### Lifetime (TM-21) data


Lumens	Narrow beam	Medium/Wide beam		
1000lm 1500lm 2000lm 2500lm 3500lm*	L90 @ 60,000hrs.	L90 @ 60,000hrs.		
4800lm 6000lm	L90 @ 60.000hrs.	L80 @ 60.000hrs.		

<sup>\*</sup> Lutron 3500lm with Medium/Wide beam is L85 @ 60,000hrs.

### **Electrical - Medium & Wide**

Liabt	Input	lmmust	Input	Drive	Input	LED	THD Factor	Power Factor
Light engine	Volts	Input Freq.	Current			Power	@ Max Load	
	120V	50/60Hz	0.073A	0.22A	8.7W	7.1W	<10%	>0.9
1000lm	277V	50/60Hz	0.032A	0.22A	8.9W	7.1W	<20%	>0.9
	347V	50/60Hz	0.029A	0.22A	10.2W	7.1W	<30%	>0.9
	120V	50/60Hz	0.109A	0.33A	13.0W	10.9W	<10%	>0.9
1500lm	277V	50/60Hz	0.047A	0.33A	13.1W	10.9W	<10%	>0.9
	347V	50/60Hz	0.043A	0.33A	14.9W	10.9W	<25%	>0.9
	120V	50/60Hz	0.149A	0.45A	17.8W	15.1W	<10%	>0.9
2000lm	277V	50/60Hz	0.065A	0.45A	18.0W	15.1W	<10%	>0.9
	347V	50/60Hz	0.057A	0.45A	19.8W	15.1W	<20%	>0.9
	120V	50/60Hz	0.179A	0.55A	21.4W	18.2W	<10%	>0.9
2500lm	277V	50/60Hz	0.078A	0.55A	21.6W	18.2W	<10%	>0.9
	347V	50/60Hz	0.066A	0.55A	22.8W	18.2W	<20%	>0.9
	120V	50/60Hz	0.220A	0.67A	26.4W	22.4W	<10%	>0.9
3000lm	277V	50/60Hz	0.095A	0.67A	26.2W	22.4W	<10%	>0.9
	347V	50/60Hz	0.079A	0.67A	27.5W	22.4W	<15%	>0.9
	120V	50/60Hz	0.245A	0.75A	29.4W	25.3W	<10%	>0.9
3500 lm	277V	50/60Hz	0.106A	0.75A	29.4W	25.3W	<10%	>0.9
	347V	50/60Hz	0.087A	0.75A	30.1W	25.3W	<15%	>0.9
-	120V	50/60Hz	0.350A	1.08A	42.0W	36.1W	<10%	>0.9
4800lm	277V	50/60Hz	0.150A	1.08A	41.5W	36.1W	<10%	>0.9
	347V	50/60Hz	0.122A	1.08A	42.5W	36.1W	<10%	>0.9
	120V	50/60Hz	0.454A	1.38A	54.5W	46.8W	<10%	>0.9
6000lm	277V	50/60Hz	0.193A	1.38A	53.5W	46.8W	<10%	>0.9
	347V	50/60Hz	0.157A	1.38A	54.5W	46.8W	<10%	>0.9

## Dim-to-Warm: CCT vs Dimmed level



# Marked spacing applications

Light engine	4800lm	6000lm
C6L_Z10 series	Х	Х
C6L_L01 series	Х	Х
C6L_L1 series	Х	Х
C6L_LD series	Х	Х

Light engine	4800lm	6000lm
C6L_LTE series	Х	Х
C6L_D series	Х	Х
C6L_DMX series	Х	Х
C6L_RA series	Х	Х

Modules marked with an X require marked spacing:


- Center-to-center of adjacent luminaires: 24" (610mm)
- Luminaire center to side building member: 12" (305mm)

In accordance with CAN ICES-005-A/ NEB-005-A and FCC Part 15-A.

# Round Downlight

### Narrow beam, 2500lm Engine, 115 lm/W at 22W

### Candela Curve



# 6RN / C6L25935NZ10U /

Output lumens: 2512 Ims 21.8 W Input watts: 90 min CCT 1. 3500K Spacing Crit.: 0.6 Beam Angle:

### Zonal summary

Zone	Lumens	%Luminaire
0-30	2231	88.8%
0-40	2423	96.5%
0-60	2510	99.9%
0-90	2512	100.0%

Angle	Mean CP	Lumens
0	6372	
5	6006	
10	4997	540
15	3915	
20	2643	1066
25	1335	
30	514	625
35	286	
40	222	192
45	107	
50	12	83
55	4	
60	2	4
65	1	
70	1	1
75	1	
80	0	0
85	0	
90	0	0

### Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
8'	100	4.8'
9'	79	5.4'
10'	64	6.0'
12'	44	6.6'
14'	33	8.4'

<sup>\*</sup> Beam diameter is where foot-candles drop to 50% of maximum

### Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	118.0	0.97
6'	77.0	0.63
7'	55.0	0.45
8'	46.0	0.38
9'	37.0	0.30
001 001 401		

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Efficacy: 115.2 lm/W STMR-1590.2

#### Adjustment factors


Finish	CCT	Lumens
CL = 100% CC = 95% CD = 87% CZ = 63% WH = 87% BK = 57%	90CRI, 4000K = 102% 90CRI, 3500K = 100% 90CRI, 3000K = 96% 90CRI, 2700K = 92%	6000lm = 240% 4800lm = 192% 3500lm = 140% 3000lm = 120% 2500lm = 100% 2000lm = 80% 1500lm = 60% 1000lm = 40%

### Coefficients of utilization

Ceili	ng		80	)%		70	1%	50	)%	30	)%	0%
Wall		70	50	30	10	50	10	50	10	50	10	0
RCR Zonal cavity method - Effec			ectiv	e floo	r refl	ectar	nce =	20%				
Room Cavity Ratio	0 1 2 3 4 5	119 114 110 106 102 98 94	119 112 106 100 95 91 87	119 110 102 96 91 86 82	119 108 100 93 87 83 78	116 110 104 99 94 90 86	116 106 99 92 87 82 78	111 106 101 96 92 88 85	111 103 96 91 86 82 78	106 102 98 94 90 87 83	106 100 94 89 85 81 77	100 95 91 87 83 79 75
	7 8 9	91 87 84 81	83 80 76 74	78 75 72 69	75 71 68 66	82 79 76 73	75 71 68 66	81 78 75 72	74 71 68 65	80 77 74 72	74 71 68 65	72 69 67 64

## Medium beam, 2500lm Engine, 119 lm/W at 21W

### Candela Curve



#### 6RN / C6L25935MZ10U / C6RDLCL

Output lumens: Input watts: CRI: 21.3 W 90 min Spacing Crit.: 0.96 Beam Angle:

#### Zonal summary

Zone	Lumens	%Luminaire
0-30	1994	78.9%
0-40	2410	95.4%
0-60	2524	99.9%
0-90	2527	100.0%

Angle	Mean CP	Lumens
0	2954	
5	2968	
10	2965	283
15	2929	
20	2620	811
25	2022	
30	1240	900
35	628	
40	322	416
45	137	
50	15	110
55	4	
60	2	4
65	1	
70	1	1
75	0	
80	0	0
85	0	
90	0	0

#### Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	118	4.8'
6'	82	5.8'
7'	60	6.7'
8'	46	7.7'
9'	36	8.6'

<sup>\*</sup> Beam diameter is where foot-candles drop to 50% of maximum.

### Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.					
5'	116.0	0.94					
6'	76.0	0.62					
7'	54.0	0.44					
8'	45.0	0.37					
9'	36.0	0.30					
20' v 20' v 10' Boom Workplane 2 E'							

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Efficacy: 118.6 lm/W Report2: STMR-2437

#### Adjustment factors

Finish	ССТ	Lumens		
CL = 100% CC = 95% CD = 87% CZ = 63% WH = 87% BK = 57%	90CRI, 4000K = 102% 90CRI, 3500K = 100% 90CRI, 3000K = 96% 90CRI, 2700K = 92%	6000lm = 240% 4800lm = 192% 3500lm = 140% 3000lm = 120% 2500lm = 100% 2000lm = 80% 1500lm = 60% 1000lm = 40%		

### Coefficients of utilization

Ceiling			80	)%		70	1%	50	)%	30	)%	0%
Wa	I	70	50	30	10	50	10	50	10	50	10	0
RCR		Zona	al cav	ity me	ethod	l – Eff	ectiv	e floo	r refl	ectar	ice =	20%
	0	119	119	119	119	116	116	111	111	106	106	100
0	1	114	111	109	107	109	105	105	102	101	99	94
Ratio	2	109	104	100	97	102	96	99	94	96	92	88
æ	3	103	97	93	89	96	88	93	87	91	85	83
ΞΞ	4	99	91	86	82	90	82	88	81	86	80	77
e S	5	94	86	81	76	85	76	83	75	82	75	73
Room Cavity	6	90	81	75	71	80	71	79	71	77	70	68
Ö	7	85	77	71	67	76	67	75	66	73	66	64
8	8	81	72	67	63	72	63	71	62	70	62	61
	9	78	69	63	59	68	59	67	59	66	59	57
	10	74	65	60	56	65	56	64	56	63	56	54


<sup>1.</sup> Correlated Color Temperature within specs as defined in ANSI\_NEMA\_ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.

<sup>2.</sup> Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

# Round Downlight

### Wide beam, 2500lm Engine, 112 lm/W at 21W

### Candela Curve



# 6RN / C6L25935WZ10U /

Output lumens:	2378 lms
Input watts:	21.3 W
CRI:	90 min
CCT1:	3500K
Spacing Crit.:	1.3
Beam Angle:	76°

#### Zonal summary

Zone	Lumens	%Luminaire
0-30 0-40 0-60 0-90	1420 2131 2376 2378	59.7% 89.6% 99.9% 100.0%

Angle	Mean CP	Lumens
	4040	
0 5	1616	
	1642	
10	1705	159
15	1780	
20	1762	501
25	1665	
30	1478	760
35	1160	
40	758	711
45	277	
50	25	238
55	7	
60	3	7
65	2	
70	1	2
75	1	
80	0	1
85	0 0 0	
90	0	0

### Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*			
5'	65	6.5'			
6'	45	7.8'			
7'	33	9.1'			
8'	25	10.4'			
9'	20	11.7'			

<sup>\*</sup> Beam diameter is where foot-candles drop to 50% of maximum.

### Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	107.0	0.94
6'	70.0	0.62
7'	50.0	0.44
8'	42.0	0.37
9'	34.0	0.30
		,

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Efficacy: 111.6 lm/W Report<sup>2</sup>: STMR-2438

#### Adjustment factors

Finish	CCT	Lumens
CL = 100% CC = 95% CD = 87% CZ = 63% WH = 87% BK = 57%	90CRI, 4000K = 102% 90CRI, 3500K = 100% 90CRI, 3000K = 96% 90CRI, 2700K = 92%	6000lm = 240% 4800lm = 192% 3500lm = 140% 3000lm = 120% 2500lm = 100% 2000lm = 80% 1500lm = 60% 1000lm = 40%

### Coefficients of utilization

Ceiling		80%		70%		50%		30%		0%		
Wa	II	70	50	30	10	50	10	50	10	50	10	0
RCR		Zona	al cav	ity me	ethod	- Eff	ectiv	e floo	r refl	ectar	ice =	20%
	0	119	119	119	119	116	116	111	111	106	106	100
0	1	113	110	108	105	108	104	104	100	100	97	93
Ě	2	107	102	98	94	100	93	97	91	94	89	85
20	3	101	94	89	85	93	84	90	83	88	81	78
Room Cavity Ratio	4	95	87	81	77	86	76	84	75	82	75	72
a	5	90	81	75	70	80	70	78	69	76	69	66
Ö	6	85	75	69	64	74	64	73	64	71	63	61
οū	7	80	70	64	59	69	59	68	59	67	58	56
8	8	76	65	59	54	65	54	64	54	63	54	52
	9	72	61	55	50	61	50	60	50	59	50	48
	10	68	57	51	47	57	47	56	47	55	46	45



<sup>1.</sup> Correlated Color Temperature within specs as defined in ANSI\_NEMA\_ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products. 2. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.