J.



Installation Instructions & Template for Halo 5" Remodel Housing

Using template, scribe circle on ceiling in desired location. Accurately cut hole in calling. Step 2 Provide electrical service with flexible cable only. Pass cable through opening and wire lixture in accordance with NEC or your local electrical code. (See back for wiring diagram). Connect supply wines to socket leads. Twist black supply consect supply winds to social reduct twice to black thermal protector were and white supply wire to white transformer load. To insulate connection, place wire nut connector (not included) over the twisted group of white wres and Egisten. Repost the same procedure with the black wires. Connect ground copper wire from wining box to green ground wire from electrical service. Splice ground wires FIG 1 FIG 2 together. Follow procedure in Slep 4 above for splicing wires together. With clips seated properly inside can (Figure 1) insert remodel housing into ceiling junction box first. To install To Install Hold ficture up against ceiling and push dip through housing sict (Figure 2). FIG 3 To lock clip in place, push flat portion against side of carr (Figure 2). To release, pull down on clip (Figure 3). Stee 9 Step 10 Install frim. Use only Helo Trims (sold separately) NOTE. In areas where excessive ceiling vibration can occur, we To Remove suggest you use a 1/4-14x1/2" pan HO sheet metal scre to further lock the spring clips against the fixture housing. Drive the screw through the hole in the spring clip and into the housing slot.

