Installation Guide

- Philips TrueForce LED Road Lamp

Please take the time to read this installation guide. The guide contains important information

and notes regarding the installation and operation.

IMPORTANT!

- · The product works ONLY with an existing ElectroMagnetic (EM) gear (refer to TrueForce LED lamps ballast - igniter compatibility list). No need to rewire or modify the luminaire, ignitor can stay in the system.
- The product is designed to fit in standard IEC compliant E40 lamp holders.
- Always switch off the power supply before commencing work!
 Please read the installation instructions carefully to ensure safety.
- · The product is not dimmable.
- · The product is not compatible with electronic gear.
- · The product DOES NOT work on Direct Mains.
- Suitable for use in operating temperature range between -40°C to +45°C.
- Do not change the structure or any components of the product to ensure safety.
- · The product should be installed by professional electrician.
- · Perform inspection before installation to ensure the luminaire and lamp holder are in good condition
- to carry the weight and performance of the product. • The product fulfills IP40 requirements, outdoor applications require the lamp to be used in luminaires
- with suitable IP rating.
- · Please do not apply the product in applications which contains emergency or/and explosive proof luminaires. The total system performance may vary depending on the lighting/luminaire system.
- · For latest information, please refer to www.philips.com/lighting.
- \cdot In case of doubt, please consult Philips representative. · The minimum dimensions requirement on lamp compartment is $(L \times Ø)$ 280mmX180mm. Please
- check the Tc temperature in application guide for best performance. • Do not install any lamp which is deformed or damaged from transportation or handling.
- · Compatible with EM ballasts 50Hz only.
- · Keep lamps clear during application (esp. no oil contamination on glass tube), to ensure good lamp performance.

DISCLAIMER:

Signify disclaims liability for any direct, indirect or incidental damages in case of installation performed either not according to this guide or not performed by a professional electrician.

CE RoHS IP40



PHILIPS



All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights. 12/2018 www.philips.com/lighting

3241 654 16801

brand Philips								
Product Family LED tube ND								
Shape								
Wattage								
Template Ref. <u>NA</u>								
SGS number 5609521								
12-NC.NBR <u>324165416801</u>								
Masterdrawing <u>NA</u>								
CRC Ref								
Barcode No. NA								
Operator(s) <u>pollypan</u>								
VERSION No. V1								
Date in <u>20150514</u>								
Date amended <u>20181210</u>								
Black Diecut								
Date Check								
Check briefing Traffic								
Artwork document								
Legend Number of colors								
12NC Trapping/Bleed								
Barcode Images hires								
Diecut Jobsizes								
Approval								
QC Lithographer SGS Shanghai Production								
Product Manager <u>connie.lh.fan@signify.com</u>								
Traffic Manager <u>Neal Yan</u>								

PHILIPS LIGHTING

Size: 148 * 210mm 80g 双胶纸, double side prin

Γ	Code 12NC:	Designer: SH SGS		Duplexbox: 324165416801		Author	Date	Change number	Revision description
Lafa Lafa	324165416801	Design date: 2018-12-12	fo	EANI number: NA	Info	SH SGS	2018/12/12		
t t	Description:		sic In	Die-Cut: NA	ange li				
			Ba	Surface treatment: N/A	Cha				
				CRC:					

PCC - SHANGHAI A4 DOCUMENT TYPE:114



SON/HPL lamps with EM gear





SYMBOL	MEANING
	LAMP SUITABLE FOR 50Hz OR 60Hz OPERATION
×	NEED TO BE USED IN DRY CONDITIONS OR IN A LUMINAIRE THAT PROVIDES PROTECTION

© 2018 Signify Holding (s)ignify