



PAR30 lamps do not require socket extender. Long neck  
PAR30 lamps are not compatible with the 1029 series trims.

Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets						
1000P1	Open Downlight						Enclosed Diffusers
	Reflector	Cone	Baffles	Basic White	Pinhole	Eyeball	
	1046 1046CD	1013 1013WH	1005 1005WH 1076 1076WH	1071	1011	1082	
							1024 1078

## Features

- Housing:** .026" galvanized steel. Access door for inspection of junction box.
- Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Four slots are positioned 90° apart to simplify alignment. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 4" X 3 1/2" X 2" (22 cu. in.) .063" (#14 ga.) galvanized steel. U.L. listed for maximum of 8 No. 12 ga. 75° C through branch circuit conductors (60° C end of run). Integral cable clamps permit attachment of non-metallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** .059" (#16 ga.) galvanized steel. 13" long bars extend to 27", rotatable and lockable, with integral T-bar tabs. Attach to wood joist or T-bar ceilings without the need of accessories.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Insulation must be kept 3" away from fixture sides and wiring compartments and must not be placed above fixture in a manner which will entrap heat. Located inside housing.

## Options & Accessories

- Mounting Bars:** 1964 - 20" set of (2)  
**Extra-Thick Ceiling Mounting Ring:** 1967B - up to 2" thick ceilings.

## Labels

UL (Suitable for Damp Locations), I.B.E.W.  
Romex® is a registered Trademark of General Cable Industries Inc.

