


Ceiling Opening: 5 3/8" Diameter



Top View



REFLECTOR TRIM

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Frame-In Kit

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

1004SICR	Open Downlight					Wall Washer	Enclosed Diffuser	
	Specular	Cone	Satin Cone	Baffles	Basic White			
	1012		1008	1005	1071	1085*	1024*	
	1012NM		1008NM	1005WH				
	1013		1010	1005NM				
	1013BK		1010NM	1005BNM				
	1013WH			1076				
	1013CD			1076WH				
	1013NM							
	1013BKNM							
	1013CDNM							

*For Non-IC applications only

Features

- Housing:** .032" (#20 ga.) Aluminum. UL listed convertible IC/NON-IC. Integral retaining spring secures housing to ceilings up to 2" thick. Removable for access to junction box and ceiling plenum. 5 1/2" tall for use in 2" X 6" joist construction and shallow plenum applications.
- Junction Box:** 2 1/2" X 2 1/2" X 3 1/2" (21 cu. in.) .032" (#22 ga.) galvanized steel. UL listed for 90°C supply wire. Suitable for branch circuit wiring supplying connected fixtures. Integral cable clamps permit attachment of non-metallic (#12 or #14 ga.) Romex® cable without tools or additional connectors.
- Socket Housing:** Impact extruded aluminum or galvanized steel. Attached trim retaining spring secures trim to any height on housing wall.

- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 (300 Volt 200°C) leads to junction box.

- Thermal Protector:** Meets NEC and U.L. requirements. Located inside housing

Options & Accessories

AirSeal® Kit: LAS56R (required for AirSeal Installation)

Labels

UL (Type IC/NON-IC Convertible, Suitable for Damp Locations)

Complies with Air Leakage Requirements stated in the Model Energy Code and the Washington State Energy Code.

Romex® is a registered trademark of General Cable Industries Inc.

