



**Domus 50** is one of the most versatile luminaires offered by Lumecc. This classic shape was one of the first in a line of pioneering Lumecc designs. **Domus** offers a subtly refined design that balances shape, dimension and proportion.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide

example: DMS50-35W32LED3K-G3-ACDR-LE2A-UNV-DMG-MA1-RCD-PH8-BKTX

Series	LED module	CCT	Gen	Optical system	Voltage	Driver	Adaptors
<b>DMS50</b>			<b>G3</b>				
DMS50 Domus	35W32LED 55W32LED 55W48LED 70W64LED 72W32LED 80W48LED 90W80LED 108W48LED 110W64LED 135W80LED 145W64LED 180W80LED	2.2K <sup>7</sup> 2200K 3K 3000K 4K 4000K	G3	<b>Globe</b> <hr/> <b>ACRD-LE2A</b> Type II (ASYM) with acrylic globe <b>ACRD-LE3A</b> Type III (ASYM) with acrylic globe <b>ACRD-LE4A</b> Type IV (ASYM) with acrylic globe <hr/> <b>Sag lens</b> <hr/> <b>LE2S</b> Type II (ASYM) Sag glass lens <b>LE3S</b> Type III (ASYM) Sag glass lens <b>LE4S</b> Type IV (ASYM) Sag glass lens <b>LE5S</b> Type V (SYMM) Sag glass lens <hr/> <b>Flat lens</b> <hr/> <b>LE2F</b> Type II (ASYM) Flat glass lens <b>LE3F</b> Type III (ASYM) Flat glass lens <b>LE4F</b> Type IV (ASYM) Flat glass lens <b>LE5F</b> Type V (SYMM) Flat glass lens	UNV 120V-277V 347 347V 480 480V	DMG 0-10V DALI <sup>2</sup> Pre-set, compatible with the DALI control system SRD <sup>2</sup> Sensor ready driver, standard configuration SRD1 <sup>2</sup> Sensor ready driver, alternate configuration	MA1 1¼" NPT threaded hole adaptor MA2 1½" NPT threaded hole adaptor SMA <sup>5</sup> Decorative retro side-mounted cast-aluminum, accepts tubes from 1½" to 2¾" SMB Decorative contemporary side-mounted cast-aluminum, accepts tubes from 1½" to 2¾"

Options				
Recepticle	Control	Luminaire	Poles & Brackets	Finish
<b>RC</b> <sup>1,4</sup> Receptacle for twist-lock photocell or shorting cap, 3-pin <b>RCD</b> <sup>1,4,7</sup> Receptacle for twist-lock photocell or shorting cap, 5-pin <b>RCD7</b> <sup>1,4,6</sup> Receptacle for twist-lock photocell or shorting cap, 7-pins	<b>PH7</b> Photoelectric Cell button type <b>PH8</b> <sup>3</sup> Twist-lock Photoelectric Cell <b>PH9</b> <sup>3</sup> Shorting cap <b>PHXL</b> <sup>2,3</sup> Twist-lock Photoelectric Cell extended life, UNV (120-277VAC)	<b>BAC</b> <sup>6</sup> Meets the requirements of the Buy American Act of 1933 (BAA) <b>BABA</b> <sup>6</sup> Meets the requirements of the Buy America Act for projects funded through FHWA that are obligated before October 1, 2026, and meets the Buy America preferences for FTA <b>HS</b> House side shield <b>SP2</b> 20kV / 10kA Surge protector	Consult signify.com/ outdoorluminaires for details and the complete line of Signify poles and brackets.	<b>BE2TX</b> Textured midnight blue <b>BE6TX</b> Textured ocean blue <b>BE8TX</b> Textured royal blue <b>BG2TX</b> Textured Sandstone <b>BKTX</b> Textured black <b>BRTX</b> Textured bronze <b>GN4TX</b> Textured blue green <b>GN6TX</b> Textured forest green <b>GN8TX</b> Textured Dk forest green <b>GNTX</b> Textured green <b>GR</b> Gray sandtex <b>GY3TX</b> Textured medium grey <b>NP</b> Natural aluminum <b>RD2TX</b> Textured burgundy <b>RD4TX</b> Textured scarlet <b>TG</b> Hammettone gold <b>WHTX</b> Textured white

- SMA or SMB adaptor is required for this option.
- Not available with 347V and 480V.
- RC,RCD or RCD7 must be selected for this option.
- Use of photoelectric cell or shorting cap (PH9) is required to ensure proper illumination.
- SMB adaptor is required for this option.
- Failure to properly select the "BAC" suffix could result in you receiving product that is not BAA compliant product with no recourse for an RMA or refund. This BAC designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Genlyte's products with a BAC option code designation are manufactured in the US and utilize a BAA COTS exemption rule for compliance. "BABAF" designates the product will meet the standards set by FHWA for BABA and FTA for Buy America. As noted, for FHWA BABA compliance, applicable projects must be funded by October 1, 2026.
- Extended lead-time may apply (consult factory).




# DMS50 Domus LED Pendant

## Urban Luminaire


### Dimensions

EPA: 1.35 ft<sup>2</sup> max.


Weight: 42 lbs (19.1kg) max.



**DMS50 - A optics**  
Long drop globe



**DMS50 - S optics**  
Sag lens



**DMS50 - F optics**  
Flat lens

### LED Performance

Predicted lumen depreciation data <sup>1</sup>				
Ambient Temperature (°C)	Driver (mA)	Calculated L <sub>70</sub> hours <sup>1,2</sup>	L <sub>70</sub> per TM-21 <sup>2,3</sup>	Lumen Maintenance % @ 60,000 hours
35°C	700 mA	>100,000	>60,000	86%

1. Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions.
2. L<sub>70</sub> is the predicted time when LED performance depreciates to 70% of initial lumen output.
3. Calculated per IESNA TM21-11. Published L<sub>70</sub> hours limited to 6 times actual LED test hours.

# DMS50 Domus LED Pendant

## Urban Luminaire

### LED Wattage and Lumen Values: for DMS50@3000K

Ordering Code:	Total LEDs	LED current (mA)	Average System Wattage (W)	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating
<b>Flat Lens 3000K</b>				<b>LE2F</b>			<b>LE3F</b>			<b>LE4F</b>			<b>LE5F</b>		
35W32LED3K-G3-x	32	350	37	5051	136	B1-U0-G1	4992	135	B1-U0-G1	4954	134	B1-U0-G1	4925	133	B3-U0-G1
55W32LED3K-G3-x	32	530	55	7264	132	B2-U0-G1	7178	131	B1-U0-G2	7123	130	B1-U0-G2	7082	129	B3-U0-G2
72W32LED3K-G3-x	32	700	72	9145	127	B2-U0-G2	9036	126	B2-U0-G2	8968	125	B2-U0-G2	8916	124	B3-U0-G2
55W48LED3K-G3-x	48	350	54	7555	141	B2-U0-G1	7466	139	B2-U0-G2	7409	138	B1-U0-G2	7366	137	B3-U0-G2
80W48LED3K-G3-x	48	530	80	10807	135	B2-U0-G2	10679	133	B2-U0-G2	10598	132	B2-U0-G2	10536	132	B4-U0-G2
108W48LED3K-G3-x	48	700	105	13572	129	B3-U0-G2	13411	128	B2-U0-G2	13309	127	B2-U0-G2	13232	126	B4-U0-G2
70W64LED3K-G3-x	64	350	69	9825	142	B2-U0-G2	9709	140	B2-U0-G2	9635	139	B2-U0-G2	9579	138	B3-U0-G2
110W64LED3K-G3-x	64	530	105	14083	134	B3-U0-G2	13917	132	B2-U0-G2	13811	131	B2-U0-G2	13731	130	B4-U0-G2
145W64LED3K-G3-x	64	700	138	17694	128	B3-U0-G2	17485	127	B3-U0-G2	17352	126	B3-U0-G3	17251	125	B4-U0-G2
90W80LED3K-G3-x	80	350	86	12264	143	B3-U0-G2	12119	141	B2-U0-G2	12027	140	B2-U0-G2	11957	139	B4-U0-G2
135W80LED3K-G3-x	80	530	131	17519	134	B3-U0-G2	17311	133	B3-U0-G2	17180	132	B3-U0-G3	17081	131	B4-U0-G2
180W80LED3K-G3-x	80	700	174	21865	126	B3-U0-G3	21606	124	B3-U0-G3	21442	123	B3-U0-G3	21318	122	B5-U0-G3
<b>Sag Lens 3000K</b>				<b>LE2S</b>			<b>LE3S</b>			<b>LE4S</b>			<b>LE5S</b>		
35W32LED3K-G3-x	32	350	37	5114	138	B1-U0-G1	5068	137	B1-U0-G1	5062	136	B1-U0-G1	5102	138	B3-U0-G1
55W32LED3K-G3-x	32	530	55	7354	134	B2-U0-G1	7288	133	B1-U0-G2	7279	132	B1-U0-G2	7337	133	B3-U0-G2
72W32LED3K-G3-x	32	700	72	9258	129	B2-U0-G2	9176	127	B2-U0-G2	9164	127	B2-U0-G2	9237	128	B3-U0-G2
55W48LED3K-G3-x	48	350	54	7649	143	B2-U0-G1	7581	141	B1-U0-G2	7571	141	B1-U0-G2	7632	142	B3-U0-G2
80W48LED3K-G3-x	48	530	80	10941	137	B2-U0-G2	10843	136	B2-U0-G2	10830	135	B2-U0-G2	10916	136	B4-U0-G2
108W48LED3K-G3-x	48	700	105	13740	131	B3-U0-G2	13618	130	B2-U0-G2	13601	130	B2-U0-G2	13709	131	B4-U0-G2
70W64LED3K-G3-x	64	350	69	9947	143	B2-U0-G2	9858	142	B2-U0-G2	9846	142	B2-U0-G2	9924	143	B4-U0-G2
110W64LED3K-G3-x	64	530	105	14258	135	B3-U0-G2	14131	134	B2-U0-G2	14114	134	B2-U0-G2	14226	135	B4-U0-G2
145W64LED3K-G3-x	64	700	138	17913	130	B3-U0-G2	17754	129	B3-U0-G2	17732	128	B3-U0-G3	17873	130	B4-U0-G2
90W80LED3K-G3-x	80	350	86	12416	145	B2-U0-G2	12305	143	B2-U0-G2	12290	143	B2-U0-G2	12388	144	B4-U0-G2
135W80LED3K-G3-x	80	530	131	17736	136	B3-U0-G2	17578	135	B3-U0-G2	17557	134	B3-U0-G3	17696	135	B4-U0-G2
180W80LED3K-G3-x	80	700	174	22136	127	B3-U0-G3	21939	126	B3-U0-G3	21912	126	B3-U0-G3	22086	127	B5-U0-G3
<b>Prism Globe 3000K</b>				<b>LE2A</b>			<b>LE3A</b>			<b>LE4A</b>					
35W32LED3K-G3-x	32	350	37	5081	137	B1-U3-G1	5042	136	B1-U3-G2	5056	136	B1-U3-G2	--	--	--
55W32LED3K-G3-x	32	530	55	7306	133	B2-U3-G2	7251	132	B2-U3-G2	7271	132	B1-U3-G2	--	--	--
72W32LED3K-G3-x	32	700	72	9198	128	B2-U3-G2	9128	127	B2-U3-G2	9154	127	B2-U3-G3	--	--	--
55W48LED3K-G3-x	48	350	54	7599	142	B2-U3-G2	7542	141	B2-U3-G2	7563	141	B2-U3-G2	--	--	--
80W48LED3K-G3-x	48	530	80	10870	136	B2-U3-G2	10788	135	B2-U3-G2	10818	135	B2-U3-G3	--	--	--
108W48LED3K-G3-x	48	700	105	13651	130	B3-U3-G3	13548	129	B3-U3-G3	13586	129	B2-U3-G3	--	--	--
70W64LED3K-G3-x	64	350	69	9883	142	B2-U3-G2	9808	141	B2-U3-G2	9835	142	B2-U3-G3	--	--	--
110W64LED3K-G3-x	64	530	105	14166	134	B3-U3-G3	14058	133	B3-U3-G3	14098	134	B2-U3-G3	--	--	--
145W64LED3K-G3-x	64	700	138	17798	129	B3-U3-G3	17663	128	B3-U3-G3	17712	128	B3-U3-G3	--	--	--
90W80LED3K-G3-x	80	350	86	12336	144	B3-U3-G3	12242	143	B2-U3-G3	12276	143	B2-U3-G3	--	--	--
135W80LED3K-G3-x	80	530	131	17622	135	B3-U3-G3	17488	134	B3-U3-G3	17537	134	B3-U3-G3	--	--	--
180W80LED3K-G3-x	80	700	174	21993	126	B3-U3-G3	21826	125	B3-U3-G3	21887	126	B3-U3-G4	--	--	--

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.;; highly recommended to confirm performance with a layout - contact Applications at [signify.com/outdoorluminaire](mailto:signify.com/outdoorluminaire).  
**Note:** Some data may be scaled based on tests of similar, but not identical luminaires.

# DMS50 Domus LED Pendant

## Urban Luminaire

LED Wattage and Lumen Values: for DMS50 @ 4000K, multiply 4000K values by 0.769 for 2200K

Ordering Code:	Total LEDs	LED current (mA)	Average System Wattage (W)	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating
<b>Flat Lens 4000K</b>				<b>LE2F</b>			<b>LE3F</b>			<b>LE4F</b>			<b>LE5F</b>		
35W32LED4K-G3-x	32	350	37	5304	143	B1-U0-G1	5241	141	B1-U0-G1	5201	140	B1-U0-G1	5171	139	B3-U0-G1
55W32LED4K-G3-x	32	530	55	7627	139	B2-U0-G1	7537	137	B2-U0-G2	7479	136	B1-U0-G2	7436	135	B3-U0-G2
72W32LED4K-G3-x	32	700	72	9602	133	B2-U0-G1	9488	132	B2-U0-G2	9416	131	B2-U0-G2	9362	130	B3-U0-G2
55W48LED4K-G3-x	48	350	54	7933	148	B2-U0-G2	7839	146	B2-U0-G2	7779	145	B2-U0-G2	7734	144	B4-U0-G2
80W48LED4K-G3-x	48	530	80	11347	142	B2-U0-G2	11213	140	B2-U0-G2	11128	139	B2-U0-G2	11063	138	B4-U0-G2
108W48LED4K-G3-x	48	700	105	14251	136	B3-U0-G2	14082	134	B2-U0-G2	13975	133	B2-U0-G2	13894	132	B4-U0-G2
70W64LED4K-G3-x	64	350	69	10316	149	B3-U0-G2	10194	147	B2-U0-G2	10117	146	B2-U0-G2	10058	145	B4-U0-G2
110W64LED4K-G3-x	64	530	105	14788	140	B3-U0-G2	14613	139	B3-U0-G2	14502	138	B2-U0-G2	14418	137	B4-U0-G2
145W64LED4K-G3-x	64	700	138	18579	135	B3-U0-G2	18359	133	B3-U0-G2	18219	132	B2-U0-G2	18114	131	B4-U0-G2
90W80LED4K-G3-x	80	350	86	12877	150	B3-U0-G2	12724	148	B3-U0-G2	12628	147	B3-U0-G3	12555	146	B4-U0-G2
135W80LED4K-G3-x	80	530	131	18395	141	B3-U0-G3	18177	139	B3-U0-G2	18039	138	B3-U0-G3	17935	137	B5-U0-G3
180W80LED4K-G3-x	80	700	174	22958	132	B3-U0-G3	22686	130	B3-U0-G3	22514	129	B3-U0-G3	22384	128	B5-U0-G3
<b>Sag Lens 4000K</b>				<b>LE2S</b>			<b>LE3S</b>			<b>LE4S</b>			<b>LE5S</b>		
35W32LED4K-G3-x	32	350	37	5370	145	B1-U0-G1	5322	143	B1-U0-G1	5315	143	B1-U0-G1	5358	144	B3-U0-G1
55W32LED4K-G3-x	32	530	55	7721	140	B2-U0-G1	7653	139	B1-U0-G2	7643	139	B1-U0-G2	7704	140	B3-U0-G2
72W32LED4K-G3-x	32	700	72	9721	135	B2-U0-G1	9634	134	B2-U0-G2	9623	134	B2-U0-G2	9699	135	B4-U0-G2
55W48LED4K-G3-x	48	350	54	8031	150	B2-U0-G2	7960	149	B2-U0-G2	7950	148	B1-U0-G2	8013	149	B3-U0-G2
80W48LED4K-G3-x	48	530	80	11488	144	B2-U0-G2	11386	142	B2-U0-G2	11372	142	B2-U0-G2	11462	143	B4-U0-G2
108W48LED4K-G3-x	48	700	105	14427	137	B3-U0-G2	14299	136	B2-U0-G2	14281	136	B2-U0-G2	14395	137	B4-U0-G2
70W64LED4K-G3-x	64	350	69	10444	150	B3-U0-G2	10351	149	B2-U0-G2	10338	149	B2-U0-G2	10421	150	B4-U0-G2
110W64LED4K-G3-x	64	530	105	14971	142	B3-U0-G2	14838	141	B2-U0-G2	14819	141	B2-U0-G2	14937	142	B4-U0-G2
145W64LED4K-G3-x	64	700	138	18809	136	B3-U0-G2	18642	135	B2-U0-G2	18619	135	B3-U0-G3	18767	136	B5-U0-G3
90W80LED4K-G3-x	80	350	86	13037	152	B3-U0-G2	12921	151	B3-U0-G3	12905	150	B2-U0-G2	13007	152	B4-U0-G2
135W80LED4K-G3-x	80	530	131	18623	143	B3-U0-G3	18457	141	B3-U0-G3	18435	141	B3-U0-G3	18581	142	B4-U0-G2
180W80LED4K-G3-x	80	700	174	23243	133	B3-U0-G3	23036	132	B3-U0-G3	23008	132	B3-U0-G4	23190	133	B5-U0-G3
<b>Prism Globe 4000K</b>				<b>LE2A</b>			<b>LE3A</b>			<b>LE4A</b>					
35W32LED4K-G3-x	32	350	37	5335	144	B1-U3-G1	5294	143	B1-U3-G2	5309	143	B1-U3-G2	--	--	--
55W32LED4K-G3-x	32	530	55	7672	139	B2-U3-G2	7613	138	B2-U3-G2	7635	139	B2-U3-G2	--	--	--
72W32LED4K-G3-x	32	700	72	9658	134	B2-U3-G2	9585	133	B2-U3-G2	9612	134	B2-U3-G3	--	--	--
55W48LED4K-G3-x	48	350	54	7979	149	B2-U3-G2	7919	148	B2-U3-G2	7941	148	B2-U3-G2	--	--	--
80W48LED4K-G3-x	48	530	80	11414	143	B2-U3-G2	11327	142	B2-U3-G3	11359	142	B2-U3-G3	--	--	--
108W48LED4K-G3-x	48	700	105	14334	137	B3-U3-G3	14225	135	B3-U3-G3	14265	136	B2-U3-G3	--	--	--
70W64LED4K-G3-x	64	350	69	10377	150	B2-U3-G2	10298	148	B2-U3-G2	10327	149	B2-U3-G3	--	--	--
110W64LED4K-G3-x	64	530	105	14874	141	B3-U3-G3	14761	140	B3-U3-G3	14803	140	B2-U3-G3	--	--	--
145W64LED4K-G3-x	64	700	138	18688	135	B3-U3-G3	18546	134	B3-U3-G3	18598	135	B3-U3-G4	--	--	--
90W80LED4K-G3-x	80	350	86	12952	151	B3-U3-G3	12854	150	B2-U3-G3	12890	150	B2-U3-G3	--	--	--
135W80LED4K-G3-x	80	530	131	18503	142	B3-U3-G3	18362	141	B3-U3-G3	18413	141	B3-U3-G4	--	--	--
180W80LED4K-G3-x	80	700	174	23093	133	B3-U3-G3	22917	132	B3-U3-G3	22981	132	B3-U3-G4	--	--	--

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at [signify.com/outdoorluminaires](http://signify.com/outdoorluminaires).

# DMS50 Domus LED Pendant

## Urban Luminaire

### Specifications

#### Housing

In a round shape, this housing is made of die cast A380 aluminum, c/w a watertight grommet, mechanically assembled to the bracket with four bolts 5/16 18 UNC. This suspension system permits for a full rotation of the luminaire in 90° increments.

#### Access-mechanism

A die cast A360 aluminum technical ring with latch, hinge and a cast in decorative skirt. The mechanism shall offer tool free access to the inside of the luminaire. An embedded memory retentive gasket shall ensure weatherproofing.

#### Light engine

LED engine composed of 5 main components:

##### Heat Sink / Lens / LED lamp / Driver / Optical System

Electrical components are RoHS compliant.

#### LED engine

LED type: Lumileds LUXEON T. Composed of high-performance white LEDs. Color temperature as per ANSI/NEMA bin Neutral White, 4000 Kelvin nominal (3985K +/- 275K or 3710K to 4260K) or Warm white, 3000 Kelvin nominal (3045K +/- 175K or 2870K to 3220K), CRI 70 Min. 75 Typical.

#### Lens

**LEXF / LEXS:** Made of soda lime tempered glass lens, mechanically assembled and sealed onto the lower part of the heat sink.

**LEXA (Globe):** Made of one-piece seamless injection-molded impact-resistant (DR) acrylic having an inner prismatic surface. The globe is mechanically assembled and sealed onto the lower part of the heat sink.

#### Heat sink

Made of cast aluminum optimizing the LEDs efficiency and life. Product does not use any cooling device with moving parts (only passive cooling device).

#### Driver

Driver comes standard with dimming compatible 0-10V. High power factor of 95%. Electronic driver, operating range 50/60 Hz. Auto adjusting universal voltage input from 120 to 277 VAC rated for both application line to line or line to neutral. Class I, THD of 20% max. Maximum ambient operating temperature from 40F(40C) to 130F(55C) degrees. Certified in compliance to UL1310 cULus requirement. Dry and damp location. Assembled on a unitized removable tray with Tyco quick disconnect plug resisting to 221F(105C) degrees. The current supplying the LEDs will be reduced by the driver if the driver experiences internal overheating as a protection to the LEDs and the electrical components. Output is protected from short circuits, voltage overload and current overload. Automatic recovery after correction. Standard built in driver surge protection of 2.5kV (min).


**DMG:** Dimmable driver 0-10V.

**DALI:** Pre-set driver compatible with the DALI control system.

**SRD:** Sensor Ready Driver including SR communication (used for dimming and other functionalities), 24V auxiliary supply and a logical signal input (LSI) connected to the top NEMA twist lock receptacle.

**SRD1:** Sensor Ready Driver including SR communication (used for dimming and other functionalities) but with 24V auxiliary supply and a logical signal input (LSI) not connected to the top NEMA twist lock.

**Prismatic globe:** IP66 rated optical system, composed of individual pre-oriented lens to achieve desired distribution, assembled with globe having an inner prismatic surface permanently sealed onto the lower part of the heat sink.




**ACRD-LE2A** - Type II (ASYM) with acrylic globe

**ACRD-LE3A** - Type III (ASYM) with acrylic globe

**ACRD-LE4A** - Type IV (ASYM) with acrylic globe

**Sag lens:** IP66 rated optical system, composed of individual pre-oriented lens to achieve desired distribution, assembled with a tempered-glass sag lens permanently sealed onto the lower part of the heat sink.




**LE2S** - Type II (ASYM) Sag glass lens

**LE3S** - Type III (ASYM) Sag glass lens

**LE4S** - Type IV (ASYM) Sag glass lens

**LE5S** - Type V (SYMM) Sag glass lens

**Flat lens:** IP66 rated optical system, composed of individual pre-oriented lens to achieve desired distribution, assembled with a tempered-glass flat lens permanently sealed onto the lower part of the heat sink.



**LE2F** - Type II (ASYM) Flat glass lens

**LE3F** - Type III (ASYM) Flat glass lens

**LE4F** - Type IV (ASYM) Flat glass lens

**LE5F** - Type V (SYMM) Flat glass lens

#### Optical system

Composed of high performance optical grade PMMA acrylic refractor lenses to achieve desired distribution optimized to get maximum spacing, target lumens and a superior lighting uniformity. Optical system is rated IP66. Performance shall be tested per LM 63, LM 79 and TM 15 (IESNA) certifying its photometric performance. Street side indicated. Flat lens (F optics) is Dark Sky compliant with 0% uplight and U0 per IESNA TM 15.

#### Surge protector

Surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid State Street Lighting Consortium) model specification for LED roadway luminaires electrical immunity requirements for High Test Level 10kV / 10kA. **SP2** 20kV/20kA optional.

#### Wiring

Gauge (#14) TEW/AWM 1015 or 1230 wires, 6" (152mm) minimum exceeding from luminaire.

#### Hardware

All exposed screws shall be complete with Ceramic primer-seal base coat to reduce seizing of the parts and offers a high resistance to corrosion. All seals and sealing devices are made and/or lined with EPDM and/or silicone and/or rubber.

#### Luminaire useful life

Refer to IES files for energy consumption and delivered lumens for each option. Based on ISTMT in situ thermal testing in accordance with UL1598 and UL8750, System Reliability Tool, Advance data and Lumileds LM-80/TM-21 data, expected to reach 100,000+ hours with >L70 lumen maintenance @ 25°C. Luminaire Useful Life accounts for LED lumen maintenance AND all of these additional factors including: LED life, driver life, PCB substrate, solder joints, on/off cycles, burning hours and corrosion. Entire luminaire is rated for operation in ambient temperature of -40°C / -40°F up to +35°C / +95°F.

#### LED products (manufacturing standard)

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with IEC61340 5 1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.

#### Quality control

Manufactured to ISO 9001 2015 standards and ISO 14001-2015 International Quality Standards Certification.

# DMS50 Domus LED Pendant

## Urban Luminaire


### Specifications (continued)

#### Luminaire options


**HS:** House side shield

**PH7:** Photoelectric cell, bottom type


**PH8:** Photoelectric Cell, Twist-lock Type. Allows a 90° rotation.



**PHXL:** Extended life photoelectric cell, Twist-lock Type. Allows a 90° rotation.



**PH9:** Shorting cap, Twist-lock Type



**RCD:** Receptacle 5 pins




**RCD7:** Receptacle 7 pins




**SP2:** Integral surge protector

#### Luminaire adaptor


**MA1:** The luminaire is suspended by means of a mounting adaptor with a 1¼" (32mm) NPT threaded hole accepting a threaded tube from the mounting. Retrofit adaptor for existing mounting




**MA2:** 1½" (38mm) NPT threaded hole accepting threaded tube from the mounting. Retrofit adaptor for existing mounting.



**SMA:** The luminaire is suspended by means of a decorative side-mounted cast aluminum adaptor. This adaptor accepts tubes from 1½" to 2¾" (41 to 60mm) and is adjustable to more or less 5°. The adaptor features a cast aluminum decorative cover and finial.



**SMB:** The luminaire is suspended by means of a decorative side-mounted cast aluminum adaptor. This adaptor accepts tubes from 1½" to 2¾" (41 to 60mm) and is adjustable to more or less 5°.



#### Vibration resistance

Meets the ANSI C136.31, American National Standard for Roadway Luminaire Vibration specifications for Bridge/overpass applications. (Tested for 3G over 100 000 cycles)

#### Certifications and compliance

cULus Listed for Canada and USA. Domus LED luminaires are DesignLights Consortium qualified.

#### Finish

In accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with +/- 1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard. The surface treatment achieves a minimum of 2000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard.

#### Textured Options Include:


**BE2TX:** Textured Midnight Blue  
**BE6TX:** Textured Ocean Blue  
**BE8TX:** Textured Royal Blue  
**BG2TX:** Textured Sandstone  
**BKTX:** Textured Black  
**BRTX:** Textured Bronze  
**GN4TX:** Textured Blue Green  
**GN6TX:** Textured Forest Green  
**GN8TX:** Textured Dark Forest Green  
**GNTX:** Textured Green  
**GR:** Gray Sandtex  
**GY3TX:** Textured Medium Grey  
**NP:** Natural Aluminum  
**RD2TX:** Textured Burgundy  
**RD4TX:** Textured Scarlet  
**TG:** Hammer-tone Gold  
**WHTX:** Textured White

# DMS50 Domus LED Pendant

## Urban Luminaire

### Specifications (continued)

#### Poles & Brackets Sample configurations.



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.