



Alkco's Kleenseal KTR 100 LED recessed is a cleanroom luminaire designed and well suited for all healthcare spaces, providing quality light.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

#### Ordering guide

Example: K12490L840G6AP3USSD

Family	Size	Lumens	CRI/CCT	Ceiling Type	Door Frame	Lens Type	Voltage	Options
<b>K1</b>					<b>6</b>		—	
<b>K1</b> Kleenseal KTR100	<b>14</b> 1x4 <b>22</b> 2x2 <b>24</b> 2x4	<b>40L</b> 4,000 nominal delivered lumens (1x4, 2x2) <b>60L</b> 6,000 nominal delivered lumens (1x4, 2x2) <b>64L</b> 6,400 nominal delivered lumens (2x4) <b>75L</b> 7,500 nominal delivered lumens (2x4) <b>87L</b> 8,700 nominal delivered lumens (2x4) <b>90L</b> 9,000 nominal delivered lumens (2x4) <b>110L</b> 11,000 nominal delivered lumens (2x4) <b>130L</b> 13,000 nominal delivered lumens (2x4)	<b>835</b> 3500K (CRI 80) <b>840</b> 4000K (CRI 80) <b>850</b> 5000K (CRI 80)	<b>G</b> 1",1-1/2" Grid T <b>2G</b> 2" Grid T <b>F</b> Flange	<b>6</b> Aluminum 4-piece flush white	<b>AP3</b> .125" acrylic prismatic  Other lenses available	<b>U</b> Universal voltage, 120-277V <b>1</b> 120V <b>2</b> 277V	<b>DN</b> Lens furnished prisms down <b>SSD</b> Stainless steel inset door <b>EMLED<sup>1</sup></b> 10W batter pack

#### General Notes

Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

#### Predicted L70 Lifetime

25°C ambient >100,000 hours (based upon LED manufacturer's supplied LM-80 data and in-situ laboratory testing).

# K1 Kleenseal LED KTR100 recessed

Cleanroom luminaire, 4,000, 6,000, 9,000, 11,000, or 13,000 lumens

## Standards

- Certified to meet UL 1598 standards for wet location.


## Construction/Finish

- Sealed aluminum housing resists corrosion and is lightweight which speeds installation.
- Fits 1", 1-1/2", 2", and Tall 2" grid or flange mountings.
- Top and end 1/2" conduit K.O.s for easy thru wiring.
- Seismic support mounting is standard.
- Removable sealed wiring access plate.
- Door is secured to housing with captive stainless steel screws.
- Door frame is retained to housing when opened for safety and ease during re-lamping.
- .125" prismatic acrylic lens is silicone sealed to flush aluminum door frame.
- Class 100-100,000 cleanrooms.

## Energy Table

Lumens	Watts	Efficiency
40L	43	93 lm/W
68L	68	100 lm/W
75L	77	97 lm/W
87L	85	102 lm/W
90L	86	104 lm/W
110L	105	105 lm/W
130L	125	104 lm/W

## Dimensions



**Note:** For technical information or codes and classifications, see PDFs Tech1-Tech5 online.

Ceiling Opening Flange Type	Grid Type	A	B	C
1X4	1" or 1-1/2" Grid	23-3/4" (603.3 mm)	47-3/4" (1212.9 mm)	1-11/16"
2X2	2" Grid	23-3/4" (603.3 mm)	47" (1194 mm)	1-11/16"
2X4				



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.