



The Hadco Savannah post top luminaire is an authentic recreation of distinctive lighting from our American past. Blending old world charm with today's energy efficient light sources and optics, Savannah is a luminaire with outstanding versatility. For restoration areas where street lighting is required Savannah offers memorable accents that complement many architectural themes.

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Ordering guide

Example: V671 A T3 N D 70S E


Series	Finish	Optics	Photo Control	Socket	Wattage	Voltage
V671	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
V671	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>J</b> Green	<b>T3</b> Type III Cutoff <b>T5</b> Type V Cutoff <b>V3</b> Vertical Ribbed Type III <b>V5</b> Vertical Ribbed Type V	<b>B</b> Button Eye Photo Control <b>R</b> Twist Lock Receptacle <sup>1</sup> <b>N</b> None	<b>D</b> Medium <b>G</b> Mogul	<b>70S</b> 70W HPS <b>100S</b> 100W HPS <b>150S</b> 150W HPS <b>250S</b> 250W HPS <sup>2</sup> <b>70H</b> 70W MH <sup>3</sup> <b>100H</b> 100W MH <sup>3</sup> <b>150H</b> 150W PMH <b>250H</b> 250W PMH <sup>2</sup>	<b>E</b> 120V <b>F</b> 208V <b>G</b> 240V <b>H</b> 277V <b>K</b> 347V

1. Twistlock receptacle (R) not available with 347V (K).
2. Available with Mogul base (G) socket only.
3. Available with Medium base (D) socket only.

# V671 Savannah


## Post top

### Dimensions



#### V671

Height: 42 1/4" (107cm)  
Width: 19 5/16" (49cm)  
Max. EPA: 2.0 sq. ft.  
Max. Weight: 37.5 lbs



### Specifications

#### HOUSING:

360 low-copper die-cast aluminum alloy . Tool-less lamp access. Hinged roof with stainless steel spring latch. A weatherproof ballast assembly isolates the ballast from water and heat for longer life. The optional photo control eye or twist-lock receptacle is located in vent cap. All non-ferrous fasteners prevent corrosion and ensure longer life. Slip Fitter Dimensions: 3" I.D. x 3" deep .

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

#### OPTICAL ASSEMBLY:

Type III Cutoff. Type V Cutoff. Precision formed, segmented specular aluminum internal cutoff reflector with horizontal lamp mounting. Decorative frosted glass chimney. U.V. stabilized, injection molded, clear acrylic panels. Type III Vertical Rib Cutoff. Type V Vertical Rib Cutoff. Precision formed, segmented specular aluminum internal cutoff reflector with horizontal lamp mounting. (NOTE: No decorative frosted glass chimney.) U.V. stabilized, injection molded ribbed acrylic panels with internal vertical ribs. Tool-less removal panels for ease of cleaning.

#### LAMPING:

MH and HPS Medium base: E17. MH and 250W HPS Mogul base: ED28. 70W-150W HPS Mogul base: ED23.5.

#### ELECTRICAL ASSEMBLY:

Ballast assemblies are mounted to an aluminum plate or spinning, which is mounted inside the roof of the fixture. 4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact. 4kv rated mogul base porcelain socket. Nickel-plated screw shell with center contact.

#### BALLAST:

All HID ballasts are core and coil and regulated with power factors better than 90% (HPF). Ballast provides +/- 5% lamp power regulation with +/- 10% input voltage regulation. Ballasts are factory pre-wired and tested. Metal halide ballasts are capable of starting at -20° F or -30° C and HPS at -40°F or -40°C. NOTE: All ballasts are EISA / Title 20 / Title

