## **Product Information Sheet**

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name	or trade mark:	PHILIPS
-----------------	----------------	---------

Supplier's address: Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

_	•			
Tyna	Λt	lioht	source	٠.
IVDE	vı	HEILL	JUUILE	- •

Lighting technology used:	МН	Non-directional or directional:	NDLS
Light source cap-type	E40		
(or other electric interface)			
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	Non-clear
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No
Product parameters			

Parameter		Value	Parameter	Value
Tarafficter				value
		General product p	T	T
	mption in on- 100 h), rounded st integer	360	Energy efficiency class	G
indicating if it r in a sphere (3	us flux (фuse), efers to the flux 60º), in a wide n a narrow cone	32 400 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	4 200
On-mode prespressed in W	oower (P <sub>on</sub> ),	360,0	Standby power (P <sub>sb</sub> ), expressed in W and rounded to the second decimal	0,00
for CLS, expres	dby power (P <sub>net</sub> ) ssed in W and second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	88
Outer	Height	226	Spectral power	See image
dimensions	Width	91	distribution in the	in last page
without	Depth	91	-	Page 1 / 3

separate control gear, lighting control parts and non- lighting control parts, if any (millimetre)	range 250 nm to 800 nm, at full-load	
Claim of equivalent power <sup>(a)</sup>	- If yes, equivalent power (W)	-
	Chromaticity coordinates (x and y)	0,371 0,366

(a)'-': not applicable; (b)'-': not applicable;

