## **Product Information Sheet**

Outer dimen-

sions without

separate con-

trol gear, light-

Height

Width

Depth

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

| sources  | LATION (LO) 2013/2            | olo with regard to energ   | gy labelling of light           |  |
|--|-------------------------------|--|---------------------------------|--|
| Supplier's name or trade mark:   | PHILIPS                       |  |                                 |  |
| Supplier's address: Customer Ca  | are Philips, I.B.R.S./C       | C.C.R.I. /Numéro 10461,  | 5600VB Eindhoven, NL            |  |
| Model identifier: 9290019535   |                               |  |                                 |  |
| Type of light source:  |                               |  |                                 |  |
| Lighting technology used:  | LED                           | Non-directional or directional:  | DLS                             |  |
| Light source cap-type  | GU10                          |  |                                 |  |
| (or other electric interface)  |                               |  |                                 |  |
| Mains or non-mains:  | MLS                           | Connected light source (CLS):  | Yes                             |  |
| Colour-tuneable light source:  | No                            | Envelope:  | -                               |  |
| High luminance light source:   | No                            |  |                                 |  |
| Anti-glare shield:   | No                            | Dimmable:  | Only with spe-<br>cific dimmers |  |
|  | Product para                  | meters   |                                 |  |
| Parameter  | Value                         | Parameter  | Value                           |  |
| General product parameters:  |                               |  |                                 |  |
| Energy consumption in on-<br>mode (kWh/1000 h), rounded<br>up to the nearest integer   | 6                             | Energy efficiency<br>class   | F                               |  |
| Useful luminous flux (φuse), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 400 in Nar-<br>row cone (90°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 2 700                           |  |
| On-mode power (P <sub>on</sub> ), expressed in W   | 5,2                           | Standby power (P <sub>sb</sub> ),<br>expressed in W and<br>rounded to the sec-<br>ond decimal  | 0,00                            |  |
| Networked standby power (P <sub>net</sub> ) for CLS, expressed in W and rounded to the second decimal                                | 0,50                          | Colour rendering in-<br>dex, rounded to the<br>nearest integer, or<br>the range of CRI-val-<br>ues that can be set   | 80                              |  |
|  |                               |  |                                 |  |

54

50

50

Spectral power dis-

range 250 nm to 800

nm, at full-load

in

the

tribution

See image

in last page

| ing control parts and non-lighting control parts, if any (millimetre)   |             |  |                |  |
|---|-------------|--|----------------|--|
| Claim of equivalent power <sup>(a)</sup>  | Yes         | If yes, equivalent power (W)                                       | 35             |  |
|   |             | Chromaticity coordinates (x and y)                                 | 0,458<br>0,410 |  |
| Parameters for directional light  | sources:    |  |                |  |
| Peak luminous intensity (cd)  | 920         | Beam angle in degrees, or the range of beam angles that can be set | 34             |  |
| Parameters for LED and OLED lig   | ht sources: |  |                |  |
| R9 colour rendering index value   | 0           | Survival factor  | 0,90           |  |
| the lumen maintenance factor  | 0,93        |  |                |  |
| Parameters for LED and OLED mains light sources:  |             |  |                |  |
| displacement factor (cos φ1)  | 0,50        | Colour consistency in McAdam ellipses                              | 6              |  |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | _(b)        | If yes then replace-<br>ment claim (W)                             | -              |  |
| Flicker metric (Pst LM)   | 1,0         | Stroboscopic effect metric (SVM)                                   | 0,4            |  |

(a)'-': not applicable; (b)'-': not applicable;

