



Lumec **Square Lantern** LED post top luminaires draw on the designs of yesteryear in order to evoke a feeling of harmony and warmth in any project. This series is another example of how Lumec melds feelings of old-time luminaires with modern lighting techniques and technology. It can complement many settings thanks to its two sizes and its internal components assure long life, reliability, and durability. The blend of form and function makes the **Square Lantern** luminaires an excellent choice for older neighborhoods or contemporary environments.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide


example: S26A-C-140L450WW-G1-ACDR-C-LE3-120-DMG-SP2-BKTX

Series	LED module	Gen.	Globe material	Globe finish	Optical system	Voltage	Driver options	Luminaire options	Poles / Brackets	Finish
<input type="text"/>	<input type="text"/>	<input type="text" value="G1"/>	<input type="text"/>	<input type="text" value="C"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
S26A-C S26N-C	3000K 140L450WW 140L650WW 140L1150WW 140L1675WW 140L2100WW 4000K 140L450NW 140L650NW 140L1150NW 140L1675NW 140L2100NW	Gen. G1 G1	ACDR Acrylic Globe PC Poly- carbonate	C Clear Globe	3 Type III (ASYM) 5 ² Type V (SYM)	347 480 UNV	CDMGE25 ³ (2) 8 hrs. 25% reduction CDMGE50 ³ (2) 8 hrs. 50% reduction CDMGE75 ³ (2) 8 hrs. 75% reduction CDMGM25 ³ (2) 6 hrs. 25% reduction CDMGM50 ³ (2) 6 hrs. 50% reduction CDMGM75 ³ (2) 6 hrs. 75% reduction CDMGS25 ³ (2) 4 hrs. 25% reduction CDMGS50 ³ (2) 4 hrs. 50% reduction CDMGS75 ³ (2) 4 hrs. 75% reduction WC Without Cupola DMG 0-10V SRD ¹ Sensor ready driver (standard configuration) SRD1 ¹ Sensor ready driver (alternate configuration)	PH7 ⁴ Photoelectric cell button type RCD7 ⁵ Receptacle 7-pin SP2 20kV/20kA surge protector TN2.875C 2 7/8" dia. Tenon adaptor TN3 3" dia. Tenon adaptor TN3.5 3 1/2" dia. Tenon adaptor	Consult with signify.com/ outdoorluminaires for details and the complete line of Signify poles and brackets.	Textured BE2TX Midnight Blue BE6TX Ocean Blue BE8TX Royal Blue BG2TX Sandstone BKTX Black BRTX Bronze GN4TX Blue Green GN6TX Forest Green GN8TX Dark Forest Green GNTX Green GY3TX Medium Grey RD2TX Burgundy RD4TX Scarlet WHTX White Other GR Gray Sandtex NP Natural Aluminum TG Hammertone Gold

1. Only available in Polycarbonate.
 2. Not available with HS option.
 3. Not available 347-480 volt.
 4. Not available with WC option.
 5. If RCD7 is required you need to select WC without cupola. The RCD7 is located on top of the roof in place of the cupola for use with a control node.

S26A-C/S26N-C Square Lantern LED Post Top Urban Luminaire

Dimensions



S26A-C

EPA: 2.97 sq ft
Weight: 44 lbs (20 kg)

S26N-C

EPA: 3.25 sq ft
Weight: 45 lbs (20.4 kg)

LED Wattage and Lumen Values: for S26A-C / S26N-C with Clear globe

Ordering Code: Clear Globe (3000K)	Total LEDs	LED Current (mA)	Color Temp.	Average System Wattage ¹ (W)	3			5		
					Lumen Output ²	Efficacy (LPW)	BUG Rating	Lumen Output ²	Efficacy (LPW)	BUG Rating
140L450WW-G1-x	140	450	3000	21	1793	85	B1-U2-G1	1720	82	B1-U2-G1
140L650WW-G1-x	140	650	3000	30	2543	85	B1-U2-G1	2440	81	B2-U2-G1
140L1150WW-G1-x	140	1150	3000	52	4267	82	B2-U3-G2	4095	79	B2-U3-G2
140L1675WW-G1-x	140	1675	3000	75	5816	78	B3-U3-G3	5582	74	B3-U3-G2
140L2100WW-G1-x	140	2100	3000	94	6964	74	B3-U3-G3	6683	71	B3-U3-G2

Ordering Code: Clear Globe (4000K)	Total LEDs	LED Current (mA)	Color Temp.	Average System Wattage ¹ (W)	3			5		
					Lumen Output ²	Efficacy (LPW)	BUG Rating	Lumen Output ²	Efficacy (LPW)	BUG Rating
140L450NW-G1-x	140	450	4000	21	1900	90	B1-U2-G1	1823	87	B1-U2-G1
140L650NW-G1-x	140	650	4000	30	2695	90	B1-U2-G1	2587	86	B2-U2-G1
140L1150NW-G1-x	140	1150	4000	52	4523	87	B2-U3-G2	4341	83	B2-U3-G2
140L1675NW-G1-x	140	1675	4000	75	6165	82	B3-U3-G3	5917	79	B3-U3-G2
140L2100NW-G1-x	140	2100	4000	94	7382	79	B3-U3-G3	7084	75	B3-U3-G2

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at signify.com/outdoorluminaires.
Note: Some data may be scaled based on tests on similar but not identical luminaires.

S26A-C/S26N-C Square Lantern LED Post Top Urban Luminaire

Specifications

Housing

Finial: Decorative cast 356 aluminum, mechanically assembled.

Cupola: Decorative spun aluminum 1100 O, mechanically mounted on hood.

Hood: In a square tapered shape, the hood is made of a one-piece die cast injection molded A360 aluminium. Mechanically assembled to the guard.

Guard: In a square tapered shape, the guard is made of one-piece die cast injection molded A360 aluminium.

Access-mechanism

Two integrated hinges on the hood with a stopper and a latch shall offer a tool-free access to the inside of the luminaire. An embedded memory-retentive gasket shall ensure weatherproofing.

Light engine

Light guide technology provides low-glare, uniform illumination. Composed of 140 LEDs strategically positioned on the edge of the optical plate. Light engine luminous opening size optimized to best achieve a balance between lumen output and optical performance with the need to provide visual comfort. Light engine frame ensures contact with housing to provide heat conduction and sealing against the elements. Light engine is RoHS compliant. Maximum ambient operating temperature up to 40°C(104°F). Standard color temperatures: 3000K +/- 130K, 4000K +/- 130K, Minimum CRI of 70. Also available in 2700K, 3500K, 5000K and Amber (>590nm) with extended lead times. Contact factory for details.

Globe/Panel

ACDR-C: Made of one-piece seamless injection-molded clear impact-resistant (DR) acrylic. The globe is assembled on the access-mechanism.

PC-CS: Made of one-piece seamless injection-molded satin clear polycarbonate. The globe is assembled on the access-mechanism.

Heat sink

Made of cast aluminum optimizing the LEDs efficiency and life. Product does not use any cooling device with moving parts (only passive cooling device).

Optical system

The advanced LED comfort optical system provides standar Types 3 and 5. Also available in Types 1, 2 and 4 with extended lead times. Contact factory for details. Composed of high performance UV-stabilized optical grade lens with molded micro-optics to achieve desired distribution optimized to get a exceptional lighting uniformity. Performance tested per LM-79 and TM-15 (IESNA) certifying its photometric performance. Street side indicated.

LE3 - Type III (ASYM)

LE5 - Type V (SYMM)

Driver

Driver comes standard with dimming compatible 0-10V. High power factor of 90% minimum. Electronic driver, operating range 50/60 Hz. Auto adjusting universal voltage input from 120 to 277 or 347 to 480 VAC rated for both application line to line or line to neutral, Class I, THD of 20% max. Maximum ambient operating temperature from 40°F (40°C) to 130°F (55°C).

Certified in compliance to UL1310 cULus requirement. Dry and damp location. Assembled on a unitized removable tray with Tyco quick disconnect plug resisting to 221°F (105°C). The current supplying the LEDs will be reduced by the driver if the driver experiences internal overheating as a protection to the LEDs and the electrical components. Output is protected from short circuits, voltage overload and current overload. Automatic recovery after correction. Standard built in driver surge protection of 2.5kV (min).

Driver options

DMG: Dimmable driver 0-10V.

CDMG: Dynadimmer standard dimming functionalities including pre-programmed scenarios to suit many applications and needs from safety to maximum energy savings.

* Contact factory for DALI options.

Order Code	Dimming		
	Scenario	Duration	Level
CDMG25	Safety	4 hours	25%
CDMG50	Safety	4 hours	50%
CDMG75	Safety	4 hours	75%
CDMG25	Median	6 hours	25%
CDMG50	Median	6 hours	50%
CDMG75	Median	6 hours	75%
CDMG25	Economy	8 hours	25%
CDMG50	Economy	8 hours	50%
CDMG75	Economy	8 hours	75%

SRD: Sensor Ready Driver including SR communication (used for dimming and other functionalities), 24V auxiliary supply and a logical signal input (LSI) connected to the top NEMA twist lock receptacle.

SRD1: Sensor Ready Driver including SR communication (used for dimming and other functionalities) but with 24V auxiliary supply and a logical signal input (LSI) not connected to the top NEMA twist lock.

LED Performance

Predicted lumen depreciation data ¹				
Ambient Temperature (°C)	Driver mA	Calculated L ₇₀ hours ^{1,2}	L ₇₀ per TM-21 ^{2,3}	Lumen Maintenance % @ 60,000 hours
25°C	2100 mA	>100,000	>60,000	84%

1. Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions.
2. L₇₀ is the predicted time when LED performance depreciates to 70% of initial lumen output.
3. Calculated per IESNA TM21-11. Published L₇₀ hours limited to 6 times actual LED test hours.

Surge protector

Surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid State Street Lighting Consortium) model specification for LED roadway luminaires electrical immunity requirements for High Test Level 10kV / 10kA. SP2 20kV/20kA optional.

Luminaire options



LF
Lily-flower decorative cap

PH7 Photoelectric cell button type

SP2 20kV/20kA integral surge protector (optional)

WC Without Cupola



RCD7
Receptacle 7-pins



TN2.875C
2-7/8" dia. tenon adaptor



TN3
3" dia. tenon adaptor



TN3.5
3-1/2" dia. tenon adaptor

S26A-C/S26N-C Square Lantern LED Post Top Urban Luminaire

Specifications (continued)

Luminaire useful life

Refer to IES files for energy consumption and delivered lumens for each option. Based on ISTMT in situ thermal testing in accordance with UL1598 and UL8750, using LM-80 data from LED manufacturers and engineering prediction methods, the luminaire useful life is expected to reach 100,000+ hours with >L70 lumen maintenance @ 25°C. Luminaire Useful Life accounts for LED lumen maintenance AND all of these additional factors including: LED life, driver life, PCB substrate, solder joints, on/off cycles, burning hours and corrosion. Entire luminaire is rated for operation in ambient temperature of -40°C / -40°F up to +35°C / +95°F.

Hardware

All exposed screws shall be complete with Ceramic primer-seal base coat to reduce seizing of the parts and offers a high resistance to corrosion. All seals and sealing devices are made and/or lined with EPDM and/or silicone and/or rubber.

Wiring

Gauge (#14) TEW/AWM 1015 or 1230 wires, 6" (152mm) minimum exceeding from luminaire.

LED products (manufacturing standard)

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with IEC61340 5 1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.


Quality control

Manufactured to ISO 9001 2008 standards and ISO 14001-2004 International Quality Standards Certification.

Certifications and Compliance

CSA, cULus Listed for Canada and USA.
Luminaires are DesignLights Consortium qualified.

Assembly example



Consult signify.com/outdoorluminaires for details and the complete line of Signify poles and brackets.

