philips dynalite ())

Multipurpose Controllers



DMC810GL Multipurpose Controller

Combining leading edge and signal dimming control

The Philips Dynalite DMC810GL is an 8-channel controller that provides a combination of control technologies. The ability to control mixed load types from one device provides savings in initial capital costs, installation costs and a reduction in ongoing maintenance.

DMC810GL

Combining leading edge and signal dimming control

- Four channels for control of dimmable loads Leading edge phase control for use with incandescent, neon, leading edge electronic and iron core transformers.
- Four signal control outputs Selectable to 1-10 VDC, DSI and DALI broadcast for control of lamp drivers.
- Four switched outputs Signal control outputs can operate in tandem with, or separately from, switched outputs.
- Interference suppression Iron powder core toroidal choke lessens effects of interference from other equipment, such as transformers.
- **Naturally ventilated** Requires no forced cooling or maintenance.
- **Diagnostic functionality** Device Online/Offline status reporting.
- User controls Incorporates service override switch all channels to 100% and a diagnostic LED.
- **Options available** Including an additional RS-485 DyNet/DMX512 port or earth leakage and overload protection on each channel.

Dimensions



Specifications Due to continuous improvements and innovations, specifications may change without notice.



DMC810GL Multipurpose Controller

Electrical

Single phase
230 VAC ±14%
40 A
4 x leading edge dimming 4 x switched
4 x 10 A single-pole thermal magnetic (6 kA surge)
Triac (40 A nominal, 600 V, 400 A surge)
Iron powder toroidal choke
12 VDC
200 mA
III

Overvoltage Category	
Control	
Serial Ports	1 x RS
Supported Protocols	E DN
DMX Rx Channels	

S-485 DyNet MX Rx 8 Control Channel Outputs 4 x signal dimming control (DALI Broadcast, DSI, 1-10 V)

User Controls	1 x service switch
	8 x DyNet address DIP switch
Indicators	1 x service LED

Physical

Dimensions (H x W x D)	386 x 212 x 179 mm (15.20 x 8.35 x 7.05 in)
Packed Weight	7.50 kg (16.53 lb)
Construction	Alloy / Steel wall-mount case Powder coat finish
Serial Ports	1 x RJ12 1 x 6-way pluggable screw terminal
Serial Port Conductor Size	2.5 mm² (#12 AWG) (max)
Supply Terminals	2 x screw terminal Line, Neutral
Supply Terminal Conductor Siz	e 10 mm² (#6 AWG) (max)
Phase Control Terminals	16 x screw terminal
Phase Control Terminal Conduc	ctor Size 5 mm ² (#10 AWG) (max)
Signal Dimming Terminals	8 x screw terminal
Signal Dimming Terminal Cond	uctor Size 2.5 mm ² (#12 AWG) (max)
Earth Bar Terminals	5 x screw terminal
Earth Bar Conductor Size	16 mm²(#6 AWG) (max)

Environment*

Operating Temperature	0° to 40°C ambient (32° to 104°F)
Storage/Transport Temperature	-25° to 70°C ambient (-13° to 158°F)
Humidity	0 to 90% non-condensing
IEC Pollution Degree	II

Compliance

Certification

CE, RCM, UKCA, RoHS

* For indoor installation only



Electrical



Control Channel Ratings

DALI/DSI	Channel	Device
Guaranteed Current	128 mA	
Maximum Current	250 mA	
Maximum Drivers	64	200
Insulation	Basic	
	,	
1-10 V	Channel	
Current	sink 50 mA source 50 mA	

Output Channel Ratings

Load Type		Maximum Rating per Output		ting		
		CH5	-CH8			
General Use		10 A, 240 VAC				
Incandescent		5 A, 2	40 VAC			
Magnetic with Halogen		2 A, 2	40 VAC			
Electronic Driver		3 A, 2	40 VAC			
Inrush Current		165 A				
Maximum Group Load	CH1 & CH5	_	H2 & H6	CH3 & CH7	CH4 & CH8	DEVICE
	10 A	10) A	10 A	10 A	40 A

Ordering Code	
Product	Philips 12NC
DMC810GL	913703028009



© 2021 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.