

PHILIPS

Desk Lamp

myHomeOffice

Amber

white

LED

66133/31/T3



Reliable desk lighting for more convenience

A batten light with integrated battery for more convenience

Easy on your eyes

- Scientific light distribution

Control

- Multi-level step dimming

Easy to experience

- Rechargeable battery

Highlights

Scientific light distribution

Multi-level step dimming

Intuitive multi-level brightness control setting gives you great control over

your lights and to create the light ambiance that you need.

Rechargeable battery

Works without plug-in charger.

Specifications

Design and finishing

- Color: white
- Material: metal/plastic

Extra feature/accessory incl.

- 5 years warranty on the LED module: No
- FFP – Frustration Free Pack: Yes

Miscellaneous

- Especially designed for: Home office & Study, Living- & Bedroom
- Type: Table lamp
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.340 kg
- Height: 24.5 cm
- Length: 3.9 cm
- Width: 29.2 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 480 lm
- Mains power: 5 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- Number of bulbs: 1
- Wattage bulb included: 1.5 W
- Maximum wattage replacement bulb: 1.5 W
- IP code: IP20, protection against objects bigger than 12.5 mm, no protection against water
- Class of protection: III – safe extra low voltage
- Light source replaceable: No



Issue date: 2023-11-08
Version: 0.35

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com