
Project	Catalog #	Туре	
Prepared by	Notes	Date	



Greengate

VNW-P-NeoSwitch

Passive Infrared/Single Level Wall Switch Vancancy Sensor (Ground Required)

Typical Applications

Private Offices • Small Conference Rooms • Lunch/Break Rooms • Small Classrooms • Small Restrooms (no stalls) • Small Lounges • Small Waiting Rooms • Small Closets • Small Storage Areas

Interactive Menu

- Order Information page 2
- Additional Resources page 2
- Wiring Diagrams page 3
- Product Warranty

Product Certification







Product Features








Top Product Features

- · Air-gap switch ensures no leakage current to load
- · Selectable built-in light level sensor
- Products tested to NEMA WD 7 2024 Occupancy Motion Sensors Standard
- Requires Manual On for activation
- LED Rated

Dimensional Details

1.732" [44mm] 0 4.195" [106.5mm] <u></u>

Scale or Mounting Height







Greengate VNW-P-NeoSwitch

Order Information

SAMPLE ORDER NUMBER: VNW-P-1001-MV-W

One single gang wallplate included.

Catalog Number

Catalog Number	Ratings	Coverage	Voltage	Color
VNW-P-1001-MV- * (*-W, V, G,R)	Incandescent: 0-800W @ 120V Fluorescent: 0-1200W @ 120V Fluorescent: 0-2700W @ 277V Max Load/Relay	180°; 1000 sq. ft.	120/277 VAC, 50/60 Hz	W=White, V=Ivory, G=Gray, R=Red
				Notes Not all colors are available in stock and some color options may have extended lead times.

Product Specifications

Technology

Passive Infrared (PIR)

Mechanical

Mounting Plate Dimensions:~4.195"~H~x~1.732"~W~(106.55mm~x~44mm)

Product Housing Dimensions: 2.618" H x 1.752" W x 1.9" D (66.5mm x 44.5mm x 48.26mm)

Environment:

- · Operating temperature: 32°F to 104°F (0°C to 40°C)
- · Relative humidity operating: 20% to 90% non-condensing
- · For indoor use only

Housing: Durable, injection molded housing. ABS resin complies with UL 94V-0 **Mounting:** Fits in a standard 3.5" deep back box. Can be mounted in multiple gang back box Refer to NEC box calculation for properly sized mounting box

Electrical

Electrical ratings:

120 VAC

- · Incandescent / Tungsten max load: 6.7 amps, 800W, 50/60 Hz
- Fluorescent / Ballast max load: 10 amps, 1200W, 50/60 Hz
- Electronic Ballast (LED): 3A
- Motor Load: 1/4 HP @ 125 VAC

277VAC

- Fluorescent / Ballast max load: 9.8 amps, 2700W, 50/60 Hz
- Electronic Ballast (LED): 3A

Ballast compatibilty:

- LED loads
- · Magnetic and Electronic ballasts

Hardware Specifications

LED Indicators:

- · Red LED = PIR detection
- · Green LED = acts as EcoMeter or night light locator

Controls and Performance

Time delays:

- · Self adjusting 15 seconds/test (10 min. Auto)
- · Selectable 5, 15, 30 minutes

Coverage:

- Major motion: 36' x 30'
- Minor motion: 20' x 16'

Light sensing level:

0 to 200 foot candles

Standards/Ratings

- · cULus Listed
- · FCC Compliant
- · RoHS Compliant

Warning

- This product is not intended to be used in applications involving the use of ammonia-based or VOC cleaners.
- Use of ammonia-based or VOC cleaners on this device must be avoided.
 Prolonged use may cause loss of integrity and expose electrified components.
 If this occurs, turn OFF power to the unit and replace.
- For detailed cleaning guidelines please refer to: Controls Care and Maintenance instructions at the end of this document.

Warrant

Five year warranty standard

Overview

The Passive Infrared Single Level Vacancy Sensing Wall Switch is a motion sensing lighting control and conventional wall switch all-in-one hat is used to for energy savings and convenience.


VNW-P-1001-MV uses Passive Infrared (PIR) sensor technology to monitor a room for occupancy and deliver maximum energy savings. The lights are turned ON by pressing the universally recognized light icon pushbutton. The sensor includes self-adaptive technology that continuously self-adjusts sensitivity and time delay in realtime, maximizing the potential energy savings that are available in the particular application. The EcoMeter provides a visual indicato of energy usage, increasing end user awareness and reminding individuals to take control of their lighting to maximize energy savings. PIR sensors are considered line-of-sight sensors, meaning that the sensor must be able to have a direct line-of-sight to the person making the motion.




Greengate **VNW-P-NeoSwitch**

Wiring Diagrams


Single Level Switching




Single Level Three-Way Wiring Diagram: Lights will turn OFF automatically when sensor that detected motion last, times out.



Controls








Greengate VNW-P-NeoSwitch

Field of View








Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

Cooper Lighting Solutions



Cooper Lighting Solutions has developed recommended guidelines for cleaning our products that will not impact the operation or finish of the product.

Recommended cleaning tips:

- · Never spray any fluids directly into the device.
- · Use of ammonia-based or VOC cleaners on this device must be avoided. Prolonged use may cause loss of integrity and expose electrified components. If this occurs, turn OFF power to the unit and replace.
- Use a damp rag or single-use wipe to avoid excess liquid penetrating the device.
- Be sure to wipe up remaining excess liquid after cleaning.
- · Ensure the cleaning agent used does not have harsh chemicals such as bleach, ammonia, highly alkaline or concentrated acids (such as hydrochloric acid that can be found inhousehold cleaners such as toilet bowl cleaners, bathroom tile and porcelain cleaners) as they could damage the device, causing them to become brittle and discolored.
- Cooper Lighting Solutions recommends the use of a mild liquid detergent and water to clean the devices. Single use wipes (e.g. Lysol brand or equivalent) are acceptable to use for cleaning the devices, however the single-use wipes cannot contain bleach, ammonia, highly alkaline or concentrated acids.



image for reference only

WARNING

This product is not intended for use in applications involving the use of ammonia-based or VOC cleaners.

Prolonged use may cause loss of integrity and expose electrified components.

> If this occurs, turn OFF power to the unit and replace.

Recommended cleaning instructions:

- · Never spray any fluids directly into the device.
- · Apply the mild liquid detergent to a damp cloth or paper towel. Single use wipes (e.g. Lysol brand or equivalent) are acceptable to use for cleaning the devices, however single-use wipes cannot contain bleach, ammonia, highly alkaline or concentrated acids.
- · If excess liquid is present, remove by wringing out the cloth or paper towel to avoid liquid penetration into the device.

5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172

- · Clean the Cooper Lighting Solutions device by wiping over the surface with the damp cloth.
- Remove an excess liquid remaining on the device with a dry cloth or paper towel.

