




Day-Brite/CFI SofTrace LED recessed is a fully luminous aperture luminaire providing contemporary appeal to architectural spaces. This linear form includes a round profile center and contiguous contoured sides with balanced glare to provide a clean aesthetic appeal. An architectural style coupled with control options makes SofTrace an ideal for applications such as office, institutional, and healthcare where energy savings and customized effects are desired.



DS lens (smooth)



D lens (ribbed)

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Qty: _____
 Notes: _____

Now available with AccuRender technology for the highest color quality at the highest efficacy.

Base configurations are indicated in blue. Standard configurations are available with all choices, unless otherwise noted.

Ordering guide (standard & wireless controls)

example: 1STXG38L840-4-D-UNV-DIM-SWZCS

Series	Ceiling Type	Lumens (nominal delivered)	Efficacy	Color (CRI/CCT)	Length	Center Diffuser	Voltage	Driver	Options						
1STX	G			-	4 -	D -	-	-							
1STX 1' SofTrace gen 2	G Grid	Base configs	Blank Standard	830 80 CRI, 3000K	4 4'	D Diffuse (ribbed)	UNV Universal Voltage, 120-277V	DIM¹ Dimming	F1 3/8" flex, 18ga. 6'; 3 leads include hot, neutral, ground						
		38B 3800	H⁵ High	835 80 CRI, 3500K						SDIM Step dimming to 40% input power	F2 3/8" flex, 18ga. 6'; 4 leads include 2 hots, neutral, ground				
		Standard configs		840 80 CRI, 4000K								LDEH Lutron LDE1, 1% dimming	F1/D 3/8" twin flex, 18ga. 6' (for dimmable); Flex 1: 3 leads include hot, neutral, ground Flex 2: 2 leads, Dim+ / Dim-		
		30L 3000		850 80 CRI, 5000K										DALI DALI dimming	F2/SW 3/8" single flex, 18ga. 6' (for dimmable); 5 leads include hot, neutral, ground, Dim+ / Dim-
		38L 3800													
45L 4500				GLR Fusing, fast blow	DSC Quick driver disconnect	CHIC³ Chicago Plenum rated									
		Other options may be ordered in increments of 100lm from 3000 to 4500lm		AccuRender^{8,9}					BSL6LST⁴ Bodine 6W selftesting battery pack						

Ordering guide - PoE controls

example: 2STXG38L840-2-DS-LV-POE-IAO

Family	Ceiling Type	Lumens (nom. delivered)	Efficacy	Color	Length	Center Diffuser	Voltage	Driver	Driver	Options			
1STX	G			-	4 -	D -	LV -	POE -					
1STX 1' SofTrace gen 2	G Grid	Std. configs	Blank Standard	830 80 CRI, 3000K	4 4'	D Diffuse (ribbed)	LV Low voltage	POE Power over Ethernet	EMPOE 600lm integral emergency driver and battery pack	BSL10LST⁴ Bodine 10W selftesting battery pack			
		30L 3000		835 80 CRI, 3500K							ER100^{4,6,7} UL924 listed sensor bypass relay, factory installed between driver & sensor		
		38L 3800		840 80 CRI, 4000K								GTD/E^{4,6} UL924 listed Bodine GTD factory installed on driver input	
		45L 4500		850 80 CRI, 5000K									GTD/SNSR^{4,6,7} UL924 listed Bodine GTD factory installed between driver & sensor
									RADIO² Interact RF sensor for wireless connectivity only, no sensing				
										IAOSB^{2,10} Interact Pro wireless sensor with occupancy, daylight, and environmental sensing capabilities			
										AG Antimicrobial Finish			
										WL Wet location listed			

Footnotes

- Integral controls options dimmable to 5% via wireless wall switch. Non-controls options are 0-10v dimmable to 1% for Standard configurations, and to 10% for Base configurations.
- Specify only with -DIM driver option.
- CHIC option not provided with air return functionality.
- Not available with 347V.
- High efficacy option may only be ordered with Standard lumen configurations.
- Must be installed in conjunction with a UL1008 device.
- Must be ordered with an integral sensing option.
- AccuRender is 90CRI with R_a>50.
- Option is qualified as Engineered-to-Order (ETO) ready. Lead times and minimum order quantities may vary, please consult factory. (DLC Standard efficacy only)
- Must order IRT9015 Interact commissioning remote with each system order.

Accessories (order separately)

- FSF414** - 1'x4' surface mount field installation kit (field assembled)
- FMA14** - 1'x4' "F" mounting frame for NEMA "F" ceiling
- STXD14L** - 1'x4' SofTrace Gen2 ribbed replacement lens
- STXD14LC** - 1'x4' SofTrace Gen2 with controls ribbed replacement lens

SWZCS accessories (order separately)

- IRT9015** - handheld remote for grouping and configuration (at least one remote required for any SWZCS installation).

Not all product variations listed on this page are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search



1STX SofTrace recessed

1x4 recessed luminaire (up to 4500 lumens)

Application

- Ideal for modern offices, institutional, retail, and healthcare applications.
- Modern architectural styling to complementary space.
- Full width luminous lens provides smooth brightness and high visual comfort.
- Directs a controlled amount of light to higher angles to eliminate "cave effect" without creating glare.
- Available in standard efficacy and high efficacy (H) configurations up to 130lm/W.
- 80 CRI minimum source provides a balanced spectral power distribution.
- AccuRender 90 CRI source provides preferred color quality.
- Suitable for use with NEMA G (15/16") and NFG (9/16") suspended t-grid ceilings. NEMA F flange ceilings require the FMA24 accessory (ordered separately).

Environment

- Rated for dry or damp locations in operating ambient temperatures 0–30°C (32–86°F). Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility. Not suitable for natatorium environments.

Construction/Finish

- Robust and durable die-formed embossed steel housing and end caps.
- Molded one-piece acrylic diffuser may be removed without tools for access to LED boards and driver(s).
- Unique spring retainers ensure the diffuser is centered in the housing opening at all times.
- T-bar grid clips are built into luminaire end caps for quick and easy installation, no extra parts.
- Air return functionality is standard for all configurations. See air flow and noise data on page 4.
- Suitable for end to end continuous row mounting. 1" gap between luminaires requires chase nipple to accommodate through wiring (by others).
- Sheet metal components are multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance baked white enamel.
- Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Validation

- cETLus listed for use in damp locations
- Declare label certified, ID SGY-0017 ([View full Declare label](#))
- When ordered with -WL option code, suitable for use in wet locations with covered ceilings
- Rated for direct contact with insulation (IC)
- CCEA Chicago Plenum listed
- SofTrace luminaires are Designlights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers, www.designlights.org/QPL

Electrical

- Driver and LED board are accessible from below by easy removal of lens.
- Non-controls Base configurations 0–10V dimmable to 10%.
- Non-controls Standard configurations 0–10V dimmable to 1%.
- Standard configurations with controls options dimmable via wireless switches (see below).
- Predicted L70 lumen maintenance up to 85,000 hours at 25°C ambient for all configurations.
- Emergency battery packs accessible from above. To estimate lumen output in emergency mode, multiply emergency pack wattage by luminaire efficacy, then by 1.10.
- The GTD/E option is used to bypass wall switches and allow luminaire operation on auxiliary power. Generator transfer requires installation in conjunction with a UL1008 listed device.
- The GTD/SNSR option is used to bypass integrated sensor control in the event of utility power loss. Generator transfer requires installation in conjunction with a UL1008 listed device.
- Compliance to CAN ICES-005-A/ NEB-005-A and FCC Part 15-A.

Warranty

- 5 year manufacturer's limited warranty. Visit signify.com/warranties for complete warranty information.

Energy data

Configuration	Nominal CCT/CRI	Flux (lm)	Input Power (W)	Efficacy (LPW)	DLC
1STXG38B835	3500K/80	3922	34	117	Standard
1STXG38B840	4000K/80	3895	34	116	Standard
1STXG30L835	3500K/80	3011	26	114	Standard
1STXG30L840	4000K/80	2988	26	113	Standard
1STXG30LH835	3500K/80	2974	24	122	Standard
1STXG30LH840	4000K/80	3038	24	126	Premium
1STXG38L835	3500K/80	3833	34	113	Standard
1STXG38L840	4000K/80	3811	34	112	Standard
1STXG38LH835	3500K/80	3729	30	124	Standard
1STXG38LH840	4000K/80	3810	30	125	Premium
1STXG45L835	3500K/80	4556	41	110	Standard
1STXG45L840	4000K/80	4524	42	109	Standard
1STXG45LH835	3500K/80	4530	36	125	Premium
1STXG45LH840	4000K/80	4634	36	128	Premium

1STX SofTrace recessed

1x4 recessed luminaire (up to 4500 lumens)

Wireless controls options

Interact

- SWZCS is a connected sensor with integral occupancy and daylight sensing and supports wireless mesh connectivity.
- The sensor works in the standalone mode (similar to SpaceWise) when configured without a gateway or in a cloud connected mode if a compatible gateway is used.
- Interact includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & Bluetooth connectivity. The App provides flexibility to choose between a gateway or non-gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely and use IRT9015 remote on-site to identify and group devices together.

Compatible with:

- SWS200 & UID8465 wireless scene switch
- Battery powered IP42 presence sensor OCC sensor IA CM WH 10/1
- Battery powered IP42 presence & daylight sensor OCC-DL sensor IA CM IP42 WH
- LCN3110: battery powered IP65 presence sensor, OCC sensor IA CM IP65W
- LCN3120: battery powered IP65 presence & daylight sensor, OCC-DL sensor IA CM IP65 WH
- For more information on Interact visit: interact-lighting.com/interactproscalablesystem

Radio only sensor (RA or RADIO)

- Integral RA or RADIO only sensor simply enables wireless mesh connectivity to the luminaire without any occupancy or daylight sensing.
- Ideal for applications where sensing functionality is managed by other Interact devices and the luminaire only needs to have wireless connectivity.
- Interact includes an App, a portal and a broad portfolio of wireless luminaires, lamps and retrofit kits all working on the same system.
- Startup is implemented via Interact Pro App (Android or iPhone) & Bluetooth connectivity. The App provides flexibility to choose between a gateway or non-gateway mode for setup.
- Setup with the gateway requires wired internet access to the gateway. It is possible to add a gateway at a later point.
- Prepare project configuration steps remotely, identify and group devices together onsite.
- Compatible with SWS200 and UID8465 wireless scene switch, wireless Occ sensor (OCC SENSOR IA CM IP42 WH 10/1) and wireless Day/Occ sensor (OCC MULTI SENSOR IA CM WH 10/1).
- For more information on Interact visit: interact-lighting.com/interactproscalablesystem

SofTrace shown with integral sensor



Sensor bundle (IAOSB or SB)

- A wireless IoT connected lighting solution for large enterprises that span across multiple floors, buildings and require multiple gateways.
- View all your projects under one dashboard and easily compare insights from multiple projects in one view.
- Compatible with SWS200 wireless scene switch, wireless Occ sensor (OCC SENSOR IA CM IP42 WH 10/1) and wireless Day/Occ sensor (OCC MULTI SENSOR IA CM WH 10/1) and wireless Occupancy or Daylight & Occupancy sensors available. Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- IAOSB or SB option in addition to occupancy and daylights sensing supports advanced IoT capabilities, such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- Requires compatible Gateway and internet connectivity for commissioning.
- For more information, visit: interact-lighting.com/interactproscalablesystem

Emergency Options (ER100)

- **Power Sensing** (factory default) – Recommended UL924 option requires unswitched power sense line, absence of voltage on the normal circuit triggers luminaire to 100% output.
- **Power Interruption Detection** (field option) – Detects AC power interruption >30ms triggers 90 minute emergency mode with luminaire at 100% output.

Interact supported sensor option codes across Genlyte Solutions product lines

	Evokit	Day-Brite	Ledalite	Lightolier
ZigBee + Bluetooth + Sensing	SWZCS	SWZCS	CS	SBA accessory (external)
ZigBee + Bluetooth	RADIO	RADIO	RA	RA
ZigBee + Bluetooth + Sensing + Environmental data	IAOSB	IAOSB	SB	SB
ZigBee + Highbay + Sensing	-	SWZCSH	-	-

Wired Controls Options

Interact Office Wired (PoE)

- PoE based IoT connected lighting solution for large enterprises that span across multiple floors, buildings and require multiple gateways.
- Use Interact software and insights to increase building efficiency, achieve building wide integration and optimize space through occupancy analytics.
- IAOSB option in addition to occupancy and daylight sensing supports advanced IoT capabilities such as people estimation analysis, desk level temperature & humidity sensing, noise classification, and BLE beacon.
- PoE lighting controller is accessible from below.
- Integral sensor option for occupancy sensing (PIR) and/or daylight harvesting available for additional energy savings.
- Optional integral emergency controller and battery pack provides 600lm nominal output. Test switch and indicator light mounted on side of chassis on one end.
- Emergency battery has a 3 month pre-installed shelf life, and must be stored and installed in environments of 20C to 30C (-4F to 86F) ambient, and 45-85% relative humidity.
- For more information, visit: www.interact-lighting.com/office or www.usa.lighting.philips.com/systems/system-areas/offices

Energy Data (PoE)

Configuration	Nominal CCT/CRI	Flux (lm)	DC Power (W)*	Efficacy (LPW)
2STXG38L840	4000K/80	3895	30	129
2STXG43L840	4000K/80	4356	34	127
2STXG48L840	4000K/80	4891	39	124

*DC power supply

1STX SofTrace recessed

1x4 recessed luminaire (up to 4500 lumens)

interact


	Gateway Connected		
	Standalone	Option 1	Option 2
Dimming, grouping, and zoning	✓	✓	✓
Bluetooth and ZigBee enabled	✓	✓	✓
Motion sensing and daylight harvesting	✓	✓	✓
Integration with 0-10V and phase dimming fixtures	✓	✓	✓
Code compliance	✓	✓	✓
Granular dimming and dwell time	✓	✓	✓
Correlated color temperature (CCT) tuning by switch	New ✓	✓	✓
Support for sensor-based Tunable White luminaires	New ✓	✓	✓
Energy reporting and monitoring		✓	✓
Scheduling		✓	✓
Demand response		✓	✓
BMS integration (BACnet)			✓
Floor plan visualization			✓
IoT sensors for wellness			✓
IoT Apps for productivity			✓

Currently supported maximum system size

To be able to design the lighting system correctly for the customer, it is important to know the prime characteristics of the system, its possibilities and limitations.

System level	
Total number of gateways	Unlimited
Total number of devices	200 per network
• Luminaires with integrated sensors	150
• Smart TLEDS	150
• Zones + groups	64
Total number of ZGP devices (sensors and switches)	50
• Sensors	30
• Switches	50


Group level	
Recommended number of lights	40 (maximum 150)
Number of ZGP devices	5
Number of scenes	16




1STX SofTrace recessed

1x4 recessed luminaire (up to 4500 lumens)

Dimensions




Air return



Integral louvers on housing ends allow air from the heated space to return to a pressurized plenum.

Return Air Data



2x2 Return Air - noise criteria								
CFM	<15	44	56.5	69	75.5	82	94	108
NC (dB)	<15	19	21.5	24	27	30	35	39

1STX SofTrace recessed

1x4 recessed luminaire (up to 4500 lumens)

Photometry

1x4 SofTrace recessed LED, base configuration, 3800 nominal delivered lumens

LER - 116

<p>Catalog No. 1STXG38B840-4-D-UNV-DIM Test No. 40757 S/MH 1.3 Lamp Type LED Lumens 3896 Input Watts 34</p> <p>Comparative yearly lighting energy cost per 1000 lumens - \$2.07 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p>Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back 45</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>1363</td> <td>1363</td> <td>1363</td> <td>1363</td> </tr> <tr> <td>5</td> <td>1335</td> <td>1360</td> <td>1369</td> <td>1360</td> </tr> <tr> <td>15</td> <td>1287</td> <td>1311</td> <td>1318</td> <td>1311</td> </tr> <tr> <td>25</td> <td>1193</td> <td>1212</td> <td>1218</td> <td>1212</td> </tr> <tr> <td>35</td> <td>1060</td> <td>1075</td> <td>1075</td> <td>1075</td> </tr> <tr> <td>45</td> <td>892</td> <td>903</td> <td>905</td> <td>903</td> </tr> <tr> <td>55</td> <td>697</td> <td>709</td> <td>717</td> <td>709</td> </tr> <tr> <td>65</td> <td>478</td> <td>508</td> <td>518</td> <td>508</td> </tr> <tr> <td>75</td> <td>236</td> <td>276</td> <td>271</td> <td>276</td> </tr> <tr> <td>85</td> <td>56</td> <td>62</td> <td>55</td> <td>62</td> </tr> </tbody> </table>	Angle	End	45	Cross	Back 45	0	1363	1363	1363	1363	5	1335	1360	1369	1360	15	1287	1311	1318	1311	25	1193	1212	1218	1212	35	1060	1075	1075	1075	45	892	903	905	903	55	697	709	717	709	65	478	508	518	508	75	236	276	271	276	85	56	62	55	62	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr> <td>0-30</td> <td>1055</td> <td>27.1</td> </tr> <tr> <td>0-40</td> <td>1726</td> <td>44.3</td> </tr> <tr> <td>0-60</td> <td>3054</td> <td>78.4</td> </tr> <tr> <td>0-90</td> <td>3897</td> <td>100</td> </tr> <tr> <td>0-180</td> <td>3897</td> <td>100</td> </tr> </tbody> </table> <p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr> <td>45</td> <td>4322</td> <td>4377</td> <td>4385</td> </tr> <tr> <td>55</td> <td>4163</td> <td>4237</td> <td>4284</td> </tr> <tr> <td>65</td> <td>3876</td> <td>4120</td> <td>4199</td> </tr> <tr> <td>75</td> <td>3120</td> <td>3652</td> <td>3591</td> </tr> <tr> <td>85</td> <td>2190</td> <td>2442</td> <td>2167</td> </tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1055	27.1	0-40	1726	44.3	0-60	3054	78.4	0-90	3897	100	0-180	3897	100	Zone	End	45°	Cross	45	4322	4377	4385	55	4163	4237	4284	65	3876	4120	4199	75	3120	3652	3591	85	2190	2442	2167	<p>Coefficients of Utilization</p> <p>Effective Floor Cavity Reflectance 20 Per (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>Ceil</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="3">50</th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>RCR</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>0</td> <td>118</td> <td>118</td> <td>118</td> <td>115</td> <td>115</td> <td>115</td> <td>111</td> <td>111</td> </tr> <tr> <td>1</td> <td>109</td> <td>104</td> <td>98</td> <td>106</td> <td>101</td> <td>97</td> <td>96</td> <td>93</td> </tr> <tr> <td>2</td> <td>98</td> <td>90</td> <td>82</td> <td>95</td> <td>88</td> <td>81</td> <td>84</td> <td>79</td> </tr> <tr> <td>3</td> <td>90</td> <td>79</td> <td>70</td> <td>86</td> <td>78</td> <td>69</td> <td>75</td> <td>68</td> </tr> <tr> <td>4</td> <td>81</td> <td>69</td> <td>60</td> <td>80</td> <td>68</td> <td>59</td> <td>66</td> <td>58</td> </tr> <tr> <td>5</td> <td>76</td> <td>63</td> <td>53</td> <td>72</td> <td>60</td> <td>53</td> <td>58</td> <td>52</td> </tr> <tr> <td>6</td> <td>69</td> <td>56</td> <td>46</td> <td>68</td> <td>55</td> <td>46</td> <td>53</td> <td>46</td> </tr> <tr> <td>7</td> <td>65</td> <td>51</td> <td>41</td> <td>63</td> <td>50</td> <td>41</td> <td>48</td> <td>40</td> </tr> <tr> <td>8</td> <td>59</td> <td>46</td> <td>38</td> <td>58</td> <td>46</td> <td>38</td> <td>44</td> <td>36</td> </tr> <tr> <td>9</td> <td>56</td> <td>42</td> <td>34</td> <td>55</td> <td>41</td> <td>34</td> <td>40</td> <td>34</td> </tr> <tr> <td>10</td> <td>53</td> <td>39</td> <td>30</td> <td>51</td> <td>39</td> <td>30</td> <td>38</td> <td>30</td> </tr> </tbody> </table>	Ceil	80			70			50			Wall	70	50	30	70	50	30	50	30	RCR									0	118	118	118	115	115	115	111	111	1	109	104	98	106	101	97	96	93	2	98	90	82	95	88	81	84	79	3	90	79	70	86	78	69	75	68	4	81	69	60	80	68	59	66	58	5	76	63	53	72	60	53	58	52	6	69	56	46	68	55	46	53	46	7	65	51	41	63	50	41	48	40	8	59	46	38	58	46	38	44	36	9	56	42	34	55	41	34	40	34	10	53	39	30	51	39	30	38	30
		Angle	End	45	Cross	Back 45																																																																																																																																																																																																																													
0	1363	1363	1363	1363																																																																																																																																																																																																																															
5	1335	1360	1369	1360																																																																																																																																																																																																																															
15	1287	1311	1318	1311																																																																																																																																																																																																																															
25	1193	1212	1218	1212																																																																																																																																																																																																																															
35	1060	1075	1075	1075																																																																																																																																																																																																																															
45	892	903	905	903																																																																																																																																																																																																																															
55	697	709	717	709																																																																																																																																																																																																																															
65	478	508	518	508																																																																																																																																																																																																																															
75	236	276	271	276																																																																																																																																																																																																																															
85	56	62	55	62																																																																																																																																																																																																																															
Degrees	Lumens	% Luminaire																																																																																																																																																																																																																																	
0-30	1055	27.1																																																																																																																																																																																																																																	
0-40	1726	44.3																																																																																																																																																																																																																																	
0-60	3054	78.4																																																																																																																																																																																																																																	
0-90	3897	100																																																																																																																																																																																																																																	
0-180	3897	100																																																																																																																																																																																																																																	
Zone	End	45°	Cross																																																																																																																																																																																																																																
45	4322	4377	4385																																																																																																																																																																																																																																
55	4163	4237	4284																																																																																																																																																																																																																																
65	3876	4120	4199																																																																																																																																																																																																																																
75	3120	3652	3591																																																																																																																																																																																																																																
85	2190	2442	2167																																																																																																																																																																																																																																
Ceil	80			70			50																																																																																																																																																																																																																												
Wall	70	50	30	70	50	30	50	30																																																																																																																																																																																																																											
RCR																																																																																																																																																																																																																																			
0	118	118	118	115	115	115	111	111																																																																																																																																																																																																																											
1	109	104	98	106	101	97	96	93																																																																																																																																																																																																																											
2	98	90	82	95	88	81	84	79																																																																																																																																																																																																																											
3	90	79	70	86	78	69	75	68																																																																																																																																																																																																																											
4	81	69	60	80	68	59	66	58																																																																																																																																																																																																																											
5	76	63	53	72	60	53	58	52																																																																																																																																																																																																																											
6	69	56	46	68	55	46	53	46																																																																																																																																																																																																																											
7	65	51	41	63	50	41	48	40																																																																																																																																																																																																																											
8	59	46	38	58	46	38	44	36																																																																																																																																																																																																																											
9	56	42	34	55	41	34	40	34																																																																																																																																																																																																																											
10	53	39	30	51	39	30	38	30																																																																																																																																																																																																																											

1x4 SofTrace recessed LED, standard configuration, 3800 nominal delivered lumens

LER - 112

<p>Catalog No. 1STXG38L840-4-D-UNV-DIM Test No. 40755 S/MH 1.3 Lamp Type LED Lumens 3811 Input Watts 34</p> <p>Comparative yearly lighting energy cost per 1000 lumens - \$2.14 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p>Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back 45</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>1340</td> <td>1340</td> <td>1340</td> <td>1340</td> </tr> <tr> <td>5</td> <td>1312</td> <td>1336</td> <td>1345</td> <td>1336</td> </tr> <tr> <td>15</td> <td>1265</td> <td>1287</td> <td>1296</td> <td>1287</td> </tr> <tr> <td>25</td> <td>1172</td> <td>1190</td> <td>1197</td> <td>1190</td> </tr> <tr> <td>35</td> <td>1040</td> <td>1056</td> <td>1057</td> <td>1056</td> </tr> <tr> <td>45</td> <td>877</td> <td>887</td> <td>888</td> <td>887</td> </tr> <tr> <td>55</td> <td>684</td> <td>696</td> <td>704</td> <td>696</td> </tr> <tr> <td>65</td> <td>438</td> <td>466</td> <td>474</td> <td>466</td> </tr> <tr> <td>75</td> <td>231</td> <td>271</td> <td>267</td> <td>271</td> </tr> <tr> <td>85</td> <td>55</td> <td>61</td> <td>54</td> <td>61</td> </tr> </tbody> </table>	Angle	End	45	Cross	Back 45	0	1340	1340	1340	1340	5	1312	1336	1345	1336	15	1265	1287	1296	1287	25	1172	1190	1197	1190	35	1040	1056	1057	1056	45	877	887	888	887	55	684	696	704	696	65	438	466	474	466	75	231	271	267	271	85	55	61	54	61	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr> <td>0-30</td> <td>1037</td> <td>27.2</td> </tr> <tr> <td>0-40</td> <td>1696</td> <td>44.5</td> </tr> <tr> <td>0-60</td> <td>3002</td> <td>78.7</td> </tr> <tr> <td>0-90</td> <td>3812</td> <td>100</td> </tr> <tr> <td>0-180</td> <td>3813</td> <td>100</td> </tr> </tbody> </table> <p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr> <td>45</td> <td>4252</td> <td>4299</td> <td>4306</td> </tr> <tr> <td>55</td> <td>4087</td> <td>4161</td> <td>4208</td> </tr> <tr> <td>65</td> <td>3554</td> <td>3779</td> <td>3845</td> </tr> <tr> <td>75</td> <td>3062</td> <td>3593</td> <td>3532</td> </tr> <tr> <td>85</td> <td>2159</td> <td>2387</td> <td>2108</td> </tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1037	27.2	0-40	1696	44.5	0-60	3002	78.7	0-90	3812	100	0-180	3813	100	Zone	End	45°	Cross	45	4252	4299	4306	55	4087	4161	4208	65	3554	3779	3845	75	3062	3593	3532	85	2159	2387	2108	<p>Coefficients of Utilization</p> <p>Effective Floor Cavity Reflectance 20 Per (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>Ceil</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="3">50</th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>RCR</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>0</td> <td>118</td> <td>118</td> <td>118</td> <td>115</td> <td>115</td> <td>115</td> <td>111</td> <td>111</td> </tr> <tr> <td>1</td> <td>109</td> <td>104</td> <td>98</td> <td>106</td> <td>102</td> <td>97</td> <td>96</td> <td>93</td> </tr> <tr> <td>2</td> <td>98</td> <td>90</td> <td>82</td> <td>95</td> <td>88</td> <td>81</td> <td>84</td> <td>80</td> </tr> <tr> <td>3</td> <td>90</td> <td>79</td> <td>70</td> <td>86</td> <td>78</td> <td>69</td> <td>75</td> <td>68</td> </tr> <tr> <td>4</td> <td>81</td> <td>69</td> <td>60</td> <td>80</td> <td>68</td> <td>60</td> <td>66</td> <td>58</td> </tr> <tr> <td>5</td> <td>76</td> <td>63</td> <td>54</td> <td>73</td> <td>61</td> <td>53</td> <td>58</td> <td>52</td> </tr> <tr> <td>6</td> <td>69</td> <td>56</td> <td>46</td> <td>68</td> <td>55</td> <td>46</td> <td>54</td> <td>46</td> </tr> <tr> <td>7</td> <td>65</td> <td>51</td> <td>41</td> <td>63</td> <td>50</td> <td>41</td> <td>48</td> <td>40</td> </tr> <tr> <td>8</td> <td>59</td> <td>46</td> <td>38</td> <td>58</td> <td>46</td> <td>38</td> <td>45</td> <td>36</td> </tr> <tr> <td>9</td> <td>56</td> <td>42</td> <td>34</td> <td>55</td> <td>41</td> <td>34</td> <td>40</td> <td>34</td> </tr> <tr> <td>10</td> <td>53</td> <td>39</td> <td>32</td> <td>51</td> <td>39</td> <td>30</td> <td>38</td> <td>30</td> </tr> </tbody> </table>	Ceil	80			70			50			Wall	70	50	30	70	50	30	50	30	RCR									0	118	118	118	115	115	115	111	111	1	109	104	98	106	102	97	96	93	2	98	90	82	95	88	81	84	80	3	90	79	70	86	78	69	75	68	4	81	69	60	80	68	60	66	58	5	76	63	54	73	61	53	58	52	6	69	56	46	68	55	46	54	46	7	65	51	41	63	50	41	48	40	8	59	46	38	58	46	38	45	36	9	56	42	34	55	41	34	40	34	10	53	39	32	51	39	30	38	30
		Angle	End	45	Cross	Back 45																																																																																																																																																																																																																													
0	1340	1340	1340	1340																																																																																																																																																																																																																															
5	1312	1336	1345	1336																																																																																																																																																																																																																															
15	1265	1287	1296	1287																																																																																																																																																																																																																															
25	1172	1190	1197	1190																																																																																																																																																																																																																															
35	1040	1056	1057	1056																																																																																																																																																																																																																															
45	877	887	888	887																																																																																																																																																																																																																															
55	684	696	704	696																																																																																																																																																																																																																															
65	438	466	474	466																																																																																																																																																																																																																															
75	231	271	267	271																																																																																																																																																																																																																															
85	55	61	54	61																																																																																																																																																																																																																															
Degrees	Lumens	% Luminaire																																																																																																																																																																																																																																	
0-30	1037	27.2																																																																																																																																																																																																																																	
0-40	1696	44.5																																																																																																																																																																																																																																	
0-60	3002	78.7																																																																																																																																																																																																																																	
0-90	3812	100																																																																																																																																																																																																																																	
0-180	3813	100																																																																																																																																																																																																																																	
Zone	End	45°	Cross																																																																																																																																																																																																																																
45	4252	4299	4306																																																																																																																																																																																																																																
55	4087	4161	4208																																																																																																																																																																																																																																
65	3554	3779	3845																																																																																																																																																																																																																																
75	3062	3593	3532																																																																																																																																																																																																																																
85	2159	2387	2108																																																																																																																																																																																																																																
Ceil	80			70			50																																																																																																																																																																																																																												
Wall	70	50	30	70	50	30	50	30																																																																																																																																																																																																																											
RCR																																																																																																																																																																																																																																			
0	118	118	118	115	115	115	111	111																																																																																																																																																																																																																											
1	109	104	98	106	102	97	96	93																																																																																																																																																																																																																											
2	98	90	82	95	88	81	84	80																																																																																																																																																																																																																											
3	90	79	70	86	78	69	75	68																																																																																																																																																																																																																											
4	81	69	60	80	68	60	66	58																																																																																																																																																																																																																											
5	76	63	54	73	61	53	58	52																																																																																																																																																																																																																											
6	69	56	46	68	55	46	54	46																																																																																																																																																																																																																											
7	65	51	41	63	50	41	48	40																																																																																																																																																																																																																											
8	59	46	38	58	46	38	45	36																																																																																																																																																																																																																											
9	56	42	34	55	41	34	40	34																																																																																																																																																																																																																											
10	53	39	32	51	39	30	38	30																																																																																																																																																																																																																											

1x4 SofTrace recessed LED, high efficacy configuration, 3800 nominal delivered lumens

LER - 128

<p>Catalog No. 1STXG38LH840-4-D-UNV Test No. 40766 S/MH 1.3 Lamp Type LED Lumens 3810 Input Watts 30</p> <p>Comparative yearly lighting energy cost per 1000 lumens - \$1.88 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p>Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back 45</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>1341</td> <td>1341</td> <td>1341</td> <td>1341</td> </tr> <tr> <td>5</td> <td>1313</td> <td>1337</td> <td>1346</td> <td>1337</td> </tr> <tr> <td>15</td> <td>1266</td> <td>1288</td> <td>1297</td> <td>1288</td> </tr> <tr> <td>25</td> <td>1173</td> <td>1191</td> <td>1197</td> <td>1191</td> </tr> <tr> <td>35</td> <td>1040</td> <td>1056</td> <td>1058</td> <td>1056</td> </tr> <tr> <td>45</td> <td>878</td> <td>887</td> <td>888</td> <td>887</td> </tr> <tr> <td>55</td> <td>684</td> <td>696</td> <td>704</td> <td>696</td> </tr> <tr> <td>65</td> <td>438</td> <td>465</td> <td>473</td> <td>465</td> </tr> <tr> <td>75</td> <td>232</td> <td>271</td> <td>266</td> <td>271</td> </tr> <tr> <td>85</td> <td>53</td> <td>62</td> <td>55</td> <td>62</td> </tr> </tbody> </table>	Angle	End	45	Cross	Back 45	0	1341	1341	1341	1341	5	1313	1337	1346	1337	15	1266	1288	1297	1288	25	1173	1191	1197	1191	35	1040	1056	1058	1056	45	878	887	888	887	55	684	696	704	696	65	438	465	473	465	75	232	271	266	271	85	53	62	55	62	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr> <td>0-30</td> <td>1038</td> <td>27.2</td> </tr> <tr> <td>0-40</td> <td>1697</td> <td>44.5</td> </tr> <tr> <td>0-60</td> <td>3002</td> <td>78.8</td> </tr> <tr> <td>0-90</td> <td>3811</td> <td>100</td> </tr> <tr> <td>0-180</td> <td>3812</td> <td>100</td> </tr> </tbody> </table> <p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr> <td>45</td> <td>4255</td> <td>4298</td> <td>4306</td> </tr> <tr> <td>55</td> <td>4088</td> <td>4158</td> <td>4206</td> </tr> <tr> <td>65</td> <td>3550</td> <td>3768</td> <td>3833</td> </tr> <tr> <td>75</td> <td>3070</td> <td>3585</td> <td>3518</td> </tr> <tr> <td>85</td> <td>2084</td> <td>2434</td> <td>2171</td> </tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1038	27.2	0-40	1697	44.5	0-60	3002	78.8	0-90	3811	100	0-180	3812	100	Zone	End	45°	Cross	45	4255	4298	4306	55	4088	4158	4206	65	3550	3768	3833	75	3070	3585	3518	85	2084	2434	2171	<p>Coefficients of Utilization</p> <p>Effective Floor Cavity Reflectance 20 Per (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>Ceil</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="3">50</th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> </tr> </thead> <tbody> <tr> <td>RCR</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>0</td> <td>118</td> <td>118</td> <td>118</td> <td>115</td> <td>115</td> <td>115</td> <td>111</td> <td>111</td> </tr> <tr> <td>1</td> <td>109</td> <td>104</td> <td>98</td> <td>106</td> <td>102</td> <td>97</td> <td>96</td> <td>93</td> </tr> <tr> <td>2</td> <td>98</td> <td>90</td> <td>82</td> <td>95</td> <td>88</td> <td>81</td> <td>84</td> <td>80</td> </tr> <tr> <td>3</td> <td>90</td> <td>79</td> <td>70</td> <td>86</td> <td>78</td> <td>69</td> <td>75</td> <td>68</td> </tr> <tr> <td>4</td> <td>81</td> <td>69</td> <td>60</td> <td>80</td> <td>68</td> <td>60</td> <td>66</td> <td>58</td> </tr> <tr> <td>5</td> <td>76</td> <td>63</td> <td>54</td> <td>73</td> <td>61</td> <td>53</td> <td>58</td> <td>52</td> </tr> <tr> <td>6</td> <td>69</td> <td>56</td> <td>46</td> <td>68</td> <td>55</td> <td>46</td> <td>54</td> <td>46</td> </tr> <tr> <td>7</td> <td>65</td> <td>51</td> <td>41</td> <td>63</td> <td>50</td> <td>41</td> <td>48</td> <td>40</td> </tr> <tr> <td>8</td> <td>59</td> <td>46</td> <td>38</td> <td>58</td> <td>46</td> <td>38</td> <td>45</td> <td>36</td> </tr> <tr> <td>9</td> <td>56</td> <td>42</td> <td>34</td> <td>55</td> <td>41</td> <td>34</td> <td>40</td> <td>34</td> </tr> <tr> <td>10</td> <td>53</td> <td>39</td> <td>32</td> <td>51</td> <td>39</td> <td>30</td> <td>38</td> <td>30</td> </tr> </tbody> </table>	Ceil	80			70			50			Wall	70	50	30	70	50	30	50	30	RCR									0	118	118	118	115	115	115	111	111	1	109	104	98	106	102	97	96	93	2	98	90	82	95	88	81	84	80	3	90	79	70	86	78	69	75	68	4	81	69	60	80	68	60	66	58	5	76	63	54	73	61	53	58	52	6	69	56	46	68	55	46	54	46	7	65	51	41	63	50	41	48	40	8	59	46	38	58	46	38	45	36	9	56	42	34	55	41	34	40	34	10	53	39	32	51	39	30	38	30
		Angle	End	45	Cross	Back 45																																																																																																																																																																																																																													
0	1341	1341	1341	1341																																																																																																																																																																																																																															
5	1313	1337	1346	1337																																																																																																																																																																																																																															
15	1266	1288	1297	1288																																																																																																																																																																																																																															
25	1173	1191	1197	1191																																																																																																																																																																																																																															
35	1040	1056	1058	1056																																																																																																																																																																																																																															
45	878	887	888	887																																																																																																																																																																																																																															
55	684	696	704	696																																																																																																																																																																																																																															
65	438	465	473	465																																																																																																																																																																																																																															
75	232	271	266	271																																																																																																																																																																																																																															
85	53	62	55	62																																																																																																																																																																																																																															
Degrees	Lumens	% Luminaire																																																																																																																																																																																																																																	
0-30	1038	27.2																																																																																																																																																																																																																																	
0-40	1697	44.5																																																																																																																																																																																																																																	
0-60	3002	78.8																																																																																																																																																																																																																																	
0-90	3811	100																																																																																																																																																																																																																																	
0-180	3812	100																																																																																																																																																																																																																																	
Zone	End	45°	Cross																																																																																																																																																																																																																																
45	4255	4298	4306																																																																																																																																																																																																																																
55	4088	4158	4206																																																																																																																																																																																																																																
65	3550	3768	3833																																																																																																																																																																																																																																
75	3070	3585	3518																																																																																																																																																																																																																																
85	2084	2434	2171																																																																																																																																																																																																																																
Ceil	80			70			50																																																																																																																																																																																																																												
Wall	70	50	30	70	50	30	50	30																																																																																																																																																																																																																											
RCR																																																																																																																																																																																																																																			
0	118	118	118	115	115	115	111	111																																																																																																																																																																																																																											
1	109	104	98	106	102	97	96	93																																																																																																																																																																																																																											
2	98	90	82	95	88	81	84	80																																																																																																																																																																																																																											
3	90	79	70	86	78	69	75	68																																																																																																																																																																																																																											
4	81	69	60	80	68	60	66	58																																																																																																																																																																																																																											
5	76	63	54	73	61	53	58	52																																																																																																																																																																																																																											
6	69	56	46	68	55	46	54	46																																																																																																																																																																																																																											
7	65	51	41	63	50	41	48	40																																																																																																																																																																																																																											
8	59	46	38	58	46	38	45	36																																																																																																																																																																																																																											
9	56	42	34	55	41	34	40	34																																																																																																																																																																																																																											
10	53	39	32	51	39	30	38	30																																																																																																																																																																																																																											