

# PHILIPS

Spot

LED

5W-50W

GU5.3

Warm White

8719514327702



## Avoid hassle of changing bulbs

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come

### High quality light

- Bright white light

### Choose for a sustainable solution

- Safe for any room and convenient to recycle

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional spot
- Socket: GU5.3
- Technology: LED

## Bulb dimensions

- Height: 4.6 cm
- Weight: 0.048 kg
- Width: 5.1 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 390 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K

## Other characteristics

- Lamp current: 580 mA
- Efficacy: 78 lm/W

## Packaging information

- EAN: 8719514327702
- EOC: 871951432770200
- Product title: LEDspots 5-50W MR16 830 60D 4PK

## Power consumption

- Power factor: 0.6
- Voltage: 12V AC electronic V
- Wattage: 5 W
- Wattage equivalent: 50 W

## Product dimensions & weight

- Length: 4.6 cm

## Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 390 lumen
- Rated peak intensity: 400 cd
- Rated power: 5 W

## Technical specifications

- Frequency: - Hz

**Bulb characteristics**

- EAN/UPC - product: 8719514327702
- Rated beam angle: 60 degree(s)
- Height: 4.6 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 60 degree(s)
- Lamp current: 580 mA
- Net weight: 0.160 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.048 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.199 kg
- EAN: 8719514327702
- Rated luminous flux: 390 lumen
- Lamp shape: Directional spot
- Width: 5.1 cm
- Color rendering index (CRI): 80
- Height: 12.400 cm
- EOC: 871951432770200
- Rated peak intensity: 400 cd
- Socket: GU5.3
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- Length: 5.100 cm
- Product title: LEDspots 5-50W MR16 830 60D 4PK
- Power factor: 0.6
- Rated power: 5 W
- Technology: LED
- Light Color Category: Warm White
- Width: 10.500 cm
- Voltage: 12V AC electronic V
- Nominal luminous flux: 390 lumen
- Material number (12NC): 929001280477
- Wattage: 5 W
- Length: 4.6 cm
- Starting time: <0.5 s
- Wattage equivalent: 50 W
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K
- Frequency: - Hz



Issue date: 2022-06-12  
Version: 0.29

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)