

# PHILIPS

Reflector

LED

14W-120W

E27

Warm White

8719514375673



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- No visible flicker

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Technology: LED

## Bulb dimensions

- Height: 13.3 cm
- Weight: 0.184 kg
- Width: 12.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 25 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 1200 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Other characteristics

- Lamp current: 110 mA
- Efficacy: 85 lm/W

## Packaging information

- EAN: 8719514375673
- EOC: 871951437567300
- Product title: LED 14-120W PAR38 827 25D 2pk AU

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 14 W
- Wattage equivalent: 120 W

## Product dimensions & weight

- Length: 13.3 cm

## Rated values

- Rated beam angle: 25 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1200 lumen
- Rated peak intensity: 5000 cd
- Rated power: 14 W

## Technical specifications

- Frequency: 50-60 Hz

**Bulb characteristics**

- EAN/UPC - product: 8719514375673
- Rated beam angle: 25 degree(s)
- Height: 13.3 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 25 degree(s)
- Lamp current: 110 mA
- Net weight: 0.326 kg
- Rated lifetime: 15,000 h
- Intended use: Indoor
- Weight: 0.184 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.381 kg
- EAN: 8719514375673
- Rated luminous flux: 1200 lumen
- Lamp shape: Directional reflector
- Width: 12.5 cm
- Color rendering index (CRI): 80
- Height: 11.600 cm
- EOC: 871951437567300
- Rated peak intensity: 5000 cd
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 2700 K
- Length: 11.600 cm
- Product title: LED 14-120W PAR38 827 25D 2pk AU
- Power factor: 0.5
- Rated power: 14 W
- Technology: LED
- Light Color Category: Warm White
- Width: 19.600 cm
- Voltage: 220-240 V
- Nominal luminous flux: 1200 lumen
- Wattage: 14 W
- Length: 13.3 cm
- Starting time: 0.5 s
- Wattage equivalent: 120 W
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K
- Frequency: 50-60 Hz



Issue date: 2022-05-13  
Version: 0.16

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)