

# PHILIPS

Spot 40W G9 G9  
x6

LED

3.2W-40W

G9

Warm White



8719514451070



## Bright LED lighting

Philips LED light bulbs provide high-quality light, an exceptionally long life and immediate, significant energy savings.

### High-quality light

- Learn about light

### Choose a simple replacement for your old lamps

- Similar shape and size as halogen reflectors

### Choose for a sustainable solution

- Saves up to 80% energy

# Highlights

## Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on

colour appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

## Replaces halogen spots



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: G9
- Type of glass: Clear
- Lamp Finish: Clear
- Bulb material: Plastic

## Lamp dimensions

- Height: 5.4 cm
- Width: 1.65 cm

## Design and finishing

- Material: Plastic

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 8,000

## Light characteristics

- Beam angle: 300 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 400 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 125 lm/W

## Packaging information

- EAN: 8719514451070
- EOC: 871951445107000
- Product title: LED 40W G9 WW ND 6CT/6 EC

#### Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 3.2 W
- Wattage equivalent: 40 W
- Energy efficiency label (EEL): E

#### Product dimensions and weight

- Length: 5.4 cm

#### Packaging dimensions and weight

- EAN/UPC – product: 8719514451070
- Net weight: 0.04 kg
- Gross weight: 0.21 kg
- Height: 7 cm
- Length: 3.2 cm
- Width: 8 cm
- Material number (12NC): 929002495596

#### Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 453190



Issue date: 2024-02-08  
Version: 0.153

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)