



CoreLine Waterproof

WT120C G2 LED19S/840 PSD L600

CoreLine Waterproof, 16.5 W, L600 mm, 1900 lm, 4000 K, DALI, Wide beam, Frosted, IP65, IK08, TW1-ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information		Warranty period	
Lamp family code	LED19S [LED module, system flux 1900 lm]		5 years
Light source replaceable	No	Sustainability rating	Unclassified
Number of gear units	Unit	Light Technical	
Driver included	Yes	Luminous Flux	1,900 lm
Service Tag	Yes	Correlated Colour Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous efficacy (rated) (nom.)	115 lm/W
Value ladder	Performance	Colour rendering index (CRI)	>80
Serviceability class	Class B, the luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge-protection device, front cover and mechanical parts	Light source colour	840 neutral white
		Optic type	Wide beam
		Luminaire light beam spread	105°

CoreLine Waterproof

Unified Glare Rating (CEN)	25
----------------------------	----

Sustainability Data

Product non-virgin material ratio	12.4 %
GWP total B6 (kg CO2eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (W) * Service life (hrs) Declared Unit * Energy mix (kg CO2eq / kWh)
GWP total B6 (kg CO2eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (W) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO2 eq / kWh)

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	19.4 A
Inrush time	0.2 ms
Power Consumption	16.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB (16 A type B)	30
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Frosted
Overall length	665 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (height x width x depth)	76 x 80 x 665 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	0.930 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED – based luminaires – January 2018'; statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70

Product Data


Order product name	WT120C G2 LED19S/840 PSD L600
Full product name	WT120C G2 LED19S/840 PSD L600
Full EOC	871869688306800
Order code	910505100038
Material no. (12 NC)	910505100038
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696883068
Numerator – packs per outer box	1
EAN/UPC – Case	8718696883068
Product family code	WT130C [Coreline Waterproof G2 LSC]

CoreLine Waterproof

Dimensional drawing



Photometric data



Polar Normal (separate) - WT120CI - 910505100038

