



CoreLine Waterproof

WT120C G2 LED65S/840 WIA L1500

CoreLine Waterproof, 45 W, L1500 mm, 6500 lm, 4000 K, Wireless, Interact Ready, Wide beam, Frosted, IP65, IK08, TW1-ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	6,500 lm
Number of gear units	Unit	Correlated Colour Temperature (Nom)	4000 K
Driver included	Yes	Luminous efficacy (rated) (nom.)	144 lm/W
Service Tag	Yes	Colour rendering index (CRI)	>80
Lighting Technology	LED	Light source colour	840 neutral white
Value ladder	Performance	Optic type	Wide beam
Warranty period	5 years	Luminaire light beam spread	105°
		Unified Glare Rating (CEN)	25


CoreLine Waterproof

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	19 A
Inrush time	0.23 ms
Power Consumption	45 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB (16 A type B)	22
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System-ready
Control interface	Wireless
Constant light output	No
Maximum dim level	10%
Connectivity	Interact Ready
Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Frosted
Overall length	1,515 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (height x width x depth)	76 x 80 x 1515 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	1.820 kg
Approval and Application	
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C


Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	-20 to +35 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70
Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	11.5 kg CO _{2e}
Product non-virgin material ratio	11.9 %
Recyclable the content ratio of the finished product	55.7 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kWh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)
Product Data	
Order product name	WT120C G2 LED65S/840 WIA L1500
Full product name	WT120C G2 LED65S/840 WIA L1500
Full EOC	871869997578400
Order code	910505101271
Material no. (12 NC)	910505101271
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699975784
Numerator – packs per outer box	1
EAN/UPC - Case	8718699975784
Product family code	WT130C [Coreline Waterproof G2 LSC]

CoreLine Waterproof

Dimensional drawing



Photometric data



Polar Normal (separate) - WT120CI - 910505101271

