



CoreLine Downlight gen5

DN142B 20S/840 WIA-E WR IP54

CoreLine Downlight gen5, 20.4 W, D200 mm, 2000 lm, 4000 K, Wireless, Interact Ready, White reflector, IP20/54, EL-ready

D200 mm, Polycarbonate, White, Pure white (RAL9010), Recessed, Wireless driver Interact System-ready external, 2000 lm, 20.4 W, 117 lm/W, 4000 K, (0.380,0.377) SDCM \leq 5, White reflector perforated without louvre, White reflector, Polycarbonate, IP20/54 | Finger-protected; dust accumulation-protected, splash-proof, IK02 | 0.2 J standard, Safety class II, 2 cables 0.15 m with connectors 2-pole, Emergency lighting ready (through compatible battery kit accessory)

Warnings and Safety

- Do not apply excessive force to the cable & DC connector, make sure that the connector clip is locked before turning the power on.

Product data

General Information		Operating and Electrical	
Number of gear units	Unit	Correlated Colour Temperature (Nom)	4000 K
Driver included	Yes	Luminous efficacy (rated) (nom.)	117 lm/W
Service Tag	Yes	Colour rendering index (CRI)	>80
Mounting	Recessed	Beam angle of light source	- degree(s)
Value ladder	Performance	Light source colour	840 neutral white
Warranty period	5 years	Optic type	White reflector perforated without louvre
		Luminaire light beam spread	84°
		Unified Glare Rating (CEN)	25
Light Technical			
Luminous Flux	2,000 lm		
Saturated Red (R9)	<50		
		Input Voltage	220 to 240 V

CoreLine Downlight gen5

Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	10 A
Inrush time	0.002 ms
Power Consumption	20.4 W
Power Factor (Fraction)	0.95
Connection	-
Cable	2 cables 0.15 m with connectors 2-pole
Number of products on MCB (16 A type B)	100
Suitable for random switching	Yes
Protection class IEC	Safety class II
Total harmonic distortion	35 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System-ready external
Control interface	Wireless
Constant light output	No
Connectivity	Interact Ready

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	-
Reflector finish	White reflector
Overall height	105 mm
Overall diameter	216 mm
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Mounting	Recessed
Net Weight (Piece)	0.800 kg

Emergency Operation

Central Emergency	No
Emergency lighting	Emergency lighting ready (through compatible battery kit accessory)

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-

Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect	1
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.380,0.377) SDCM≤5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Embedded carbon (A1-A3)	4.67 kg CO ₂ e
Product non-virgin material ratio	32 %
Recyclable the content ratio of the finished product	32.9 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)

Product Data

Order product name	DN142B 20S/840 WIA-E WR IP54
Full product name	DN142B 20S/840 WIA-E WR IP54
Full EOC	872016910913100
Order code	910505103613
Material no. (12 NC)	910505103613
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169109131
Numerator – packs per outer box	1
EAN/UPC - Case	8720169109131
Product family code	DN142B [CoreLine Downlight gen5]

CoreLine Downlight gen5

Dimensional drawing



Photometric data



Polar Normal (separate) - DN142BI - 910505103613

